

# Current transformer - PACT RCP-4000A-1A-D140 - 2904922


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Set consisting of one 1 A measuring transducer and one Rogowski coil with signal line. Length of Rogowski coil: 450 mm, diameter: 140 mm. Length of signal line: 3 m. The Rogowski coil measures the AC current of busbars and power lines.



## Key Commercial Data

|              |   |
|--------------|---|
| Packing unit | 1 pc  |
| GTIN         | <br>4 046356 900959 |
| GTIN         | 4046356900959   |

## Technical data

### Dimensions

|        |         |
|--------|---------|
| Width  | 22.5 mm |
| Height | 85 mm   |
| Depth  | 70.4 mm |

### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)           | -30 °C ... 80 °C (Measuring coil)       |
|   | -20 °C ... 70 °C (Measuring transducer) |
| Ambient temperature (storage/transport)   | -40 °C ... 80 °C (Measuring coil)       |
|   | -25 °C ... 85 °C (Measuring transducer) |
| Maximum altitude                          | < 2000 m                                |
| Permissible humidity (operation)          | 5 % ... 95 % (non-condensing)           |
| Measuring coil degree of protection       | IP67 (not assessed by UL)               |
| Measuring transducer degree of protection | IP20                                    |

### Measuring transducer supply

|                              |                         |
|------------------------------|-------------------------|
| Nominal supply voltage       | 24 V DC -20 % ... +25 % |
| Nominal supply voltage range | 19.2 V DC ... 30 V DC   |
| Max. current consumption     | 190 mA                  |

# Current transformer - PACT RCP-4000A-1A-D140 - 2904922

## Technical data

### Measuring transducer supply

|                   |     |
|-------------------|-----|
| Power consumption | 4 W |
|-------------------|-----|

### Measuring coil input data

|                           |                    |
|---------------------------|--------------------|
| Frequency measuring range | 40 Hz ... 20000 Hz |
| Position error            | < 1 %              |
| Linearity error           | 0.1 %              |

### Measuring transducer input data

|  |   |
|--|---|
| Measuring ranges (current)                       | 100 A 250 A 400 A 630 A 1000 A 1500 A 2000 A 4000 A |
| Configurable/programmable                        | Via DIP switches                                    |
| Phase angle                                      | < 1 °   |
| Max. distances for copper cables at $P_{N \max}$ | 32 m (0.75 mm <sup>2</sup> (AWG 20))                |
|  | 64 m (1.5 mm <sup>2</sup> (AWG 16))                 |
|  | 107 m (2.5 mm <sup>2</sup> (AWG 14))                |

### Measuring transducer signal input

|                         |                                  |
|-------------------------|----------------------------------|
| Input signal (at 50 Hz) | 100 mV (1000 A)                  |
| Input impedance         | 27 kΩ (smallest measuring range) |

### Measuring coil signal output

|   |  |
|---|--|
| Output signal (at 50 Hz)                          | 100 mV (no load, at 1,000 A)   |
| Output voltage (in no-load operation)             | $V_{OUT} = M \cdot dl/dt$  |
| Output voltage (sinusoidal, in no-load operation) | 100 mV ( $V_{OUT} = 2 \cdot \pi \cdot M \cdot f \cdot I$ (M = 0.318 μH; example: At 50 Hz; I = 1,000 A)) |

### Measuring transducer signal output

|                       |                |
|-----------------------|----------------|
| Current output signal | 0 A AC ... 1 A |
| Rated power           | 1.5 VA         |
| Load                  | 0 Ω ... 1.5 Ω  |

### General data, measuring coil

|                                 |                                 |
|---------------------------------|---------------------------------|
| Length of measuring coil        | 450 mm                          |
| Diameter of measuring coil      | 8.3 mm ±0.2 mm                  |
| Length of signal cable          | 3000 mm                         |
| Conductor structure signal line | 2x 0.22 mm (Signal (tinned))    |
|                                 | 1x 0.22 mm (Shielding (tinned)) |
| Coil material                   | Elastollan                      |
| Housing material                | PC                              |
| Insulation                      | double insulation               |
| Rated insulation voltage        | 1000 V AC (rms CAT III)         |
|                                 | 600 V AC (rms CAT IV)           |
| Test voltage                    | 10.45 kV (DC / 1 min.)          |
| Basic accuracy                  | <± 0.21 %                       |
| UL, USA/Canada                  | UL 61010 Recognized             |

# Current transformer - PACT RCP-4000A-1A-D140 - 2904922

## Technical data

### General data for measuring transducer

|                            |   |
|----------------------------|---|
| Linearity error            | < 0.5 % (From the range end value)                |
| Maximum transmission error | ≤ 0.5 % (From the range end value)                |
| Frequency range            | 45 Hz ... 65 Hz                                   |
| Max. detectable harmonics  | < 2 kHz   |
| Current consumption        | < 190 mA (at 19.2 V)                              |
| Housing material           | Polyamide   |
| Test voltage               | 1.5 kV AC (Supply/input and output: 50 Hz, 1 min) |
| Operating voltage display  | Green LED   |
| UL, USA/Canada             | UL 508 Listed                                     |

### General data

|                          |  |
|--------------------------|--|
| Standards/regulations    | IEC 61010-1  |
|                          | IEC 61010-2-032  |
| Insulation               | double insulation  |
| Temperature coefficients | 0.005 %/K (+10 °C ... +70 °C, both components have the same ambient temperature) |
|                          | 0.07 %/K (-20°C ... +10°C; both components have the same ambient temperature)    |
| Typical measuring error  | < 1 %  |

### Connection data

|                                  |   |
|----------------------------------|---|
| Connection name                  | Measuring transducer side                   |
| Connection method                | Screw connection                            |
| Stripping length                 | 7 mm  |
| Screw thread                     | M3  |
| Conductor cross section solid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section AWG      | 24 ... 14                                   |
| Torque                           | 0.5 Nm ... 0.6 Nm                           |

### Standards and Regulations

|                       |                                    |
|-----------------------|------------------------------------|
| Standards/regulations | IEC 61010-1                        |
|                       | IEC 61010-2-032                    |
| Insulation            | double insulation                  |
| Pollution degree      | 2                                  |
| Overvoltage category  | III (1000 V, to neutral conductor) |
|                       | IV (600 V, to neutral conductor)   |

### Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | Lead 7439-92-1  |
| China RoHS | Environmentally Friendly Use Period = 50 years  |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

# Current transformer - PACT RCP-4000A-1A-D140 - 2904922

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27210902 |
| eCl@ss 11.0   | 27210902 |
| eCl@ss 4.0    | 27210900 |
| eCl@ss 4.1    | 27210900 |
| eCl@ss 5.0    | 27210900 |
| eCl@ss 5.1    | 27210900 |
| eCl@ss 6.0    | 27210900 |
| eCl@ss 7.0    | 27210902 |
| eCl@ss 9.0    | 27210902 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC002048 |
| ETIM 4.0 | EC002048 |
| ETIM 5.0 | EC002048 |
| ETIM 6.0 | EC002048 |
| ETIM 7.0 | EC002048 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 39121032 |
| UNSPSC 18.0 | 39121032 |
| UNSPSC 19.0 | 39121032 |
| UNSPSC 20.0 | 39121032 |
| UNSPSC 21.0 | 39121032 |

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

|     |  |                     |
|-----|--|---------------------|
| EAC |  | RU*DE*08.B.01187/19 |
|-----|--|---------------------|

## Current transformer - PACT RCP-4000A-1A-D140 - 2904922

### Accessories

#### Accessories

#### Mounting material

##### Holder - PACT RCP-CLAMP - 2904895



The optional holding device ensures the Rogowski coil is securely seated on busbars with a thickness of 10 ... 15 mm. During installation, the coil housing is pushed onto the flange of the holding device and snaps in automatically.

---

##### Holder - PACT RCP-CLAMP-5-10 - 2907888



The optional holding device ensures the Rogowski coil is securely seated on busbars that are 5 ... 10 mm thick. During installation, the coil housing is pushed onto the flange of the holding device and snaps in automatically.

---

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>