

Lower Voltage Ceramic DC Disc Capacitors 1000 V_{DC} Temperature and Voltage Stabilized


RoHS
COMPLIANT

FEATURES

- Low losses
- High stability
- High capacitance in small size
- Complete range of capacitance values
- Radial leads
- Ceramic singlelayer capacitor
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Bypassing
- Resonant circuit
- Coupling

DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper or tinned copper clad steel having diameters of 0.020" (0.51 mm) or 0.025" (0.64 mm).

The capacitors may be supplied with radial kinked or straight leads having lead spacing of 0.250" (6.35 mm) or 0.375" (9.5 mm).

The standard tolerance is $\pm 10\%$.

Coating is made of flame retardant epoxy resin in accordance with "UL 94 V-0".

CAPACITANCE RANGE

10 pF to 10 nF

RATED VOLTAGE

1000 V_{DC}

DIELECTRIC STRENGTH BETWEEN LEADS

Component test:

2500 V_{DC}, 2 s

CERAMIC DIELECTRIC

C0G, U2J (Class 1)

X5F, X7R (Class 2)

QUICK REFERENCE DATA				
DESCRIPTION	VALUE			
Ceramic Class	1		2	
Ceramic Dielectric	C0G	U2J	X5F	X7R
Voltage (V _{DC})	1000			
Min. Capacitance (pF)	10	27	56	10 000
Max. Capacitance (pF)	10	39	4700	10 000
Mounting	Radial			

INSULATION RESISTANCE

Min. 1000 ΩF or 50 000 MΩ

TOLERANCE ON CAPACITANCE

$\pm 10\%$

DISSIPATION FACTOR

2.0 % max. at 1 kHz; 1 V

CATEGORY TEMPERATURE RANGE

(-55 to +125) °C C0G, U2J, X7R

(-25 to +85) °C X5F


CLIMATIC CATEGORY ACC. TO EN 60068-1

55/125/21 C0G, U2J, X7R

25/085/21 X5F

OPERATING TEMPERATURE RANGE

(-55 to +105) °C



ORDERING INFORMATION, CERAMIC 1000 V_{DC} TEMPERATURE AND VOLTAGE STABILIZED														
C (pF)	TOL. (%)	D _{max.} DIAMETER INCH (mm)	T _{max.} THICKNESS INCH (mm)	LS LEAD SPACE INCH (mm) ± 1 mm	LO LEAD OFFSET INCH (mm) ± 0.5 mm	WIRE SIZE		FIG.	ORDERING CODE					
						AWG	INCH (mm)							
C0G (NP0)														
10	± 10	0.250 (6.4)	0.156 (4.0)	0.250 (6.4)	0.051 (1.3)	24	0.020 (0.51)	2	561R10TSQ10					
U2J (N750)														
27	± 10	0.290 (7.4)	0.156 (4.0)	0.250 (6.4)	0.047 (1.2)	24	0.020 (0.51)	2	561R10TSQ27					
30					0.039 (1.0)				561R10TSQ30					
33					0.039 (1.0)				561R10TSQ33					
39					0.039 (1.0)				561R10TSQ39					
X5F														
56	± 10	0.250 (6.4)	0.156 (4.0)	0.250 (6.4)	0.075 (1.9)	24	0.020 (0.51)	2	562R10TSQ56					
68					0.063 (1.6)				562R10TSQ68					
75					0.059 (1.5)				562R10TSQ75					
82					0.055 (1.4)				562R10TSQ82					
100					0.055 (1.4)				562R10TST10					
120					0.051 (1.3)				562R10TST12					
150					0.043 (1.1)				562R10TST15					
180					0.043 (1.1)				562R10TST18					
200					0.039 (1.0)				562R10TST20					
220					0.051 (1.3)				562R10TST22					
250		0.047 (1.2)	562R10TST25											
270		0.043 (1.1)	562R10TST27											
300		0.039 (1.0)	562R10TST30											
330		0.039 (1.0)	562R10TST33											
390		0.043 (1.1)	562R10TST39											
470		0.039 (1.0)	562R10TST47											
500		0.039 (1.0)	562R10TST50											
560		0.290 (7.4)	0.156 (4.0)	0.250 (6.4)	0.047 (1.2)				24	0.025 (0.64)	1	562R10TST56		
680					0.043 (1.1)							562R10TST68		
750					0.039 (1.0)							562R10TST75		
820	0.039 (1.0)				562R10TST82									
1000	0.035 (0.9)				562R10TSD10									
1500	0.440 (11.2)				0.156 (4.0)	0.250 (6.4)	0.051 (1.3)	22				0.025 (0.64)	1	562R10TSD15
2000	0.490 (12.4)				0.156 (4.0)	0.375 (9.5)	0.051 (1.3)							562R10TSD20
2200	0.490 (12.4)				0.156 (4.0)	0.375 (9.5)	0.047 (1.2)							562R10TSD22
2700	0.560 (14.2)				0.156 (4.0)	0.375 (9.5)	0.051 (1.3)							562R10TSD27
3300	0.560 (14.2)				0.156 (4.0)	0.375 (9.5)	0.047 (1.2)							562R10TSD33
4700	0.680 (17.3)	0.156 (4.0)	0.375 (9.5)	0.051 (1.3)	562R10TSD47									
X7R														
0.010 μF	± 10	0.680 (17.3)	0.156 (4.0)	0.375 (9.5)	0.047 (1.2)	22	0.025 (0.64)	1	562R10TSS10					

TAPE AND REEL OPTIONS

- Tape and reel available on diameter sizes 0.250" to 0.680"
- Part number codes and specifications for tape and reel packaging are found in the general information document - find web-link below

RELATED DOCUMENTS	
General Information	www.vishay.com/doc?23140



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.