

HV RAD-LDD Indust X7R HVHT200C, Ceramic, 1000 pF, -0/+100%, 2000 VDC, X7R, Commercial, High Temperature, HighVoltage, Lead Spacing = 5.08mm



Dimensions	
L	8.13mm MAX
H	7.62mm MAX
T	6.35mm MAX
S	5.08mm +/-0.762mm
LL	3.175mm MIN
F	0.635mm +0.102/-0.051mm

Packaging Specifications	
Packaging:	Waffle
Packaging Quantity:	28

General Information	
Series:	HV RAD-LDD Indust X7R HVHT200C
Style:	Radial
Description:	Commercial, High Temperature, HighVoltage
Features:	Commercial
RoHS:	No
Prop 65:	WARNING: Cancer and reproductive harm - www.p65warnings.ca.gov .
REACH:	SVHC (Pb – CAS 7439-92-1)
Termination:	Nickel
AEC-Q200:	No

Specifications	
Capacitance:	1000 pF
Capacitance Tolerance:	-0/+100%
Voltage DC:	2000 VDC
Temperature Range:	-55/+200°C
Temperature Coefficient:	X7R
Dissipation Factor:	2%
Aging Rate:	2% Loss/Decade Hour
Insulation Resistance:	100 GOhms