



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

X1270 W V S -2xXX A -6T V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:V-Stright Angle 180°
- 4.Welding Way:S-SMT
- 5.Row No-Pin No:2xXX-2x05P~2x30P
- 6.A:No gap
- 7.Material:6T:PA6T UL94V-0
- 8.Plating Category: V01-All Gold Flash

XKB Connectivity

NUMBER OF POSITIONS	DIMENSION		
	A	B	C
10	5.08	11.25	12.65
14	7.62	13.79	15.19
16	8.89	15.06	16.46
20	11.43	17.60	19.00
26	15.24	21.41	22.81
30	17.78	23.95	25.35
34	20.32	26.49	27.89
40	24.13	30.30	31.70
50	30.48	36.65	38.05
60	36.83	43.00	44.40

X1270WVS-2xXXA-6TV01	PA6T UL 94V-0	Brass	Gold Flash	X1270H
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing

					ANGLAR	±5°		DSND		SCALE: N/A	MODEL TYPE: 1.27mm BTB Style Connectors	
ΔX					L ≤ 4	±0.2		DWN		VIEW:		PART NO.:
ΔX					4 < L ≤ 16	±0.3		CHKD		UNIT: mm/in	DWG NO.: X1270WVS-2xXXA-6TV01	
ΔX					16 < L ≤ 63	±0.4		APPD		SIZE: A4		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5	UNSPECIFIED TOLERANCES			WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED			1/1	A0	