


# KYB Series

- Low impedance, high ripple and long life from KYA series
- Newly innovative electrolyte is employed to minimize impedance
- Endurance with ripple current : 4,000 to 10,000 hours at 105°C
- Non solvent resistant type
- RoHS2 Compliant




## SPECIFICATIONS

| Items  | Characteristics   |   |      |      |      |      |  |      |      |      |  |
|--|---|---|------|------|------|------|--|------|------|------|--|
| Category Temperature Range                             | -40 to +105°C   |   |      |      |      |      |  |      |      |      |  |
| Rated Voltage Range                                    | 6.3 to 100V <sub>dc</sub>   |   |      |      |      |      |  |      |      |      |  |
| Capacitance Tolerance                                  | ±20% (M) (at 20°C, 120Hz)   |   |      |      |      |      |  |      |      |      |  |
| Leakage Current  | I=0.01CV or 3μA, whichever is greater.<br>Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20°C after 2 minutes)   |   |      |      |      |      |  |      |      |      |  |
| Dissipation Factor (tan δ)                             | Rated voltage (V <sub>dc</sub> )  | 6.3V  | 10V  | 16V  | 25V  | 35V  | 50V  | 63V  | 80V  | 100V |  |
|  | tan δ (Max.)  | 0.22  | 0.19 | 0.16 | 0.14 | 0.12 | 0.10   | 0.09 | 0.09 | 0.08 |  |
|  | When nominal capacitance exceeds 1,000μF, add 0.02 to the value above for each 1,000μF increase. (at 20°C, 120Hz)   |   |      |      |      |      |  |      |      |      |  |
| Low Temperature Characteristics (Max. Impedance Ratio) | Rated voltage (V <sub>dc</sub> )  | 6.3V  | 10V  | 16V  | 25V  | 35V  | 50V  | 63V  | 80V  | 100V |  |
|  | Z(-25°C)/Z(+20°C)   | 4   | 3    | 2    | 2    | 2    | 2  | 2    | 2    | 2    |  |
|  | Z(-40°C)/Z(+20°C)   | 8   | 6    | 4    | 3    | 3    | 3  | 3    | 3    | 3    |  |
| Endurance  | The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for the specified period of time at 105°C.                      |   |      |      |      |      |  |      |      |      |  |
|  | Rated Voltage(V <sub>dc</sub> )   | 6.3 to 10V <sub>dc</sub>                                  |      |      |      |      | 16 to 100V <sub>dc</sub>                                   |      |      |      |  |
|  | Time  | φ5: 4,000hours φ6.3 & 8: 6,000hours φ10 to 18: 8,000hours |      |      |      |      | φ5: 5,000hours φ6.3 & 8: 7,000hours φ10 to 18: 10,000hours |      |      |      |  |
|  | Capacitance change  | ≤ ±30% of the initial value                               |      |      |      |      | ≤ ±25% of the initial value                                |      |      |      |  |
|  | D.F. (tan δ)  | ≤200% of the initial specified value                      |      |      |      |      | ≤200% of the initial specified value                       |      |      |      |  |
|  | Leakage current   | ≤The initial specified value                              |      |      |      |      | ≤The initial specified value                               |      |      |      |  |
| Shelf Life   | The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 500 hours at 105°C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4. |   |      |      |      |      |  |      |      |      |  |
|  | Capacitance change  | ≤ ±25% of the initial value                               |      |      |      |      |  |      |      |      |  |
|  | D.F. (tan δ)  | ≤200% of the initial specified value                      |      |      |      |      |  |      |      |      |  |
|  | Leakage current   | ≤The initial specified value                              |      |      |      |      |  |      |      |      |  |


## DIMENSIONS [mm]

- Terminal Code : E



| φD  | 5          | 6.3 | 8   | 10  | 12.5 | 16  | 18  |
|-----|------------|-----|-----|-----|------|-----|-----|
| φd  | 0.5        | 0.5 | 0.6 | 0.6 | 0.6  | 0.8 | 0.8 |
| F   | 2.0        | 2.5 | 3.5 | 5.0 | 5.0  | 7.5 | 7.5 |
| φD' | φD+0.5max. |     |     |     |      |     |     |
| L'  | L+1.5max.  |     |     |     |      |     |     |

## PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"

◆ STANDARD RATINGS

| WV<br>(V <sub>dc</sub> ) | Cap<br>(μF) | Case size<br>φD×L(mm) | Impedance<br>(Ω max./100kHz) |       | Rated<br>ripple<br>current<br>(mA <sub>rms</sub> /<br>100kHz) | Part No.           | WV<br>(V <sub>dc</sub> ) | Cap<br>(μF) | Case size<br>φD×L(mm) | Impedance<br>(Ω max./100kHz) |                    | Rated<br>ripple<br>current<br>(mA <sub>rms</sub> /<br>100kHz) | Part No.           |
|--------------------------|-------------|-----------------------|------------------------------|-------|---|--------------------|--------------------------|-------------|-----------------------|------------------------------|--------------------|---|--------------------|
|                          |             |                       | 20°C                         | -10°C |   |                    |                          |             |                       | 20°C                         | -10°C              |   |                    |
| 6.3                      | 180         | 5×11                  | 0.29                         | 1.2   | 340   | EKYB6R3E□□181ME11D | 16                       | 4,700       | 12.5×35               | 0.018                        | 0.072              | 3,140   | EKYB160E□□472MK35S |
|                          | 390         | 6.3×11                | 0.15                         | 0.60  | 540   | EKYB6R3E□□391MF11D |                          | 4,700       | 18×20                 | 0.021                        | 0.084              | 3,000   | EKYB160E□□472MM20S |
|                          | 820         | 8×11.5                | 0.087                        | 0.35  | 840   | EKYB6R3E□□821MHB5D |                          | 5,600       | 12.5×40               | 0.017                        | 0.068              | 3,640   | EKYB160E□□562MK40S |
|                          | 1,200       | 8×15                  | 0.069                        | 0.28  | 1,050   | EKYB6R3E□□122MH15D |                          | 5,600       | 16×25                 | 0.020                        | 0.080              | 3,140   | EKYB160E□□562ML25S |
|                          | 1,200       | 10×12.5               | 0.064                        | 0.26  | 1,050   | EKYB6R3E□□122MJC5S |                          | 6,800       | 16×31.5               | 0.016                        | 0.064              | 3,610   | EKYB160E□□682MLN3S |
|                          | 1,500       | 8×20                  | 0.060                        | 0.24  | 1,210   | EKYB6R3E□□152MH20D |                          | 6,800       | 18×25                 | 0.017                        | 0.068              | 3,530   | EKYB160E□□682MM25S |
|                          | 1,800       | 10×16                 | 0.049                        | 0.20  | 1,400   | EKYB6R3E□□182MJ16S |                          | 8,200       | 16×35.5               | 0.014                        | 0.056              | 4,080   | EKYB160E□□822MLP1S |
|                          | 2,200       | 10×20                 | 0.037                        | 0.15  | 1,650   | EKYB6R3E□□222MJ20S |                          | 8,200       | 18×31.5               | 0.014                        | 0.056              | 4,220   | EKYB160E□□822MMN3S |
|                          | 2,700       | 10×25                 | 0.031                        | 0.13  | 1,910   | EKYB6R3E□□272MJ25S |                          | 10,000      | 16×40                 | 0.013                        | 0.052              | 4,220   | EKYB160E□□103ML40S |
|                          | 3,300       | 10×30                 | 0.027                        | 0.11  | 2,230   | EKYB6R3E□□332MJ30S |                          | 10,000      | 18×35.5               | 0.012                        | 0.048              | 4,280   | EKYB160E□□103MMP1S |
|                          | 3,900       | 12.5×20               | 0.027                        | 0.11  | 2,230   | EKYB6R3E□□392MK20S |                          | 12,000      | 18×40                 | 0.011                        | 0.044              | 4,700   | EKYB160E□□123MM40S |
|                          | 4,700       | 12.5×25               | 0.024                        | 0.096 | 2,530   | EKYB6R3E□□472MK20S |                          | 82          | 5×11                  | 0.29                         | 1.2                | 340   | EKYB250E□□820ME11D |
|                          | 6,800       | 12.5×30               | 0.021                        | 0.084 | 2,860   | EKYB6R3E□□682MK30S |                          | 150         | 6.3×11                | 0.15                         | 0.60               | 540   | EKYB250E□□151MF11D |
|                          | 6,800       | 16×20                 | 0.025                        | 0.10  | 2,610   | EKYB6R3E□□682ML20S |                          | 330         | 8×11.5                | 0.087                        | 0.35               | 840   | EKYB250E□□331MHB5D |
|                          | 8,200       | 12.5×35               | 0.018                        | 0.072 | 3,140   | EKYB6R3E□□822MK35S |                          | 390         | 8×15                  | 0.069                        | 0.28               | 1,050   | EKYB250E□□391MH15D |
|                          | 8,200       | 18×20                 | 0.021                        | 0.084 | 3,000   | EKYB6R3E□□822MM20S |                          | 470         | 10×12.5               | 0.064                        | 0.26               | 1,050   | EKYB250E□□471MJC5S |
|                          | 10,000      | 12.5×40               | 0.017                        | 0.068 | 3,640   | EKYB6R3E□□103MK40S |                          | 560         | 8×20                  | 0.060                        | 0.24               | 1,210   | EKYB250E□□561MH20D |
|                          | 10,000      | 16×25                 | 0.020                        | 0.080 | 3,140   | EKYB6R3E□□103ML25S |                          | 680         | 10×16                 | 0.049                        | 0.20               | 1,400   | EKYB250E□□681MJ16S |
|                          | 12,000      | 16×31.5               | 0.016                        | 0.064 | 3,610   | EKYB6R3E□□123MLN3S |                          | 1,000       | 10×20                 | 0.037                        | 0.15               | 1,650   | EKYB250E□□102MJ20S |
|                          | 12,000      | 18×25                 | 0.017                        | 0.068 | 3,530   | EKYB6R3E□□123MM25S |                          | 1,200       | 10×25                 | 0.031                        | 0.13               | 1,910   | EKYB250E□□122MJ25S |
|                          | 15,000      | 16×35.5               | 0.014                        | 0.056 | 4,080   | EKYB6R3E□□153MLP1S |                          | 1,500       | 10×30                 | 0.027                        | 0.11               | 2,230   | EKYB250E□□152MJ30S |
|                          | 15,000      | 18×31.5               | 0.014                        | 0.056 | 4,220   | EKYB6R3E□□153MMN3S |                          | 1,500       | 12.5×20               | 0.027                        | 0.11               | 2,230   | EKYB250E□□152MK20S |
| 18,000                   | 16×40       | 0.013                 | 0.052                        | 4,220 | EKYB6R3E□□183ML40S  | 2,200              | 12.5×25                  | 0.024       | 0.096                 | 2,530                        | EKYB250E□□222MK25S |   |                    |
| 18,000                   | 18×35.5     | 0.012                 | 0.048                        | 4,280 | EKYB6R3E□□183MMP1S  | 2,700              | 12.5×30                  | 0.021       | 0.084                 | 2,860                        | EKYB250E□□272MK30S |   |                    |
| 22,000                   | 18×40       | 0.011                 | 0.044                        | 4,700 | EKYB6R3E□□223MM40S  | 2,700              | 16×20                    | 0.025       | 0.10                  | 2,610                        | EKYB250E□□272ML20S |   |                    |
| 10                       | 120         | 5×11                  | 0.29                         | 1.2   | 340   | EKYB100E□□121ME11D | 3,300                    | 12.5×35     | 0.018                 | 0.072                        | 3,140              | EKYB250E□□332MK35S  |                    |
|                          | 330         | 6.3×11                | 0.15                         | 0.60  | 540   | EKYB100E□□331MF11D | 3,300                    | 18×20       | 0.021                 | 0.084                        | 3,000              | EKYB250E□□332MM20S  |                    |
|                          | 560         | 8×11.5                | 0.087                        | 0.35  | 840   | EKYB100E□□561MHB5D | 3,900                    | 12.5×40     | 0.017                 | 0.068                        | 3,640              | EKYB250E□□392MK40S  |                    |
|                          | 820         | 8×15                  | 0.069                        | 0.28  | 1,050   | EKYB100E□□821MH15D | 3,900                    | 16×25       | 0.020                 | 0.080                        | 3,140              | EKYB250E□□392ML25S  |                    |
|                          | 1,000       | 8×20                  | 0.060                        | 0.24  | 1,210   | EKYB100E□□102MH20D | 4,700                    | 16×31.5     | 0.016                 | 0.064                        | 3,610              | EKYB250E□□472MLN3S  |                    |
|                          | 1,000       | 10×12.5               | 0.064                        | 0.26  | 1,050   | EKYB100E□□102MJC5S | 4,700                    | 18×25       | 0.017                 | 0.068                        | 3,530              | EKYB250E□□472MM25S  |                    |
|                          | 1,200       | 10×16                 | 0.049                        | 0.20  | 1,400   | EKYB100E□□122MJ16S | 5,600                    | 16×35.5     | 0.014                 | 0.056                        | 4,080              | EKYB250E□□562MLP1S  |                    |
|                          | 1,800       | 10×20                 | 0.037                        | 0.15  | 1,650   | EKYB100E□□182MJ20S | 6,800                    | 16×40       | 0.013                 | 0.052                        | 4,220              | EKYB250E□□682ML40S  |                    |
|                          | 2,200       | 10×25                 | 0.031                        | 0.13  | 1,910   | EKYB100E□□222MJ25S | 6,800                    | 18×31.5     | 0.014                 | 0.056                        | 4,220              | EKYB250E□□682MMN3S  |                    |
|                          | 2,700       | 10×30                 | 0.027                        | 0.11  | 2,230   | EKYB100E□□272MJ30S | 8,200                    | 18×35.5     | 0.012                 | 0.048                        | 4,280              | EKYB250E□□822MMP1S  |                    |
|                          | 2,700       | 12.5×20               | 0.027                        | 0.11  | 2,230   | EKYB100E□□272MK20S | 47                       | 5×11        | 0.29                  | 1.2                          | 340                | EKYB350E□□470ME11D  |                    |
|                          | 3,900       | 12.5×25               | 0.024                        | 0.096 | 2,530   | EKYB100E□□392MK25S | 100                      | 6.3×11      | 0.15                  | 0.60                         | 540                | EKYB350E□□101MF11D  |                    |
|                          | 4,700       | 12.5×30               | 0.021                        | 0.084 | 2,860   | EKYB100E□□472MK30S | 180                      | 8×11.5      | 0.087                 | 0.35                         | 840                | EKYB350E□□181MHB5D  |                    |
|                          | 4,700       | 16×20                 | 0.025                        | 0.10  | 2,610   | EKYB100E□□472ML20S | 270                      | 8×15        | 0.069                 | 0.28                         | 1,050              | EKYB350E□□271MH15D  |                    |
|                          | 5,600       | 12.5×35               | 0.018                        | 0.072 | 3,140   | EKYB100E□□562MK35S | 330                      | 8×20        | 0.060                 | 0.24                         | 1,210              | EKYB350E□□331MH20D  |                    |
|                          | 6,800       | 12.5×40               | 0.017                        | 0.068 | 3,640   | EKYB100E□□682MK40S | 330                      | 10×12.5     | 0.064                 | 0.26                         | 1,050              | EKYB350E□□331MJC5S  |                    |
|                          | 6,800       | 16×25                 | 0.020                        | 0.080 | 3,140   | EKYB100E□□682ML25S | 470                      | 10×16       | 0.049                 | 0.20                         | 1,400              | EKYB350E□□471MJ16S  |                    |
|                          | 6,800       | 18×20                 | 0.021                        | 0.084 | 3,000   | EKYB100E□□682MM20S | 680                      | 10×20       | 0.037                 | 0.15                         | 1,650              | EKYB350E□□681MJ20S  |                    |
|                          | 8,200       | 16×31.5               | 0.016                        | 0.064 | 3,610   | EKYB100E□□822MLN3S | 820                      | 10×25       | 0.031                 | 0.13                         | 1,910              | EKYB350E□□821MJ25S  |                    |
|                          | 8,200       | 18×25                 | 0.017                        | 0.068 | 3,530   | EKYB100E□□822MM25S | 1,000                    | 10×30       | 0.027                 | 0.11                         | 2,230              | EKYB350E□□102MJ30S  |                    |
|                          | 10,000      | 16×35.5               | 0.014                        | 0.056 | 4,080   | EKYB100E□□103MLP1S | 1,000                    | 12.5×20     | 0.027                 | 0.11                         | 2,230              | EKYB350E□□102MK20S  |                    |
|                          | 10,000      | 18×31.5               | 0.014                        | 0.056 | 4,220   | EKYB100E□□103MMN3S | 1,500                    | 12.5×25     | 0.024                 | 0.096                        | 2,530              | EKYB350E□□152MK25S  |                    |
| 12,000                   | 16×40       | 0.013                 | 0.052                        | 4,220 | EKYB100E□□123ML40S  | 1,800              | 12.5×30                  | 0.021       | 0.084                 | 2,860                        | EKYB350E□□182MK30S |   |                    |
| 12,000                   | 18×35.5     | 0.012                 | 0.048                        | 4,280 | EKYB100E□□123MMP1S  | 1,800              | 16×20                    | 0.025       | 0.10                  | 2,610                        | EKYB350E□□182ML20S |   |                    |
| 15,000                   | 18×40       | 0.011                 | 0.044                        | 4,700 | EKYB100E□□153MM40S  | 2,200              | 12.5×35                  | 0.018       | 0.072                 | 3,140                        | EKYB350E□□222MK35S |   |                    |
| 16                       | 120         | 5×11                  | 0.29                         | 1.2   | 340   | EKYB160E□□121ME11D | 2,200                    | 18×20       | 0.021                 | 0.084                        | 3,000              | EKYB350E□□222MM20S  |                    |
|                          | 270         | 6.3×11                | 0.15                         | 0.60  | 540   | EKYB160E□□271MF11D | 2,700                    | 12.5×40     | 0.017                 | 0.068                        | 3,640              | EKYB350E□□272MK40S  |                    |
|                          | 470         | 8×11.5                | 0.087                        | 0.35  | 840   | EKYB160E□□471MHB5D | 2,700                    | 16×25       | 0.020                 | 0.080                        | 3,140              | EKYB350E□□272ML25S  |                    |
|                          | 680         | 8×15                  | 0.069                        | 0.28  | 1,050   | EKYB160E□□681MH15D | 3,300                    | 16×31.5     | 0.016                 | 0.064                        | 3,610              | EKYB350E□□332MLN3S  |                    |
|                          | 680         | 10×12.5               | 0.064                        | 0.26  | 1,050   | EKYB160E□□681MJC5S | 3,300                    | 18×25       | 0.017                 | 0.068                        | 3,530              | EKYB350E□□332MM25S  |                    |
|                          | 820         | 8×20                  | 0.060                        | 0.24  | 1,210   | EKYB160E□□821MH20D | 3,900                    | 16×35.5     | 0.014                 | 0.056                        | 4,080              | EKYB350E□□392MLP1S  |                    |
|                          | 1,000       | 10×16                 | 0.049                        | 0.20  | 1,400   | EKYB160E□□102MJ16S | 4,700                    | 16×40       | 0.013                 | 0.052                        | 4,220              | EKYB350E□□472ML40S  |                    |
|                          | 1,500       | 10×20                 | 0.037                        | 0.15  | 1,650   | EKYB160E□□152MJ20S | 4,700                    | 18×31.5     | 0.014                 | 0.056                        | 4,220              | EKYB350E□□472MMN3S  |                    |
|                          | 1,800       | 10×25                 | 0.031                        | 0.13  | 1,910   | EKYB160E□□182MJ25S | 5,600                    | 18×35.5     | 0.012                 | 0.048                        | 4,280              | EKYB350E□□562MMP1S  |                    |
|                          | 2,200       | 10×30                 | 0.027                        | 0.11  | 2,230   | EKYB160E□□222MJ30S | 27                       | 5×11        | 0.48                  | 2.0                          | 238                | EKYB500E□□270ME11D  |                    |
|                          | 2,200       | 12.5×20               | 0.027                        | 0.11  | 2,230   | EKYB160E□□222MK20S | 56                       | 6.3×11      | 0.20                  | 0.80                         | 385                | EKYB500E□□560MF11D  |                    |
|                          | 3,300       | 12.5×25               | 0.024                        | 0.096 | 2,530   | EKYB160E□□332MK25S | 100                      | 8×11.5      | 0.12                  | 0.48                         | 620                | EKYB500E□□101MHB5D  |                    |
|                          | 3,900       | 12.5×30               | 0.021                        | 0.084 | 2,860   | EKYB160E□□392MK30S | 150                      | 8×15        | 0.093                 | 0.38                         | 810                | EKYB500E□□151MH15D  |                    |
|                          | 3,900       | 16×20                 | 0.025                        | 0.10  | 2,610   | EKYB160E□□392ML20S | 150                      | 10×12.5     | 0.10                  | 0.40                         | 810                | EKYB500E□□151MJC5S  |                    |

□□ : Enter the appropriate lead forming or taping code.

◆STANDARD RATINGS

| WV<br>(V <sub>dc</sub> ) | Cap<br>(μF) | Case size<br>φD×L(mm) | Impedance<br>(Ω max./100kHz) |       | Rated<br>ripple<br>current<br>(mA <sub>rms</sub> /<br>105°C,<br>100kHz) | Part No.           | WV<br>(V <sub>dc</sub> ) | Cap<br>(μF) | Case size<br>φD×L(mm) | Impedance<br>(Ω max./100kHz) |                    | Rated<br>ripple<br>current<br>(mA <sub>rms</sub> /<br>105°C,<br>100kHz) | Part No.           |
|--------------------------|-------------|-----------------------|------------------------------|-------|---|--------------------|--------------------------|-------------|-----------------------|------------------------------|--------------------|---|--------------------|
|                          |             |                       | 20°C                         | -10°C |   |                    |                          |             |                       | 20°C                         | -10°C              |   |                    |
| 50                       | 180         | 8×20                  | 0.075                        | 0.30  | 980   | EKYB500E□□181MH20D | 80                       | 56          | 8×15                  | 0.14                         | 0.56               | 585   | EKYB800E□□560MH15D |
|                          | 220         | 10×16                 | 0.069                        | 0.28  | 1,100   | EKYB500E□□221MJ16S |                          | 82          | 8×20                  | 0.11                         | 0.44               | 735   | EKYB800E□□820MH20D |
|                          | 270         | 10×20                 | 0.055                        | 0.22  | 1,300   | EKYB500E□□271MJ20S |                          | 82          | 10×12.5               | 0.14                         | 0.56               | 624   | EKYB800E□□820MJC5S |
|                          | 390         | 10×25                 | 0.043                        | 0.18  | 1,600   | EKYB500E□□391MJ25S |                          | 120         | 10×16                 | 0.10                         | 0.40               | 780   | EKYB800E□□121MJ16S |
|                          | 470         | 10×30                 | 0.038                        | 0.16  | 1,820   | EKYB500E□□471MJ30S |                          | 180         | 10×20                 | 0.075                        | 0.30               | 1,040   | EKYB800E□□181MJ20S |
|                          | 470         | 12.5×20               | 0.034                        | 0.14  | 1,820   | EKYB500E□□471MK20S |                          | 220         | 10×25                 | 0.060                        | 0.24               | 1,170   | EKYB800E□□221MJ25S |
|                          | 680         | 12.5×25               | 0.030                        | 0.12  | 2,100   | EKYB500E□□681MK25S |                          | 270         | 10×30                 | 0.053                        | 0.22               | 1,350   | EKYB800E□□271MJ30S |
|                          | 820         | 12.5×30               | 0.025                        | 0.10  | 2,450   | EKYB500E□□821MK30S |                          | 270         | 12.5×20               | 0.048                        | 0.20               | 1,430   | EKYB800E□□271MK20S |
|                          | 820         | 16×20                 | 0.028                        | 0.12  | 2,350   | EKYB500E□□821ML20S |                          | 390         | 12.5×25               | 0.039                        | 0.16               | 1,620   | EKYB800E□□391MK25S |
|                          | 1,000       | 12.5×35               | 0.021                        | 0.084 | 2,800   | EKYB500E□□102MK35S |                          | 470         | 12.5×30               | 0.033                        | 0.14               | 1,950   | EKYB800E□□471MK30S |
|                          | 1,000       | 18×20                 | 0.025                        | 0.10  | 2,600   | EKYB500E□□102MM20S |                          | 470         | 16×20                 | 0.036                        | 0.15               | 1,750   | EKYB800E□□471ML20S |
|                          | 1,200       | 12.5×40               | 0.019                        | 0.076 | 3,100   | EKYB500E□□122MK40S |                          | 560         | 12.5×35               | 0.026                        | 0.11               | 2,250   | EKYB800E□□561MM20S |
|                          | 1,200       | 16×25                 | 0.024                        | 0.096 | 2,750   | EKYB500E□□122ML25S |                          | 560         | 18×20                 | 0.032                        | 0.13               | 2,100   | EKYB800E□□561MM20S |
|                          | 1,500       | 16×31.5               | 0.019                        | 0.076 | 3,150   | EKYB500E□□152MLN3S |                          | 680         | 12.5×40               | 0.024                        | 0.096              | 2,450   | EKYB800E□□681MK40S |
|                          | 1,500       | 18×25                 | 0.021                        | 0.084 | 2,890   | EKYB500E□□152MM25S |                          | 680         | 16×25                 | 0.028                        | 0.12               | 2,250   | EKYB800E□□681ML25S |
|                          | 1,800       | 16×35.5               | 0.016                        | 0.064 | 3,550   | EKYB500E□□182MLP1S |                          | 820         | 16×31.5               | 0.022                        | 0.088              | 2,400   | EKYB800E□□821MLN3S |
|                          | 2,200       | 16×40                 | 0.014                        | 0.056 | 3,900   | EKYB500E□□222ML40S |                          | 820         | 18×25                 | 0.027                        | 0.11               | 2,270   | EKYB800E□□821MM25S |
|                          | 2,200       | 18×31.5               | 0.014                        | 0.056 | 3,800   | EKYB500E□□222MMN3S |                          | 1,000       | 16×35.5               | 0.020                        | 0.080              | 2,600   | EKYB800E□□102MLP1S |
| 2,700                    | 18×35.5     | 0.013                 | 0.052                        | 4,100 | EKYB500E□□272MMP1S  | 1,200              | 16×40                    | 0.018       | 0.072                 | 2,900                        | EKYB800E□□122ML40S |   |                    |
| 63                       | 18          | 5×11                  | 0.50                         | 2.0   | 220   | EKYB630E□□180ME11D | 1,200                    | 18×31.5     | 0.020                 | 0.080                        | 2,550              | EKYB800E□□122MMN3S  |                    |
|                          | 33          | 6.3×11                | 0.25                         | 1.0   | 350   | EKYB630E□□330MF11D | 1,500                    | 18×35.5     | 0.018                 | 0.072                        | 3,050              | EKYB800E□□152MMP1S  |                    |
|                          | 56          | 8×11.5                | 0.16                         | 0.64  | 530   | EKYB630E□□560MHB5D | 100                      | 6.8         | 5×11                  | 0.80                         | 3.2                | 163   | EKYB101E□□6R8ME11D |
|                          | 82          | 8×15                  | 0.12                         | 0.48  | 700   | EKYB630E□□820MH15D |                          | 15          | 6.3×11                | 0.43                         | 1.8                | 267   | EKYB101E□□150MF11D |
|                          | 120         | 8×20                  | 0.085                        | 0.34  | 880   | EKYB630E□□121MH20S |                          | 27          | 8×11.5                | 0.18                         | 0.72               | 462   | EKYB101E□□270MHB5D |
|                          | 120         | 10×12.5               | 0.11                         | 0.44  | 725   | EKYB630E□□121MJC5S |                          | 39          | 8×15                  | 0.14                         | 0.56               | 585   | EKYB101E□□390MH15D |
|                          | 180         | 10×16                 | 0.073                        | 0.30  | 1,050   | EKYB630E□□181MJ16S |                          | 56          | 8×20                  | 0.11                         | 0.44               | 735   | EKYB101E□□560MH20D |
|                          | 220         | 10×20                 | 0.055                        | 0.22  | 1,300   | EKYB630E□□221MJ20S |                          | 56          | 10×12.5               | 0.14                         | 0.56               | 624   | EKYB101E□□560MJC5S |
|                          | 330         | 10×25                 | 0.045                        | 0.18  | 1,550   | EKYB630E□□331MJ25S |                          | 82          | 10×16                 | 0.10                         | 0.40               | 780   | EKYB101E□□820MJ16S |
|                          | 390         | 10×30                 | 0.040                        | 0.16  | 1,780   | EKYB630E□□391MJ30S |                          | 100         | 10×20                 | 0.075                        | 0.30               | 1,040   | EKYB101E□□101MJ20S |
|                          | 390         | 12.5×20               | 0.036                        | 0.15  | 1,780   | EKYB630E□□391MK20S |                          | 120         | 10×25                 | 0.060                        | 0.24               | 1,170   | EKYB101E□□121MJ25S |
|                          | 560         | 12.5×25               | 0.030                        | 0.12  | 2,100   | EKYB630E□□561MK25S |                          | 150         | 10×30                 | 0.053                        | 0.22               | 1,350   | EKYB101E□□151MJ30S |
|                          | 680         | 12.5×30               | 0.026                        | 0.11  | 2,415   | EKYB630E□□681MK30S |                          | 180         | 12.5×20               | 0.048                        | 0.20               | 1,430   | EKYB101E□□181MK20S |
|                          | 680         | 16×20                 | 0.028                        | 0.12  | 2,250   | EKYB630E□□681ML20S |                          | 220         | 12.5×25               | 0.039                        | 0.16               | 1,620   | EKYB101E□□221MK25S |
|                          | 820         | 12.5×35               | 0.022                        | 0.088 | 2,700   | EKYB630E□□821MK35S |                          | 270         | 12.5×30               | 0.033                        | 0.14               | 1,950   | EKYB101E□□271MK30S |
|                          | 820         | 18×20                 | 0.028                        | 0.12  | 2,500   | EKYB630E□□821MM20S |                          | 270         | 16×20                 | 0.036                        | 0.15               | 1,750   | EKYB101E□□271ML20S |
|                          | 1,000       | 12.5×40               | 0.020                        | 0.080 | 3,000   | EKYB630E□□102MK40S |                          | 330         | 16×25                 | 0.028                        | 0.12               | 2,250   | EKYB101E□□331ML25S |
|                          | 1,000       | 16×25                 | 0.025                        | 0.10  | 2,730   | EKYB630E□□102ML25S |                          | 390         | 12.5×35               | 0.026                        | 0.11               | 2,250   | EKYB101E□□391MK35S |
| 1,200                    | 16×31.5     | 0.020                 | 0.080                        | 3,000 | EKYB630E□□122MLN3S  | 390                |                          | 18×20       | 0.032                 | 0.13                         | 2,100              | EKYB101E□□391MM20S  |                    |
| 1,200                    | 18×25       | 0.022                 | 0.088                        | 2,800 | EKYB630E□□122MM25S  | 470                |                          | 12.5×40     | 0.024                 | 0.096                        | 2,450              | EKYB101E□□471MK40S  |                    |
| 1,500                    | 16×35.5     | 0.018                 | 0.072                        | 3,200 | EKYB630E□□152MLP1S  | 470                | 16×31.5                  | 0.022       | 0.088                 | 2,400                        | EKYB101E□□471MLN3S |   |                    |
| 1,500                    | 18×31.5     | 0.018                 | 0.072                        | 3,300 | EKYB630E□□152MMN3S  | 560                | 16×35.5                  | 0.020       | 0.080                 | 2,600                        | EKYB101E□□561MLP1S |   |                    |
| 1,800                    | 16×40       | 0.016                 | 0.064                        | 3,590 | EKYB630E□□182ML40S  | 560                | 18×25                    | 0.027       | 0.11                  | 2,270                        | EKYB101E□□561MM25S |   |                    |
| 1,800                    | 18×35.5     | 0.017                 | 0.068                        | 3,570 | EKYB630E□□182MMP1S  | 680                | 16×40                    | 0.018       | 0.072                 | 2,900                        | EKYB101E□□681ML40S |   |                    |
| 2,200                    | 18×40       | 0.016                 | 0.064                        | 3,670 | EKYB630E□□222MM40S  | 680                | 18×31.5                  | 0.020       | 0.080                 | 2,550                        | EKYB101E□□681MMN3S |   |                    |
| 80                       | 12          | 5×11                  | 0.80                         | 3.2   | 163   | EKYB800E□□120ME11D | 820                      | 18×35.5     | 0.018                 | 0.072                        | 3,050              | EKYB101E□□821MMP1S  |                    |
|                          | 22          | 6.3×11                | 0.43                         | 1.8   | 267   | EKYB800E□□220MF11D | 1,000                    | 18×40       | 0.017                 | 0.068                        | 3,510              | EKYB101E□□102MM40S  |                    |
|                          | 39          | 8×11.5                | 0.18                         | 0.72  | 462   | EKYB800E□□390MHB5D |                          |             |                       |                              |                    |   |                    |

□ □ : Enter the appropriate lead forming or taping code.

◆RATED RIPPLE CURRENT MULTIPLIERS

● Frequency Multipliers

| Capacitance(μF) | Frequency(Hz) |      |      |      |
|-----------------|---------------|------|------|------|
|                 | 120           | 1k   | 10k  | 100k |
| 6.8 to 180      | 0.40          | 0.75 | 0.90 | 1.00 |
| 220 to 560      | 0.50          | 0.85 | 0.94 | 1.00 |
| 680 to 1,800    | 0.60          | 0.87 | 0.95 | 1.00 |
| 2,200 to 3,900  | 0.75          | 0.90 | 0.95 | 1.00 |
| 4,700 to        | 0.85          | 0.95 | 0.98 | 1.00 |

The endurance of capacitors is reduced with internal heating produced by ripple current at the rate of halving the lifetime with every 5°C rise. When long life performance is required in actual use, the rms ripple current has to be reduced.