

# Aluminum Capacitors



## FEATURES

- Load life: 2000 h at 105 °C
- Extra low impedance, high ripple current
- Polarized SMD aluminum electrolytic capacitors, non solid electrolyte
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS**  
COMPLIANT

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case size (Ø D x L in mm)	6 x 5.8 to 12.5 x 13.5
Rated capacitance range C <sub>R</sub>	10 µF to 1500 µF
Capacitance tolerance	± 20 %
Rated voltage range	6.3 V to 50 V
Category temperature range	-40 °C to 105 °C
Load life	2000 h
Based on sectional specification	IEC 60384-4 / EN 130300
Climatic category IEC 60068	40 / 105 / 56

## APPLICATIONS

- SMD technology, for high mounting density
- Industrial and professional applications
- General industrial, consumer
- Smoothing, filtering, buffering


## PACKAGING

Supplied in blister tape.

SELECTION CHART FOR C <sub>R</sub> , U <sub>R</sub> , AND RELEVANT NOMINAL CASE SIZES (Ø D x L in mm)						
C <sub>R</sub> (µF)	RATED VOLTAGE (V)					
	6.3	10	16	25	35	50
10	→	→	→	→	→	6.3 x 5.8
22	→	→	→	→	→	6.3 x 5.8
33	→	→	→	→	6.3 x 5.8	8 x 6.2
47	→	→	→	→	6.3 x 5.8	8 x 6.2
68	→	→	→	6.3 x 5.8	8 x 6.2	8 x 10
100	→	→	6.3 x 5.8	8 x 6.2	8 x 10	10 x 10
220	6.3 x 5.8	6.3 x 7.7	8 x 6.2	8 x 10	10 x 10	-
330	8 x 6.2	→	8 x 10	-	-	-
470	→	8 x 10	10 x 10	-	-	-
680	→	10 x 10	-	-	-	-
1000	10 x 10	-	-	-	-	-
1500	10 x 10	-	-	-	-	-



ELECTRICAL DATA AND ORDERING INFORMATION							
$U_R$ (V)	$C_R$ 120 Hz ( $\mu$ F)	DIMENSIONS D x L (mm)	$\tan \delta$ 120 Hz	Z 100 kHz / 20 °C ( $\Omega$ )	$I_R$ 100 kHz / 105 °C (mA)	WEIGHT (g)	CATALOG NUMBER
25	68	6.3 x 5.8	0.14	0.44	230	0.30	MALSECL00AD268EARK
	100	8 x 6.2	0.14	0.26	300	0.55	MALSECL00AE310EARK
	220	8 x 10	0.14	0.17	450	1.00	MALSECL00AF322EARK
35	33	6.3 x 5.8	0.12	0.44	230	0.30	MALSECL00AD233FARK
	47	6.3 x 5.8	0.12	0.44	230	0.30	MALSECL00AD247FARK
	68	8 x 6.2	0.12	0.26	300	0.55	MALSECL00AE268FARK
	100	8 x 10	0.12	0.17	450	1.00	MALSECL00AF310FARK
	220	10 x 10	0.12	0.09	670	1.21	MALSECL00AG322FARK
50	10	6.3 x 5.8	0.12	0.88	165	0.30	MALSECL00AD210HARK
	22	6.3 x 5.8	0.12	0.88	165	0.30	MALSECL00AD222HARK
	33	8 x 6.2	0.12	0.63	300	0.55	MALSECL00AE233HARK
	47	8 x 6.2	0.12	0.63	300	0.55	MALSECL00AE247HARK
	68	8 x 10	0.12	0.34	450	1.00	MALSECL00AF268HARK
	100	10 x 10	0.12	0.18	670	1.21	MALSECL00AG310HARK

**REFLOW SOLDERING CONDITIONS FOR SMD ALUMINUM ELECTROLYTIC CAPACITORS**


PROFILE FEATURE	SOLDERING CONDITION		
	$\varnothing$ 4 TO $\varnothing$ 10	$\varnothing$ 12.5	$\varnothing$ 16
Average ramp-up rate ( $T_L$ to $T_P$ )	3 °C/s max.	3 °C/s max.	
Preheat			
Temperature min. ( $T_s$ min.)	150 °C	150 °C	
Temperature max. ( $T_s$ max.)	200 °C	200 °C	
Time ( $T_s$ min. to $T_s$ max.)	60 s to 150 s	40 s to 120 s	40 s to 100 s
$T_s$ max. to $T_L$			
Ramp-up rate	3 °C/s max.	3 °C/s max.	
Time maintained above			
Temperature ( $T_L$ )	217 °C	217 °C	
Time ( $t_L$ )	60 s to 90 s	40 s to 60 s	
Peak / classification temperature ( $T_P$ )	250 °C	240 °C	230 °C
Time within 5 °C of actual peak temperature ( $T_P$ )	10 s max.	10 s max.	
Ramp-down rate	3 °C/s max.	3 °C/s max.	
Time 25 °C to peak temperature	8 min max.	8 min max.	



RESISTANCE TO SOLDERING HEAT	
Leakage current	Less than specified value
Capacitance value	Within $\pm 10\%$ of initial value
$\tan \delta$	Less than specified value

LOW TEMPERATURE BEHAVIOR (at 120 Hz)								
IMPEDANCE RATIO (Z) T2/(Z) T1	RATED VOLTAGE (V)							
T2/T1	6.3	10	16	25	35	50	63	100
-25 °C / +20 °C	2	2	2	2	2	2	3	3
-40 °C / +20 °C	3	3	3	3	3	3	4	4

MULTIPLIER OF RIPPLE CURRENT ( $I_R$ ) AS A FUNCTION OF FREQUENCY	
FREQUENCY (Hz)	$I_R$ MULTIPLIER
50	0.41
120	0.59
300	0.69
1000	0.80
10 000	0.88
100 000	1.00

ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
<b>Current</b>		
Leakage current (test conditions: $U_R$ , 20 °C)	After 2 min at $U_R$	$I_{L2} \leq 0.01 \times C_R \times U_R$ or 3 $\mu$ A for $U_R \leq 100$ V (whichever is greater)
<b>Resistance</b>		
Equivalent series resistance (ESR)	Calculated from $\tan \delta_{max}$ .	$ESR = \tan \delta / 2 \pi f C_R$

TEST PROCEDURES AND REQUIREMENTS		
TEST	PROCEDURE (quick reference)	REQUIREMENTS
Load life	$T_{amb} = 105$ °C $U_R$ and $I_R$ applied After 2000 h	$\Delta C/C: \pm 25\%$ of initial value $I_L \leq$ spec. limit $\tan \delta \leq 2 \times$ spec. limit
Shelf life	No voltage applied After 1000 h After test: $U_R$ to be applied for 30 min 24 h to 48 h before measurement	$\Delta C/C: \pm 25\%$ of initial value $I_L \leq$ spec. limit $\tan \delta \leq 2 \times$ spec. limit

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.