


D4UB60 THRU D4UB100 SINGLE PHASE 4.0 AMP BRIDGE RECTIFIERS

FEATURES

- * Ideal for printed circuit board
- * Low forward voltage
- * Low leakage current
- * Polarity: marked on body
- * Mounting position: Any
- * Weight: 4.8 grams



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS


Rating 25°C ambient temperature uniess otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

	Symbols	D4UB60	D4UB80	D4UB100	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	600	800	1000	Volts
Maximum RMS Voltage	V _{RMS}	420	560	700	Volts
Maximum DC Blocking Voltage	V _{DC}	600	800	1000	Volts
Maximum Average Forward Rectified Current	T	4.0			Amp
.375"(9.5mm) Lead Length at T _A =50	I _(AV)				
Peak Forward Surge Current,					Amp
8.3ms single half-sine-wave	I _{FSM} 100				
superimposed on rated load (JEDEC method)					
Maximum Forward Voltage	V _F 1.1			Volts	
at 4.0A DC and 25					
Maximum Reverse Current at T _A =25	T	IR 10.0 500			uAmp
at Rated DC Blocking Voltage T _A =100	1 _R				
Typical Junction Capacitance (Note 1)	CJ	25			pF
Typical Thermal Resistance (Note 2)	R _{0JA}	25			/W
Typical Thermal Resistance (Note 2)	R _{0JL}	16			/W
Operating and Storage Temperature Range	T _J , Tstg		-55 to +150		

NOTES:

1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.

2- Thermal Resistance Junction to Ambient and form junction to lead at 0.375"(9.5mm) lead length P.C.B. Mounted.



www.gk-goodwork.com.