

Vishay Semiconductors

HALOGEN

FREE

Small Signal Switching Diodes, Low Leakage Current



FEATURES

- Silicon planar diodes
- · Saving space
- · Hermetic sealed parts
- Fits onto SOD-323/SOT-23 footprints
- Electrical data identical with the devices BAQ33 to BAQ35, BAQ133 to BAQ135
- Very low reverse current
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



• Protection circuits, time delay circuits, peak follower circuits, logarithmic amplifiers



DESIGN SUPPORT TOOLS click logo to get started



MECHANICAL DATA

Case: MicroMELF Weight: approx. 12 mg Cathode band color: black Packaging codes / options:

TR3/10K per 13" reel (8 mm tape), 10K/box TR/2.5K per 7" reel (8 mm tape), 12.5K/box

PARTS TABLE							
PART	TYPE DIFFERENTIATION	ORDERING CODE	CIRCUIT CONFIGURATION	REMARKS			
BAQ333	$V_{RRM} = 40 \text{ V}$	BAQ333-TR3 or BAQ333-TR	Single	Tape and reel			
BAQ334	V _{RRM} = 70 V	BAQ334-TR3 or BAQ334-TR	Single	Tape and reel			
BAQ335	V _{RRM} = 140 V	BAQ335-TR3 or BAQ335-TR	Single	Tape and reel			

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT	
		BAQ333	V_{RRM}	40	V	
Repetitive peak reverse voltage		BAQ334	V_{RRM}	70	V	
		BAQ335	V_{RRM}	140	V	
		BAQ333	V_R	30	V	
Reverse voltage		BAQ334	V_R	60	V	
		BAQ335	V_R	125	V	
Peak forward surge current	t _p = 1 μs		I _{FSM}	2	А	
Forward continuous current			l _F	200	mA	

THERMAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Thermal resistance junction to ambient air	Mounted on epoxy-glass hard tissue, fig. 4 35 µm copper clad, 0.9 mm ² copper area per electrode	R_{thJA}	500	K/W		
Junction temperature		Tj	175	°C		
Storage temperature range		T _{stg}	-65 to +175	°C		



www.vishay.com

Vishay Semiconductors

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I _F = 100 mA		V_{F}			1	V
	E ≤ 300 lx, rated V _R		I _R		1	3	nA
	$E \le 300 \text{ lx}$, rated V_R , $T_j = 125 ^{\circ}\text{C}$		I _R			0.5	μΑ
Reverse current	E ≤ 300 lx, V _R = 15 V	BAQ333	I _R		0.5	1	nA
	$E \le 300 \text{ lx}, V_R = 30 \text{ V}$	BAQ334	I _R		0.5	1	nA
	$E \le 300 Ix, V_R = 60 V$	BAQ335	I _R		0.5	1	nA
	$I_R = 5 \mu A, t_p/T = 0.01,$ $t_p = 0.3 \text{ ms}$	BAQ333	V _(BR)	40			V
Breakdown voltage		BAQ334	V _(BR)	70			V
		BAQ335	V _(BR)	140			V
Diode capacitance	V _R = 0 V, f = 1 MHz		C _D			3	pF

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Reverse Current vs. Junction Temperature




Fig. 3 - Board for R_{thJA} Definition (in mm)





Fig. 2 - Forward Current vs. Forward Voltage




www.vishay.com


Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters (inches): MicroMELF





Foot print recommendation:



Created - Date: 26.July.1996 Rev. 13 - Date: 07.June.2006 Document no.:6.560-5007.01-4 96 12072

^{*} The gap between plug and glass can be either on cathode or anode side



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.