

Voltage rating:500V AC/DC

额定电压:500V AC/DC

Current rating:1.0A

额定电流:1.0A

Insulation resistance:1000MΩ Min

绝缘电阻:1000MΩ Min

Withstanding voltage:≥500V AC/minute

耐压:≥500VC/分钟

Temperature range:-40℃-+105℃

使用温度:-40℃-+105℃

X1270 W V S -2xXX A2 -6T XX  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Series No.

② Category:W-wafer

③ Welding Board Angle:V- Straight 180°



④ Welding Way:S-SMT

⑤ Row No.-Pin No.:2xXX-2x04P~2x40P

⑥ A2:1.27x2.54mm

⑦ Material:6T-Nylon PA6T UL94V-0

⑧ Planting Category:V01-Gold Plating Or Sn-Tin Plating



广东星坤科技股份有限公司

ΔX	生效	日期
ΔX		
ΔX		
MARK	DESCRIPTION	DATE

文件工程章

REVISIONS UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5



DSND	SCALE: N/A	MODEL TYPE: 1.27x2.54mm
DWN	VIEW:	PART NO.: X1270WVS-2xXXA2-6TXX
CHKD	UNIT: mm/in	DWG NO.: X-X1270WVS-2xXXA2-6TXX
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO.,LIMITED