



Straight Type



Voltage rating:500V AC/DC

额定电压:500V AC/DC

Current rating:1.0A

额定电流: 1.0A

Insulation resistance:1000MΩ Min

绝缘电阻: 1000MΩ Min

Withstanding voltage:≥500V AC/minute

耐压: ≥500V/分钟

Temperature range:-40 °C~+105 °C

使用温度: -40 °C~+105 °C

X1270 W V -2xXX A2 - 6T V01  
① ② ③ ④ ⑤ ⑥ ⑦

① Series No.

② Category:W-wafer


③ Welding Board Angle:V- Straight 180°

④ Row No.-Pin No.:2xXX-2x04P~2x40P


⑤ A2:1.27x2.54mm No gaps

⑥ Material:6T-Nylon PA6T UL94V-0

⑦ Planting Category:V01-All Gold Flash



P.C.B Layout



position	A	B	C
2x04	12.64	11.04	3.81
2x05	13.91	12.31	5.08
2x06	15.18	13.58	6.35
2x07	16.45	14.85	7.62
2x08	17.72	16.12	8.89
2x10	20.26	18.66	11.43
2x13	24.07	22.47	15.24
2x15	26.61	25.01	17.78
2x17	29.15	27.55	20.32
2x20	32.96	31.36	24.13
2x22	35.50	33.90	26.67
2x25	39.31	37.71	30.48
2x30	45.66	44.06	36.83
2x33	48.20	46.60	39.37
2x34	50.74	49.14	41.91
2x40	58.36	56.76	49.53

广东星坤科技股份有限公司

ΔX	生效	日期
ΔX		
ΔX		
MARK	文件工程草	DESCRIPTION
	REVISIONS	DATE
	REVISED	APPROVED
	UNSPECIFIED TOLERANCES	

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

XKIB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE: 1.27x2.54mm
DWN	VIEW:	PART NO.: X1270WV-2xXXA2-6TV01
CHKD	UNIT: mm/in	DWG NO.: X-X1270WV-2xXXA2-6TV01
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0