STEALTH™ Diode

15 A, 600 V

ISL9R1560G2, ISL9R1560P2, ISL9R1560S3S

Description

The ISL9R1560G2, ISL9R1560P2, ISL9R1560S3S is a STEALTH diode optimized for low loss performance in high frequency hard switched applications. The STEALTH family exhibits low reverse recovery current (I_{rr}) and exceptionally soft recovery under typical operating conditions. This device is intended for use as a free wheeling or boost diode in power supplies and other power switching applications. The low I_{rr} and short ta phase reduce loss in switching transistors. The soft recovery minimizes ringing, expanding the range of conditions under which the diode may be operated without the use of additional snubber circuitry. Consider using the STEALTH diode with an SMPS IGBT to provide the most efficient and highest power density design at lower cost.

Features

- Stealth Recovery $t_{rr} = 29.4 \text{ ns}$ (@ $I_F = 15 \text{ A}$)
- Max Forward Voltage, $V_F = 2.2 \text{ V}$ (@ $T_C = 25^{\circ}\text{C}$)
- 600 V Reverse Voltage and High Reliability
- Avalanche Energy Rated
- These Devices are Pb-Free and are RoHS Compliant


Applications

- SMPS
- Hard Switched PFC Boost Diode
- UPS Free Wheeling Diode
- Motor Drive FWD
- SMPS FWD
- Snubber Diode





ON Semiconductor®

www.onsemi.com




TO-247-2LD CASE 340CL





TO-220-2LD CASE 340BA





D²PAK-3 (TO-263, 3-LEAD) CASE 418AJ



MARKING DIAGRAM

\$Y = ON Semiconductor Logo &Z = Assembly Plant Code &3 = Numeric Date Code &K = Lot Code

R1560G2, R1560P2,

R1560S3S = Specific Device Code

SYMBOL



ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

DEVICE MAXIMUM RATINGS ($T_C = 25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Ratings	Unit
Repetitive Peak Reverse Voltage	V _{RRM}	600	V
Working Peak Reverse Voltage	V _{RWM}	600	V
DC Blocking Voltage	V _R	600	V
Average Rectified Forward Current (T _C = 145°C)	I _{F(AV)}	15	Α
Repetitive Peak Surge Current (20 kHz Square Wave)	I _{FRM}	30	Α
Non-repetitive Peak Surge Current (Halfwave 1 Phase 60 Hz)	I _{FSM}	200	Α
Power Dissipation	P _D	150	W
Avalanche Energy (1 A, 40 mH)	E _{AVL}	20	mJ
Operating and Storage Temperature Range	$T_{J_i}T_{STG}$	-55 to +175	°C
Maximum Temperature for Soldering Leads at 0.063 in (1.6 mm) from Case for 10 s Package Body for 10 s, See Techbrief TB334	T _L T _{PKG}	300 260	°C °C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

PACKAGE MARKING AND ORDERING INFORMATION

Device	Device Marking	Package	Packing Method	Reel Size	Tape Width	Quantity
ISL9R1560G2	R1560G2	TO-247-2LD	Tube	N/A	N/A	30
ISL9R1560P2	R1560P2	TO-220-2LD	Tube	N/A	N/A	50
ISL9R1560S3ST	R1560S3S	TO-263(D ² -PAK)	Reel	13" dia	24 mm	800

THERMAL CHARACTERISTICS

Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit
Thermal Resistance Junction to Case	$R_{\theta JC}$		-	-	1.0	°C/W
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	TO-247	_	_	30	°C/W
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	TO-220	-	_	62	°C/W
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	TO-263	-	-	62	°C/W

ELECTRICAL CHARACTERISTICS ($T_C = 25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Test Conditions		Min	Тур	Max	Unit
Off State Characteristics	•				•	•	
Instantaneous Reverse Current	I _R	V _R = 600 V	T _C = 25°C	-	_	100	μΑ
			T _C = 125°C	-	_	1.0	mA
On State Characteristics							-
Instantaneous Forward Voltage	V _F	I _F = 15 A	T _C = 25°C	-	1.8	2.2	V
			T _C = 125°C	_	1.65	2.0	V
Dynamic Characteristics							-
Junction Capacitance	СЈ	V _R = 10 V, I _F = 0 A		ı	62	-	pF
Switching Characteristics							
Reverse Recovery Time	t _{rr}	$I_F = 1 \text{ A, } dI_F/dt = 100 \text{ A/}\mu\text{s, } V_R = 30 \text{ V}$		-	25	30	ns
		$I_F = 15 \text{ A}, dI_F/dt = 100 \text{ A/}\mu\text{s}, V_R = 30 \text{ V}$		_	35	40	ns
Reverse Recovery Time	t _{rr}	I _F = 15 A, dI _F /dt = 200 A/μs, V _R = 390 V,		-	29.4	-	ns
Reverse Recovery Current	I _{rr}			_	3.5	-	Α
Reverse Recovered Charge	Q_{rr}	T _C = 25°C		-	57	-	nC
Reverse Recovery Time	t _{rr}	I _F = 15 A,		-	90	_	ns
Softness Factor (t _b / _{ta})	S	dl _F /dt = 200 A/μs, V _R = 390 V,		-	2.0	_	
Reverse Recovery Current	I _{rr}	T _C = 125°C		-	5.0	-	Α
Reverse Recovered Charge	Q _{rr}			-	275	-	nC
Reverse Recovery Time	t _{rr}	I _F = 15 A,		_	52	-	ns
Softness Factor (t _b / _{ta})	S	dI _F /dt = 800 A/μs, V _R = 390 V, T _C = 125°C		-	1.36	_	
Reverse Recovery Current	I _{rr}			-	13.5	_	Α
Reverse Recovered Charge	Q _{rr}			-	390	_	nC
Maximum di/dt During t _b	dl _{M/} dt			-	800	-	A/μs

TYPICAL PERFORMANCE CURVES




Figure 1. Forward Current vs. Forward Voltage




Figure 2. Reverse Current vs. Reverse Voltage




Figure 3. ta and tb Curves vs. Forward Current




Figure 4. t_a and t_b Curves vs. dl_F/dt




Figure 5. Maximum Reverse Recovery Current vs. Forward Current




Figure 6. Maximum Reverse Recovery Current vs. dl_F/dt

TYPICAL PERFORMANCE CURVES (continued)




Figure 7. Reverse Recovery Softness Factor vs. dl_F/dt




Figure 8. Reverse Recovered Charge vs. dI_F/dt




Figure 9. Junction Capacitance vs. Reverse Voltage




Figure 10. DC Current Derating Curve





Figure 11. Normalized Maximum Transient Thermal Impedance


TEST CIRCUIT AND WAVEFORMS



 $0 \xrightarrow{\text{l}_{\text{F}}} \frac{\text{d}_{\text{I}_{\text{F}}}}{\text{d}^{\text{T}}} \xrightarrow{\text{d}_{\text{F}}} \frac{\text{d}_{\text{F}}}{\text{d}^{\text{T}}} \xrightarrow{\text{d}_{\text{F}}} \frac{\text{d}_{\text{F}}} \xrightarrow{\text{d}_{\text{F}}} \frac{\text{d}_{\text{F}}} \xrightarrow{\text{d}_{\text{F}}} \xrightarrow{\text{d}_{\text{F}}} \frac{\text{d}_{\text{$

Figure 12. t_{rr} Test Circuit

Figure 13. t_{rr} Waveforms and Definitions






Figure 14. Avalanche Energy Test Circuit


Figure 15. Avalanche Current and Voltage Waveforms


STEALTH is a trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.



TO-220-2LD CASE 340BA ISSUE O

DATE 31 AUG 2016





NOTES:


- A. PACKAGE REFERENCE: JEDEC TO220 VARIATION AC.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
 C. DIMENSION AND TOLERANCE AS PER ASME Y14.5-2009.
- D. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.

DOCUMENT NUMBER:	98AON13831G	Electronic versions are uncontrolled except when accessed directly from Printed versions are uncontrolled except when stamped "CONTROLLED"	
DESCRIPTION:	TO-220-2LD		PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

DATE 03 DEC 2019


TO-247-2LD CASE 340CL **ISSUE A**





- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 2009.
 D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

GENERIC MARKING DIAGRAM*



XXXX = Specific Device Code

= Assembly Location

= Year

WW = Work Week

= Assembly Lot Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

	L	
Ø P		Ø <u>P1</u> D2
E1 —	1	D1
•		

DIM	MILLIMETERS			
DIM	MIN	NOM	MAX	
Α	4.58	4.70	4.82	
A1	2.29	2.40	2.66	
A2	1.30	1.50	1.70	
b	1.17	1.26	1.35	
b2	1.53	1.65	1.77	
С	0.51	0.61	0.71	
D	20.32	20.57	20.82	
D1	16.37	16.57	16.77	
D2	0.51	0.93	1.35	
Е	15.37	15.62	15.87	
E1	12.81	l	~	
E2	4.96	5.08	5.20	
е	~	11.12	~	
L	15.75	16.00	16.25	
L1	3.69	3.81	3.93	
ØΡ	3.51	3.58	3.65	
Ø P 1	6.61	6.73	6.85	
Q	5.34	5.46	5.58	
S	5.34	5.46	5.58	


DOCUMENT NUMBER:	98AON13850G	Electronic versions are uncontrolled except when accessed directly from the Document Repo Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	TO-247-2LD		PAGE 1 OF 1

ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.



D²PAK-3 (TO-263, 3-LEAD) CASE 418AJ ISSUE F

DATE 11 MAR 2021




RECOMMENDED MOUNTING FOOTPRINT


For additional information on our Pb-Free strategy and soldering details, please download the IN Seniconductor Soldering and Mounting Techniques Reference Manual, SILIERRM/D.


NOTES


- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
- 2. CONTROLLING DIMENSION: INCHES
- 3. CHAMFER OPTIONAL.
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH.
 MOLD FLASH SHALL NOT EXCEED 0.005 PER SIDE.
 THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST
 EXTREMES OF THE PLASTIC BODY AT DATUM H.
- 5. THERMAL PAD CONTOUR IS OPTIONAL WITHIN DIMENSIONS E, L1, D1, AND E1.
- 6. OPTIONAL MOLD FEATURE.
- 7. ①,② ... DPTIONAL CONSTRUCTION FEATURE CALL DUTS.

	INCHES		MILLIN	ETERS
DIM	MIN.	MAX.	MIN.	MAX.
Α	0.160	0.190	4.06	4.83
A1	0.000	0.010	0.00	0.25
b	0.020	0.039	0.51	0.99
С	0.012	0.029	0.30	0.74
c2	0.045	0.065	1.14	1.65
D	0.330	0.380	8.38	9.65
D1	0.260		6.60	
E	0.380	0.420	9.65	10.67
E1	0.245		6.22	
e	0.100	BSC	2.54	BSC
Н	0.575	0.625	14.60	15.88
L	0.070	0.110	1.78	2.79
L1		0.066		1.68
L5		0.070		1.78
L3	0.010 BSC		0.25	BSC
м	0+	8*	n•	8.












VIEW A-A







VIEW A-A

OPTIONAL CONSTRUCTIONS

GENERIC MARKING DIAGRAMS*

XXXXXX = Specific Device Code A = Assembly Location

 WL
 = Wafer Lot

 Y
 = Year

 WW
 = Work Week

 W
 = Week Code (SSG)

 M
 = Month Code (SSG)

 G
 = Pb-Free Package

 AKA
 = Polarity Indicator

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " •", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:

98AON56370E

Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

DESCRIPTION:

D²PAK-3 (TO-263, 3-LEAD)

PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative