

Inductors for decoupling circuits **Multilayer ferrite** MLZ series (for automotive A²B)











MLZ2012-A type













FEATURES

- O Inductors for automotive A²B (Audiobus), compatible with an operating temperature range of –55 to +125°C.
- Oue to the narrow tolerance (±8%) of the inductance, the optimal characteristics are realized for automotive A²B.
- Olt has high DC superimposed properties and is suitable for high current applications.
- Operating temperature range: -55 to +125°C (including self-temperature rise)
- Ocompliant with AEC-Q200

APPLICATION

O Automotive A²B (Audiobus)

■ PART NUMBER CONSTRUCTION

M	MLZ 2012		M	1	3F	3	ļ A	Ą	-	Γ	D	69	
Serie	es name		imensions ×1.25 mm	Prod interna			tance H)	Characte	ristic type	Packagi	ng style	Interna	al code

CHARACTERISTICS SPECIFICATION TABLE

L		Thickness	L measuring	conditions	DC resistance	Rated current	Reference value	Part No.
		Т	Frequency	Current		(Isat)*1	(Itemp)*2	
(µH)	Tolerance*3	(mm)	(MHz)	(mA)	(Ω)±30%	(mA)max.	(mA)typ.	
3.3	+20%	1.25	2	0.1	0.20	350	500	ML 72012M3B3ATD69

^{*1} Current assumed when inductance ratio has decreased by 50% max...

Measurement equipment

Measurement item	Product No.	Manufacturer
L	4294A+16034G	Keysight Technologies
DC resistance	Type-7561	Yokogawa

^{*} Equivalent measurement equipment may be used.




^{*2} Current assumed when temperature has risen to 20°C typ. (reference value). Operating temperature environment at this time: 105°C max.

^{*3} The inductance tolerance within the same lot is guaranteed to be ±8% of the center value.



MLZ2012-A type

■INDUCTANCE FREQUENCY CHARACTERISTICS GRAPH




Measurement equipment

Product No.	Manufacturer
E4991A+16192A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.

■ IMPEDANCE VS. FREQUENCY CHARACTERISTICS GRAPH



Measurement equipment


Product No.	Manufacturer
E4991A+16192A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.



MLZ2012-A type


■INDUCTANCE VS. DC BIAS CHARACTERISTICS GRAPH






MLZ2012-A type

SHAPE & DIMENSIONS




■ PACKAGING STYLE

REEL DIMENSIONS




Dimensions in mm

■ RECOMMENDED LAND PATTERN




TAPE DIMENSIONS



Dimensions in mm

Type	Α	В	K	
MLZ2012-A	1.5±0.2	2.3±0.2	1.5max.	

■ RECOMMENDED REFLOW PROFILE



160min. Taping 200min. Taping 200min. Drawing direction 300min.

Dimensions in mm

PACKAGE QUANTITY

Package quantity	2000 pcs/reel

■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range*	Storage temperature range**	Individual weight	
−55 to +125 °C	−55 to +125 °C	14 mg	

^{*} Operating temperature range includes self-temperature rise.

^{**} The storage temperature range is for after the assembly.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

REMINDERS ○ The storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. On not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.). Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C. Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur. When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions. O Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design. Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference. Use a wrist band to discharge static electricity in your body through the grounding wire. On not expose the products to magnets or magnetic fields. O Do not use for a purpose outside of the contents regulated in the delivery specifications. The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society,

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)

set forth in the each catalog, please contact us.

(3) Medical equipment

person or property.

- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions