

ES1A THRU ES1J

Super Fast Recovery Rectifier Diode

Features

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- High frequency
- High forward surge capability
- Meets MSL level 1, per J-STD-020,LF maximum peak of 260 °C



Typical Application

For use in high frequency rectification of power supply, inverters, converters, and freewheeling diodes for consumer and telecommunication.



Mechanical Data

- Package: DO-214AC(SMA)
Molding compound meets UL 94 V-0 flammability rating,RoHS-compliant
- Terminals: Tin plated leads, solderable per J-STD-002 and JESD22-B102
- Polarity: Cathode line denotes the cathode end

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	Symbol	Unit	Conditions	ES1				
				A	B	D	G	J
Repetitive Peak Reverse Voltage	V_{RRM}	V		50	100	200	400	600
Average Forward Current	I_o	A	Half-sine wave, Resistance load, Ta(Fig 1)	1.0				
Surge(Nonrepetitive)Forward Current	I_{FSM}	A	60HZ sine wave, 1 cycle, Ta=25°C	30				
Current Squared Time	I^2t	A ² s	1ms≤t<8.3ms Tj=25°C,Rating of per diode	3.7				
Thermal Resistance	$R_{\theta J-A}$	°C/W	Between junction and case	85				
Storage Temperature	T_{stg}	°C		-55 ~ +150				
Junction Temperature	T_j	°C		-55 ~ +150				

Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	Symbol	Unit	Conditions	ES1				
				A	B	D	G	J
Peak Forward Voltage	V_{FM}	V	$I_F = 1.0A$	0.95			1.3	1.7
Peak Reverse Current	I_{RRM1}	μA	$V_{RM} = V_{RRM}$	Ta=25°C				
	I_{RRM2}			Ta=125°C				
Maximum reverse recovery time	T_{rr}	ns	$I_F = 0.5A, I_R = 1.0A, I_{rr} = 0.25A$	35				



ES1A THRU ES1J

■ Characteristics (Typical)

FIG1: Forward Current Derating Curve




FIG2: Surge Forward Current Capability




FIG3: Instantaneous Forward Voltage




FIG4: Typical Reverse Characteristics





Diagram of circuit and Testing wave form of reverse recovery time



ES1A THRU ES1J

Ordering Information (Example)

PREFERED	PACKAGE CODE	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
ES1A-ES1J	DO-214AC(SMA)	5000	10000	80000	13" reel
ES1A-ES1J	DO-214AC(SMA)	7500	15000	120000	13" reel

Outline Dimensions

