

ES1A THRU ES1J

Super Fast Recovery Rectifier Diode

Features

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- High frequency
- High forward surge capability
- Meets MSL level 1, per J-STD-020,LF maximum peak of 260 °C



Typical Application

For use in high frequency rectification of power supply, inverters, converters, and freewheeling diodes for consumer and telecommunication.



Mechanical Data

- Package: DO-214AC(SMA)
 Molding compound meets UL 94 V-0 flammability rating,RoHS-compliant
- Terminals: Tin plated leads, solderable per J-STD-002 and JESD22-B102
- Polarity: Cathode line denotes the cathode end

■ Maximum Ratings (Ta=25°C Unless otherwise specified)

DARAMETER	Cumbal	Unit	Conditions	ES1					
PARAMETER	Symbol		Conditions	Α	В	D	G	J	
Repetitive Peak Reverse Voltage	VRRM	V		50	100	200	400	600	
Average Forward Current	lo	Α	Half-sine wave, Resistance load, Ta(Fig 1)	1.0					
Surge(Nonrepetitive)Forward Current	IFSM	Α	60HZ sine wave, 1 cycle, Ta=25℃	30					
Current Squared Time	I ² t	A ² s	1ms≤t<8.3ms Tj=25℃,Rating of per diode	3.7					
Thermal Resistance	R өJ-A	°C/W	Between junction and case	85					
Storage Temperature	Tstg	°C		-55 ~ + 150					
Junction Temperature	Tj	$^{\circ}$		-55 ~ +150					

Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	Symbol	Unit	Conditions		ES1					
FARAMETER	Syllibol				Α	В	D	G	J	
Peak Forward Voltage	VFM	V	IF=	1.0A 0.95				1.3	1.7	
Peak Reverse Current	IRRM1	μΑ	VRM=VRRM	Ta=25℃			5			
Peak Reverse Current	IRRM2			Ta=125℃	200					
Maximum reverse recovery time	Trr	ns	I _F =0.5A,I _R =1.0A,I _{rr} =0.25A		35					

Revised: 2021-11-29








ES1A THRU ES1J

■ Characteristics (Typical)






FIG3:Instantaneous Forward Voltage




FIG4:Typical Reverse Characteristics





Diagram of circuit and Testing wave form of reverse recovery time



Revised: 2021-11-29






ES1A THRU ES1J

■ Ordering Information (Example)

PREFERED	PACKAGE CODE	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE	
ES1A-ES1J	DO-214AC(SMA)	5000	10000	80000	13" reel	
ES1A-ES1J	DO-214AC(SMA)	7500	15000	120000	13" reel	

■ Outline Dimensions



Revised: 2021-11-29



