

**Revision: B** 



# Dongguan TLC Electronic Technology Co., LTD

No.18,5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710

0603 Fast Acting SMD

Fuses

DOC.NO.:

ISS:F06F0.75

TEL: 86-0769-3892 0511

FAX: 86-0769-8793 2077

Http: www.tlcet.com.cn

Rev.	Effective Date	Changed Contents	
A	2020-9-27	New Release	
В	2021-4-7	Update Spedfications	

The individual specification sheet are the property of Dongguan TLC electronic technology Co.,Ltd and shall not be copied or used as commercial purposes without permission.

PREPEARED BY	APPROVED BY
杨崎	ST BE



#### Description

F06F Series are the fuses set the industry standard for performance, reliability and quality. The solder-free design provides excellent on-off and temperature cycling characteristics during use and also makes our SMD fuses more heat and shock tolerant than typical subminiature fuses.

Electrical Characteristics				
Rated Current	1.0In	2.5In		
750mA	4 hour minimum	5 sec maximum		

#### Features

- > AEC-Q200 Automotive Grade Certified
- Compatible with reflow and wave solder
- Excellent environmental integrity
- One time positive disconnect
- Lead Free and Halogen free material

#### **Specifications**

Specification							
Part No.	Rated Voltage DC	Rated Current (A)	Breaking Capacity (A) <sup>1</sup>	Typical Cold. Resistance (mOhms) <sup>2</sup>	Typical Voltage Drop (mV)	Typical Pre- Arcing I <sup>2</sup> t (A <sup>2</sup> Sec) <sup>3</sup>	Alpha Mark
F06F0.25		0.250	50A	3250	893	0.00042	D
F06F0.375		0.375	50A	1800	587	0.00093	E
F06F0.5		0.500	50A	1070	582	0.001	F
F06F0.75		0.750	50A	470	427	0.009	G
F06F1		1	50A	250	335	0.011	В
F06F1.5		1.5	50A	150	270	0.045	H
F06F2		2	50A	78	160	0.115	K
F06F2.5	32V	2.5	50A	49	145	0.14	L
F06F3		3	50A	35	130	0.21	0
F06F3.5		3.5	50A	28	130	0.5	R
F06F4		4	50A	18	120	0.56	S
F06F5		5	50A	14	110	1.2	Т
F06F6		6	50A	11	110	1.7	V**
F06F7	] [	7	50A	9.5	80	2.3	X**
F06F8		8	50A	7	75	3.0	Z**

1. DC Interrupting Rating (Measured at rated voltage, time constant of less than 50 microseconds, battery source)


2. DC Cold Resistance are measured at <10% of rated current in ambient temperature of 25degrees

3. Typical Pre-arcing I<sup>2</sup>t are measured at 10In Current


\*\* For 1A-5A, the color of glass coating is Green; for others, it's Blue.

Specifications are subject to change without notice. Application testing is strongly recommended.

Dimension Drawing not to scale (Unit: mm/inch)




TLC Electronic





## **Recommended land pattern**




Unit: mm/inches

### Soldering method

- > Wave solder
  - Reservoir temperature: 260°C
  - Time in reservoir: 10 seconds maximum
- Infrared reflow
  - Temperature: 260°C
  - Time: 30 seconds maximum

## Solder reflow profile






Profile Feature	Lead(Pb) free solder	
Preheat and soak	eheat and soak • Temperature min.(T <sub>smin</sub> )	
	• Temperature max. (T <sub>smax</sub> )	200°C
	60 - 120 Seconds	
Average ramp up rate $T_{smax}$ to T	3°C / Second Max.	
Liquidous temperature $(T_L)$	217°C	
Time at liquidous (t <sub>L</sub> )	60 - 150 Seconds	
Peak package body temperatur	260°C	
Time ( $t_P$ ) within 5°C of the speci	30 Seconds	
Average ramp-down rate (TP to	6°C / Second Max.	
Time (25°C to Peak Temperatur	8 Minutes Max.	

### **Temperature Derating Curve**

# Normal ambient temperature: 23+/-3°C

Operating temperature: -55 ~ 125°C, with proper correction factor applied



#### Package

5000 fuses on 8mm tape-and-reel on a 7 inch (178mm) reel per EIA Standard 481.

--- End of Document ---