

KEMET Part Number: CKC21X123FDGACTU
(CKC21X123FDGAC7800)



KC Link Auto C0G, Ceramic, 0.012 uF, 1%, 1000 VDC, C0G, SMD, MLCC, FT-CAP, Ultra-Stable, 2220



| General Information | |
|---------------------|---------------------------------|
| Series: | KC Link Auto C0G |
| Style: | SMD Chip |
| Description: | SMD, MLCC, FT-CAP, Ultra-Stable |
| Features: | Ultra-Stable, Low Loss |
| RoHS: | Yes |
| Termination: | Flexible Termination |
| Marking: | No |
| AEC-Q200: | No |
| Shelf Life: | 78 Weeks |
| MSL: | 1 |

| Dimensions | |
|------------|-----------------|
| Chip Size | 2220 |
| L | 5.9mm +/-0.75mm |
| W | 5mm +/-0.4mm |
| T | 2.5mm +/-0.20mm |
| B | 0.7mm +/-0.35mm |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 500 |

| Specifications | |
|---|------------------------|
| Capacitance: | 0.012 uF |
| Measurement Condition: | 1 kHz 1.0Vrms |
| Capacitance Tolerance: | 1% |
| Voltage DC: | 1000 VDC |
| Dielectric Withstanding Voltage: | 1200 VDC |
| Temperature Range: | -55/+150°C |
| Temperature Coefficient: | C0G |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC): | 30 ppm/C, 1kHz 1.0Vrms |
| Dissipation Factor: | 0.1% 1 kHz 1.0Vrms |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 83.333 GOhms |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

