

**KEMET Part Number: CKC21X472MWGACTU**  
(CKC21X472MWGAC7800)



KC Link Auto C0G, Ceramic, 4700 pF, 20%, 650 VDC, C0G, SMD, MLCC, FT-CAP, Ultra-Stable, 2220



**Dimensions**

Chip Size		2220
<b>L</b>		6.1mm +/-0.75mm
<b>W</b>		5mm +/-0.4mm
<b>T</b>		1.6mm +/-0.20mm
<b>B</b>		0.7mm +/-0.35mm

**Packaging Specifications**

<b>Weight:</b>	190 mg
<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	1000

**General Information**

<b>Series:</b>	KC Link Auto C0G
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, FT-CAP, Ultra-Stable
<b>Features:</b>	FT-CAP, Ultra-Stable
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>Marking:</b>	No
<b>Qualifications:</b>	AEC-Q200
<b>AEC-Q200:</b>	Yes
<b>Shelf Life:</b>	78 Weeks
<b>MSL:</b>	1

**Specifications**

<b>Capacitance:</b>	4700 pF
<b>Measurement Condition:</b>	1 kHz 1.0Vrms
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	650 VDC
<b>Dielectric Withstanding Voltage:</b>	845 VDC
<b>Temperature Range:</b>	-55/+150°C
<b>Temperature Coefficient:</b>	C0G
<b>Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC):</b>	30 ppm/C, 1kHz 1.0Vrms
<b>Dissipation Factor:</b>	0.1% 1 kHz 1.0Vrms
<b>Aging Rate:</b>	0% Loss/Decade Hour
<b>Insulation Resistance:</b>	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

