

General Description

The AOZ8211 is a one-line transient voltage suppressor diode designed to protect voltage sensitive electronics from high transient conditions and ESD.

This device incorporates one TVS diode in an ultra-small DFN 1.0 mm x 0.6 mm package. During transient conditions, the one-line TVS diode directs the transient to ground. It may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (±15 kV air, ±8 kV contact discharge).

The AOZ8211 comes in an RoHS compliant package and is rated over a -40 °C to +85 °C ambient temperature range.

The ultra-small 1.0 mm x 0.6 mm x 0.5 mm DFN package makes the AOZ8211 ideal for applications where PCB space is at a premium. The small size and high ESD protection makes the AOZ8211 ideal for protecting voltage sensitive electronics from high transient conditions and ESD.

Features

ESD protection for high-speed data lines:

AOZ8211DI-02

- Exceeds: IEC 61000-4-2 (ESD) ±30 kV (air), ±30 kV (contact)
- Human Body Model (HBM) ±30 kV

AOZ8211DI-03

- Exceeds: IEC 61000-4-2 (ESD) ±30 kV (air), ±30 kV (contact)
- Human Body Model (HBM) ±30 kV

AOZ8211DI-05

- Exceeds: IEC 61000-4-2 (ESD) ±28 kV (air),±28 kV (contact)
- Human Body Model (HBM) ±30 kV

AOZ8211DI-12

- Exceeds: IEC 61000-4-2 (ESD) ±28 kV (air),±28 kV (contact)
- Human Body Model (HBM) ±30 kV

AOZ8211DI-24


- Exceeds: IEC 61000-4-2 (ESD) ±15 kV (air), ±18 kV (contact)
- Human Body Model (HBM) ±30 kV
- Small package saves board space
- Low insertion loss
- Low clamping voltage
- Low operating voltage: 2.5 V, 3.3 V, 5 V, 12 V and 24 V

Applications

- Portable handheld devices
- Keypads, data lines, buttons
- Notebook computers
- Digital cameras
- Portable GPS
- MP3 players



Typical Application



Unidirection Protection of Single Line

Pin Configuration

Cathode 2 O O 1 Anode



Ordering Information

Part Number	Ambient Temperature Range	Package	Environmental
AOZ8211DI-02			
AOZ8211DI-03			0 5 1 1
AOZ8211DI-05	-40 °C to +85 °C	DFN 1.0 x 0.6	Green Product RoHS Compliant
AOZ8211DI-12			Norte Compilant
AOZ8211DI-24			



AOS Green Products use reduced levels of Halogens, and are also RoHS compliant.

Please visit www.aosmd.com/media/AOSGreenPolicy.pdf for additional information.

Absolute Maximum Ratings

Exceeding the Absolute Maximum Ratings may damage the device.

Parameter	AOZ8211DI-02	AOZ8211DI-03	AOZ8211DI-05	AOZ8211DI-12	AOZ8211DI-24
Peak Pulse Current, t _P = 8/20 μs	6 A	6 A	5.5 A	5 A	2.5 A
Peak Pulse Power, t _P = 8/20 μs	50 W	55 W	50 W	100 W	110 W
Storage Temperature (T _S)	-65 °C to +150 °C				
ESD Rating per IEC61000-4-2, Contact ⁽¹⁾	±30 kV	±30 kV	±28 kV	±28 kV	±18 kV
ESD Rating per IEC61000-4-2, Air ⁽¹⁾	±30 kV	±30 kV	±28 kV	±28 kV	±15 kV
ESD Rating per Human Body Model ⁽²⁾	±30 kV				

Notes:

- 1. IEC 61000-4-2 discharge with C $_{Discharge}$ = 150pF, R $_{Discharge}$ = 330 $\Omega.$
- 2. Human Body Discharge per MIL-STD-883, Method 3015 $C_{Discharge}$ = 100 pF, $R_{Discharge}$ = 1.5 k Ω .

Maximum Operating Ratings

Parameter	Rating
Junction Temperature (T _J)	-40 °C to +85 °C

Rev. 3.0 October 2015 **www.aosmd.com** Page 2 of 7



Electrical Characteristics

T_A = 25 °C unless otherwise specified.

Symbol	Parameter	Diagram
I _{PP}	Maximum Reverse Peak Pulse Current	
V _{CL}	Clamping Voltage @ I _{PP}	
V _{RWM}	Working Peak Reverse Voltage	F
I _R	Maximum Reverse Leakage Current	
V _{BR}	Breakdown Voltage @ I _T	V _{CL} V _{BR} V _{RWM}
I _F	Forward Current	IR VF
V _F	Forward Voltage	
P _{PK}	Peak Power Dissipation	 PP
СЈ	Capacitance @ V _R = 0 and f = 1 MHz	'


Electrical Characteristics


 T_A = 25 °C unless otherwise noted, V_F = 0.9 V Max. @ I_F = 10 mA for all types.


	Device	V _{RWM} (V)	I _R (μΑ)	V _{BR} (V)	V- (V)		V _{CL} Max.			
Device	Marking	Max.	Max.	Min.		Typ.	I _{PP} = 1 A	I _{PP} = 5 A	I _{PP} = 12 A	C _J (pF) Typ.
AOZ8211DI-02	Q	2.5	0.1	2.8	2 μΑ	0.75	5.00	7.00	9.50	11
AOZ8211DI-03	G	3.3	0.1	3.7	2 μΑ	0.75	5.50	7.50	9.50	11
AOZ8211DI-05	J	5.0	0.1	6.0	1 mA	0.75	8.00	9.00	10.00	16
AOZ8211DI-12	K	12.0	0.1	14.0	1 mA	0.75	18.00	20.00	21.00	30
AOZ8211DI-24	М	24.0	0.1	27.0	1 mA	0.75	33.00	36.00	37.00	20




Typical Performance Characteristics














Package Dimensions, DFN 1.0 x 0.6, 2L





RECOMMENDED LAND PATTERN



Dimensions in millimeters

Symbols	Min.	Nom.	Max.				
Α	0.47	0.50	0.53				
A1	0.00	0.03	0.05				
b	0.45	0.50	0.55				
D	0.95	1.00	1.05				
E	0.55	0.60	0.65				
е		0.40					
L	0.20	0.25	0.30				
L1	0.0	5±0.03 F	Ref.				
R	0.05	0.10	0.15				
aaa		0.15	-				
bbb	0.05						
ccc		0.05					

Dimensions in inches


Symbols	Min.	Nom.	Max.							
Α	0.019	0.020	0.021							
A1	0.000	0.001	0.002							
b	0.018	0.020	0.022							
D	0.037	0.039	0.041							
E	0.022	0.024	0.026							
е		0.016								
L	0.008	0.010	0.012							
L1	0.00	2±0.001	Ref.							
R	0.002	0.006								
aaa	0.006									
bbb	0.002									
CCC	0.002									

Notes:


- 1. All dimensions are in milliteters. Angles are in degrees.
- 2. Coplanarity applies to the exposed heat sink slug as well as the terminals.




Tape and Reel Dimensions, DFN 1.0 x 0.6, 2L




Option	Package	A0	В0	K0	D0	D1	Е	E1	E2	P0	P1	P2	Т
А	DFN 1.0x0.6/ DFN 1.0x0.6A (8 mm)	0.69 ±0.05	1.19 ±0.05	0.66 ±0.05	0.40 ±0.05	1.50 ±0.10	8.00 +0.3/-0.1	1.75 ±0.10	3.50 ±0.05	2.00 ±0.05	4.00 ±0.10	2.00 ±0.05	0.23 ±0.02
В	DFN 1.0x0.6/ DFN 1.0x0.6A (8 mm)	0.65 ±0.04	1.05 ±0.04	0.61 ±0.04	0.40 ±0.05	1.50 ±0.10	8.00 +0.3/-0.1	1.75 ±0.10	3.50 ±0.05	2.00 ±0.10	4.00 ±0.10	2.00 ±0.05	0.20 ±0.05







Part Marking



LEGAL DISCLAIMER

Applications or uses as critical components in life support devices or systems are not authorized. AOS does not assume any liability arising out of such applications or uses of its products. AOS reserves the right to make changes to product specifications without notice. It is the responsibility of the customer to evaluate suitability of the product for their intended application. Customer shall comply with applicable legal requirements, including all applicable export control rules, regulations and limitations.

AOS' products are provided subject to AOS' terms and conditions of sale which are set forth at: http://www.aosmd.com/terms and conditions of sale

LIFE SUPPORT POLICY

ALPHA AND OMEGA SEMICONDUCTOR PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS.

As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.