



CMOS/ 1.8V to 3.3V/ 2.5×2.0mm



RoHS Compliant

Features

- Miniature ceramic package
2.5 (L) × 2.0 (W) × 0.7 (H) mm (Typ.)
- Highly reliable with seam welding
- CMOS output
- Supply voltage 1.8/ 2.5/ 3.3V
Wide operating voltage range 1.6 to 3.63V
- Low current consumption
- High output frequency 125MHz

Table 1

| Freq. Tol. Code | Tolerance | Operating Temperature Range (°C) | Note |
|-----------------|-----------|----------------------------------|--|
| 0 | ± 50 | -10 to +70 | Standard specifications |
| S | ± 30 | | |
| U | ± 25 | | |
| F | ± 100 | -40 to +85 | Please contact us for available frequencies. |
| G | ± 50 | | |
| 6 | ± 50 | -40 to +105 | |

How to Order

KC2520B 25.0000 C 1 □ E 00
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series
- ②Output Frequency
- ③Output Type (CMOS)
- ④Supply Voltage (1.8V, 2.5V, 3.3V Compatible)
- ⑤Frequency Tolerance (See Table 1)
- ⑥Symmetry/ INH Function (45/ 55%)
- ⑦Individual Specification (STD Specification is "00")

Packaging (Tape & Reel 2000 pcs./ reel)


Specifications

| Item | Symbol | Conditions | Specifications | | Unit | |
|---|--------------------|--|--|--------------------|------|--------------------|
| | | | Min. | Max. | | |
| Output Frequency Range | fo | | 1.5 | 125 | MHz | |
| Frequency Tolerance | f _{tol} | Initial tolerance, Operating temperature range, Rated power supply voltage change, Aging (1 year @25°C), Shock and vibration | Temp.: -40 to +85°C | -100 | +100 | × 10 ⁻⁶ |
| | | | Temp.: -10 to +70°C/ -40 to +85°C/ -40 to +105°C | -50 | +50 | |
| | | | Temp.: -10 to +70°C | -30 | +30 | |
| Storage Temperature Range | T _{stg} | | -55 | +125 | °C | |
| Operating Temperature Range | T _{use} | Standard Specifications | -10 | +70 | °C | |
| | | Extend (Option) | -40 | +85 | | |
| Max. Supply Voltage | — | 1.5 ≤ fo ≤ 80MHz | -0.6 | +6.0 | V | |
| | | 80 < fo ≤ 125MHz | -0.3 | +4.0 | | |
| Supply Voltage | V _{cc} | | +1.6 | +3.63 | V | |
| Current Consumption (Maximum Loaded/ 1.6 ≤ V _{cc} ≤ 2.0V) | I _{cc} | 1.5 ≤ fo ≤ 24MHz | — | 2.5 | mA | |
| | | 24 < fo ≤ 40MHz | — | 3.5 | | |
| | | 40 < fo ≤ 60MHz | — | 5.0 | | |
| | | 60 < fo ≤ 80MHz | — | 6.0 | | |
| | | 80 < fo ≤ 125MHz | — | 11.0 | | |
| Current Consumption (Maximum Loaded/ 2.0 < V _{cc} ≤ 2.8V) | I _{cc} | 1.5 ≤ fo ≤ 24MHz | — | 3.0 | mA | |
| | | 24 < fo ≤ 40MHz | — | 4.5 | | |
| | | 40 < fo ≤ 60MHz | — | 5.5 | | |
| | | 60 < fo ≤ 80MHz | — | 6.5 | | |
| | | 80 < fo ≤ 125MHz | — | 14.0 | | |
| Current Consumption (Maximum Loaded/ 2.8 < V _{cc} ≤ 3.63V) | I _{cc} | 1.5 ≤ fo ≤ 24MHz | — | 3.5 | mA | |
| | | 24 < fo ≤ 40MHz | — | 5.0 | | |
| | | 40 < fo ≤ 60MHz | — | 6.0 | | |
| | | 60 < fo ≤ 80MHz | — | 8.0 | | |
| Stand-by Current | I _{std} | | — | 10 | μA | |
| | | @50%V _{cc} | 45 | 55 | | |
| Symmetry | SYM | | 45 | 55 | % | |
| Rise/ Fall Time (10% V _{cc} to 90% V _{cc} Maximum Loaded) | Tr/ Tf | 1.6 ≤ V _{cc} ≤ 2.0V/ 1.5 < fo ≤ 80MHz | — | 6.5 | ns | |
| | | 2.0 < V _{cc} ≤ 2.8V/ 1.5 < fo ≤ 80MHz | — | 5.0 | | |
| | | 2.8 < V _{cc} ≤ 3.63V/ 1.5 < fo ≤ 80MHz | — | 4.5 | | |
| | | 1.6 ≤ V _{cc} ≤ 3.63V/ 80 < fo ≤ 125MHz | — | 4.0 | | |
| Low Level Output Voltage | V _{OL} | I _{OL} = 4mA | — | 10%V _{cc} | V | |
| High Level Output Voltage | V _{OH} | I _{OH} = -4mA | 90%V _{cc} | — | V | |
| Output Load | L _{CMOS} | CMOS Output | — | 15 | pF | |
| Low Level Input Voltage | V _{IL} | | — | 30%V _{cc} | V | |
| High Level Input Voltage | V _{IH} | | 70%V _{cc} | — | V | |
| Disable Time | t _{dis} | | — | 100 | ns | |
| Enable Time | t _{ena} | | — | 5 | ms | |
| Start-up Time | t _{str} | @Minimum operating voltage to be 0 sec. | — | 10 | ms | |
| 1 Sigma Jitter | J _{Sigma} | Measured with Wavcrest SIA-3000 | 1.5 ≤ fo ≤ 80MHz | — | 8 | ps |
| | | | 80 < fo ≤ 125MHz | — | 4 | |
| Peak to Peak Jitter | J _{PK-PK} | Measured with Wavcrest SIA-3000 | 1.5 ≤ fo ≤ 80MHz | — | 80 | ps |
| | | | 80 < fo ≤ 125MHz | — | 40 | |

Note: All electrical characteristics are defined at the maximum load and operating temperature range. Please contact us for inquiry about operating temperature range, available frequencies and other conditions.

Dimensions

(Unit: mm)



Recommended Land Pattern

(Unit: mm)

