


KEMET Part Number: T340C226K016AT7301 Not for New Design
(T340C226K016ATTR)



T340, Tantalum, MnO2 Tantalum, Commercial Grade, 22 uF, 10%, 16 VDC, Lead Spacing = 5mm



General Information	
Series:	T340
Dielectric:	MnO2 Tantalum
Style:	Radial Molded
Description:	Radial, Solid Tantalum, Molded
RoHS:	Yes
Termination:	Tin
AEC-Q200:	No
Construction:	Molded
Miscellaneous:	Includes Standoff Height of 0.38 +/- 0.13mm.
Notes:	Longest Lead Is Positive

Dimensions	
W	7.3mm MAX
H	10.5mm MAX
T	4.3mm MAX
S	5mm +/-0.5mm
LL	15mm +/-2mm
F	0.5mm +/-0.03mm

Specifications	
Capacitance:	22 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC (85C), 10 VDC (125C), 0.16 VDC (125C Reverse)
Temperature Range:	-55/+125°C
Dissipation Factor:	6%
Leakage Current:	4 uA

Packaging Specifications	
Packaging:	T&R, 305mm
Packaging Quantity:	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

