

AOZ8231A

One-line Bi-directional TVS Diode

General Description

The AOZ8231A is a one-line bi-directional transient voltage suppressor diode designed to protect voltage sensitive electronics from high transient conditions and ESD.

This device incorporates one TVS diode in an ultra-small DFN 1006 package. It may be used to meet the ESD immunity requirements of EC 61000-4-2, Level 4 (±15kV air, ±8kV contact discharge).

The AOZ8231A comes in a RoHS compliant, Halogen-Free DFN 1.0 mm x 0.6 mm package and is rated over a -40 °C to +85 °C ambient temperature range.

The ultra-small 1.0 mm x 0.6 mm x 0.5 mm DFN package makes it ideal for applications where PCB space is a premium. The small size and high ESD protection makes it ideal for protecting voltage sensitive electronics from high transient conditions and ESD.

Applications

- Portable handheld devices
- Keypads, data lines, buttons
- Notebook computers
- Digital Cameras
- Portable GPS
- MP3 players

Features

- ESD protection for high-speed data lines
 - AOZ8231ADI-02:
 - Exceeds: IEC 61000-4-2 (ESD) ± 30 kV (air),
 ± 30 kV (contact)
 - Human Body Model (HBM) ± 30 kV
 - IEC 61000-4-5 (Lightning) 6 A (8/20 μS)
 - IEC 61000-4-4 (EFT) 40 A

AOZ8231ADI-03:

- Exceeds: IEC 61000-4-2 (ESD) ± 30 kV (air),± 30 kV (contact)
- Human Body Model (HBM) ± 30 kV
- IEC 61000-4-5 (Lightning) 6 A (8/20 μS)
- IEC 61000-4-4 (EFT) 40 A

AOZ8231ADI-05:

- Exceeds: IEC 61000-4-2 (ESD) ± 30 kV (air), ±30 kV (contact)
- Human Body Model (HBM) ± 30 kV
- IEC 61000-4-5 (Lightning) 5 A (8/20 μS)
- IEC 61000-4-4 (EFT) 40 A

AOZ8231ADI-08:

- Exceeds: IEC 61000-4-2 (ESD) ± 30 kV (air),
 ± 30 kV (contact)
- Human Body Model (HBM) ± 30 kV
- IEC 61000-4-5 (Lightning) 5 A (8/20 μS)
- IEC 61000-4-4 (EFT) 40 A

AOZ8231ADI-12:

- Exceeds: IEC 61000-4-2 (ESD) ± 30 kV (air),
 ± 30 kV (contact)
- Human Body Model (HBM) ± 30 kV
- IEC 61000-4-5 (Lightning) 4 A (8/20 μS)
- IEC 61000-4-4 (EFT) 40 A

AOZ8231ADI-24:


- Exceeds: IEC 61000-4-2 (ESD) ± 18 kV (air),± 15 kV (contact)
- Human Body Model (HBM) ± 15 kV
- IEC 61000-4-5 (Lightning) 2.5 A (8/20 μS)
- IEC 61000-4-4 (EFT) 40 A
- Small package saves board space
- Low insertion loss
- Low clamping voltage
- Low operating voltage
- Pb-free device





Typical Application

Pin Configuration





Bidirection Protection of Single Line

Ordering Information

| Part Number | Ambient Temperature Range | Package | Environmental | |
|---------------|---------------------------|---------------|---------------|--|
| AOZ8231ADI-02 | | | | |
| AOZ8231ADI-03 | | | | |
| AOZ8231ADI-05 | -40 °C to +85 °C | DFN 1.0 x 0.6 | Green Product | |
| AOZ8231ADI-08 | | | Green Floudci | |
| AOZ8231ADI-12 | | | | |
| AOZ8231ADI-24 |] | | | |



AOS Green Products use reduced levels of Halogens, and are also RoHS compliant.

Please visit www.aosmd.com/media/AOSGreenPolicy.pdf for additional information.

Absolute Maximum Ratings

Exceeding the Absolute Maximum ratings may damage the device.

| | Rating for AOZ8231ADI | | | | | | | |
|---|-----------------------|---------|-----------|---------|---------|---------|--|--|
| Parameter | -02 | -03 | -05 | -08 | -12 | -24 | | |
| VP – VN | 2.5 V | 3.3 V | 5 V | 8 V | 12 V | 24 V | | |
| Peak Pulse Current, t _P = 8/20 µs | 6 A | 6 A | 5 A | 5 A | 4 A | 2.5 A | | |
| Storage Temperature (T _S) | | | -65 °C to | +150 °C | | | | |
| ESD Rating per IEC61000-4-2, Contact ⁽¹⁾ | ± 30 kV | ± 30 kV | ± 30 kV | ± 30 kV | ± 30 kV | ± 15 kV | | |
| ESD Rating per IEC61000-4-2, Air ⁽¹⁾ | ± 30 kV | ± 30 kV | ± 30 kV | ± 30 kV | ± 30 kV | ±18 kV | | |
| ESD Rating per Human Body Model ⁽²⁾ | ± 30 kV | ± 30 kV | ± 30 kV | ± 30 kV | ± 30 kV | ± 15 kV | | |

Notes:

- 1. IEC 61000-4-2 discharge with C_Discharge = 150 pF, R_Discharge = 330 $\Omega.$
- 2. Human Body Discharge per MIL-STD-883, Method 3015 $C_{Discharge}$ = 100 pF, $R_{Discharge}$ = 1.5 k Ω .

Maximum Operating Ratings


| Parameter | Rating |
|--|-------------------|
| Junction Temperature (T _J) | -40 °C to +125 °C |



Electrical Characteristics

T_A = 25 °C unless otherwise specified.

| Symbol | Parameter |
|------------------|---|
| I _{PP} | Reverse Peak Pulse Current, (t _{period} = 100 ns, t _r = 1 ns) |
| V _{CL} | Clamping Voltage @ I _{PP} |
| V _{RWM} | Working Peak Reverse Voltage |
| I _R | Maximum Reverse Leakage Current |
| V _{BR} | Breakdown Voltage |
| CJ | Capacitance @ V _R = 0 and f = 1 MHz |



| | Device | V _{RWM} (V) | V _{BR} (V) Min. @ | I _R (μΑ) | V _{CL} Max. ⁽³⁾ | | | | C _J (pF) ⁽³⁾ | | |
|---------------|---------|----------------------|-------------------------------|---------------------|-------------------------------------|-----------------------|------------------------|------|------------------------------------|------|--|
| Device | Marking | Max. | 1mA | Max. | I _{PP} = 1 A | I _{PP} = 5 A | I _{PP} = 12 A | Min. | Тур. | Max. | |
| AOZ8231ADI-02 | Р | 2.5 | 3.0 | 0.1 | 6.5 | 9.0 | 12.5 | 4.4 | 5.5 | 7.0 | |
| AOZ8231ADI-03 | D | 3.3 | 3.7 | 0.1 | 7.5 | 10.0 | 13.5 | 4.4 | 5.5 | 7.0 | |
| AOZ8231ADI-05 | E | 5.0 | 5.5 | 0.1 | 10.5 | 13.5 | 15.5 | 10.4 | 13.0 | 14.0 | |
| AOZ8231ADI-08 | Y | 8.0 | 9.5 | 0.1 | 15.0 | 18.0 | 22.5 | 19.0 | 23.0 | 27.0 | |
| AOZ8231ADI-12 | F | 12.0 | 13.0 | 0.1 | 20.0 | 23.0 | 26.0 | 10.4 | 13.0 | 14.0 | |
| AOZ8231ADI-24 | R | 24.0 | 27.0 | 0.1 | 35.0 | 38.0 | 39.0 | 9.6 | 12.0 | 15.0 | |

Note:


Rev. 4.0 August 2015 **www.aosmd.com** Page 3 of 7

^{3.} Guaranteed by design and characterization.




Typical Performance Characteristics

Clamping Voltage vs. Peak Pulse Current




Typical Variation of C_{IN} vs. V_{R}




Rev. 4.0 August 2015 www.aosmd.com Page 4 of 7



Package Dimensions, DFN 1.0 x 0.6



RECOMMENDED LAND PATTERN



Dimensions in millimeters

| Symbols | Min. | Nom. | Max. | | | | |
|---------|----------|----------|------|--|--|--|--|
| Α | 0.47 | 0.51 | 0.55 | | | | |
| A1 | 0.00 | 0.02 | 0.05 | | | | |
| b | 0.45 | 0.50 | 0.55 | | | | |
| D | 0.60 BSC | | | | | | |
| Е | 1.00 BSC | | | | | | |
| е | (| 0.65 BSC | | | | | |
| L | 0.20 | 0.25 | 0.30 | | | | |
| aaa | 0.05 | | | | | | |
| ccc | 0.03 | | | | | | |
| ddd | | 0.10 | | | | | |

Dimensions in inches

| Symbols | Min. | Nom. | Max. |
|---------|-------|-------|-------|
| Α | 0.019 | 0.020 | 0.022 |
| A1 | 0.000 | 0.001 | 0.002 |
| b | 0.018 | 0.020 | 0.022 |
| D | | 0.024 | |
| E | | 0.039 | |
| е | | 0.026 | |
| L | 0.008 | 0.010 | 0.012 |
| aaa | | 0.002 | |
| CCC | | 0.001 | |
| ddd | | 0.004 | |


Notes:

- 1. Dimensions and tolerancing conform to ASME Y14.5-2009.
- 2. All dimensions are in milliteters.
- **1** "e" represents the terminal grid pitch.
- 4. N isthe total number of terminals.
- A visual index feature must be located within the hatched area. Typical index feature (chamfer) must be located on the edge of the Pin#1 feature.
- This dimension includes stand-off height "A1" and packaged body thickness, but does not include attached feature e.g. external heatsink or chip capacitors, an internal heatslug is not considered as attached feature.
- ⚠ Dimension "A1" is primarily terminal plating, and does not include small metal protrusions.

Rev. 4.0 August 2015 www.aosmd.com Page 5 of 7




Tape and Reel Dimensions, DFN 1.0 x 0.6



| Option | Package | A0 | В0 | K0 | D0 | D1 | E | E1 | E2 | P0 | P1 | P2 | Т |
|--------|--|---------------|---------------|---------------|---------------|---------------|-------------------|---------------|---------------|---------------|---------------|---------------|---------------|
| А | DFN 1.0x0.6/ DFN 1.0x0.6A (8 mm) | 0.69 ±0.05 | 1.19 ±0.05 | 0.66 ±0.05 | 0.40 ±0.05 | 1.50 ±0.10 | 8.00 +0.3/-0.1 | 1.75 ±0.10 | 3.50 ±0.05 | 2.00 ±0.05 | 4.00 ±0.10 | 2.00 ±0.05 | 0.23 ±0.02 |
| В | DFN 1.0x0.6/ DFN 1.0x0.6A (8 mm) | 0.65 ±0.04 | 1.05 ±0.04 | 0.61 ±0.04 | 0.40 ±0.05 | 1.50 ±0.10 | 8.00 +0.3/-0.1 | 1.75 ±0.10 | 3.50 ±0.05 | 2.00 ±0.10 | 4.00 ±0.10 | 2.00 ±0.05 | 0.20 ±0.05 |






| Tape Size | Reel Size | М | N | w | W1 | Н | K | S | G | R | V |
|-----------|-----------|------|-----|---------|------|-------|------|------|-----|-----|-----|
| 8mm | ø178 | ø178 | ø55 | 8.4 | Max. | ø13.0 | Max. | 2.0 | N/A | N/A | N/A |
| | | ±0.5 | ±1 | +1.5/-0 | 14.4 | ±0.5 | 10.1 | ±0.5 | | | |

Leader / Trailer & Orientation






Rev. 4.0 August 2015 **www.aosmd.com** Page 6 of 7



Part Marking



LEGAL DISCLAIMER

Applications or uses as critical components in life support devices or systems are not authorized. AOS does not assume any liability arising out of such applications or uses of its products. AOS reserves the right to make changes to product specifications without notice. It is the responsibility of the customer to evaluate suitability of the product for their intended application. Customer shall comply with applicable legal requirements, including all applicable export control rules, regulations and limitations.

AOS' products are provided subject to AOS' terms and conditions of sale which are set forth at: http://www.aosmd.com/terms and conditions of sale

LIFE SUPPORT POLICY

ALPHA AND OMEGA SEMICONDUCTOR PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS.

As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Rev. 4.0 August 2015 www.aosmd.com Page 7 of 7