

Model 402W IoT Enhanced Quartz Crystal

Features

- Optimized Design for Low Plating Capacitance and ESR
- Improves Start-Up and Power Savings for Low Energy Applications
- Hermetic Ceramic Surface Mount Package
- Fundamental Crystal Design
- Frequency Range 16 52MHz
- Operating Temperature Range to -40°C to +125°C
- Tape and Reel Packaging, EIA-418

Standard Frequencies – see Page 5 for developed frequencies.

* Check with factory for availability of frequencies not listed.



- Wireless Communications
- Low Power MCUs, SoCs, RF ICs
- M2M Communications
- WiFi, ZigBee, ZigBee RF4CE, Z-Wave
- Bluetooth, Bluetooth Low Energy
- LoRa, LPWAN, 6LowPan, WLAN
- Near Field Communication

Part Dimensions:


2.0 × 1.6 × 0.55mm • 5.7002mg

- Low Drive Chipsets
- ISM Band Applications

Description

CTS Model 402W incorporates a high Q quartz resonator and has optimized design parameters for Low ESR and Load Capacitance [C_L]. M402W is ideal for supporting commercial and industrial **IoT** applications using low power MCUs, portable RF communication ICs and low drive chipsets.

Ordering Information



Notes.

- 1] Refer to document 016-1454-0, Frequency Code Tables. 3-digits for frequencies <100MHz.
- 2] Available with all stability codes.
- 3] Available with stability codes X, 2, Y, 3, 5 and 6.
- 4] Available with stability codes 3, 5 and 6.
- 5] Available with stability codes 5 and 6. Contact factory for availability

Not all performance combinations and frequencies may be available. Contact your local CTS Representative or CTS Customer Service for availability.

This product is specified for use only in standard commercial applications. Supplier disclaims all express and implied warranties and liability in connection with any use of this product in any non-commercial applications or in any application that may expose the product to conditions that are outside of the tolerances provided in its specification.



Electrical Specifications

Operating Conditions

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
			-20		+70	
			-30		+85	
Operating Temperature	T_A	-	-40	+25	+85	°C
			-40		+105	
			-40		+125	
Storage Temperature	T _{STG}	-	-55	-	+125	°C

Frequency Stability

PARAMETER SYMBO		CONDITIONS	MIN	TYP	MAX	UNIT
Frequency Range	f _O	-	16 - 52		MHz	
Frequency Tolerance	$\Delta f/f_O$	@ +25°C 10, 15, 20, 25 or 30			r 30	±ppm
Frequency Stability	Frequency Stability $\Delta f/f_{25}$		10, 15, 20, 25, 30, 50 or 100			±ppm
Aging	$\Delta f/f_0$	Typical per year @ +25°C	-3	±2	3	ppm

Crystal Parameters

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Operating Mode	-	-		Fundamenta		-
Crystal Cut	-	-		AT-Cut Strip		-
Load Capacitance	C_L	-	See O	rdering Inforr	nation	pF
Shunt Capacitance	C ₀	-	-	1.0	<3.0	pF
Series Resistance						
		16MHz - <18MHz	-	100	150	
		18MHz - <21MHz	-	80	100	0
Fundamental	R_1	21MHz - <30MHz	-	60	prmation <3.0	Ω
		30MHz - <38MHz	-	30	60	
		38MHz - 52MHz	-	25	50	
Drive Level	DL	-	-	10	100	μW
Insulation Resistance	R _i	+100Vdc ±15Vdc	500	-	-	МΩ


 $[\]Delta f/f_0$ - Frequency deviation referenced to nominal frequency.


 $[\]Delta f/f_{25}$ - Frequency deviation over operating temperature range, referenced to +25°C frequency.



Mechanical Specifications

Package Drawing






Marking Information

- 1. 402W CTS model.
- 2. D Date Code. See Table I for codes.
- 3. xxx Frequency Code, 3-digits for frequencies below 100MHz.

[See document 016-1454-0, Frequency Code Tables.]

Recommended Pad Layout



Notes

- 1. JEDEC termination code (e4). Barrier-plating is nickel [Ni] with gold [Au] flash plate.
- 2. Terminations #2, #4 and the metal lid are connected internally. End user may connect these pins to circuit ground for EMI suppression.
- Due to package variability, the pad chamfer on the bottom could be located on Pin 2 or 4 in a given lot. Layout orientation should be based on the top view [marking side], as indicated in package drawing. The chamfer location does not affect the electrical performance of the device.
- 4. Reflow conditions per JEDEC J-STD-020; +260°C maximum, 20 seconds.
- 5. MSL = 1.

Table I - Date Code, Beginning year 2021

		M	10NTH		LANI	CED	MAD	ADD	MAN	HIAI		AUG	CED	ост	NOV	DEC
	YEAR		JAN FEB			MAR APR N		MAY JUN		AUG	SEP	OCI NO		DEC		
2021	2025	2029	2033	2037	А	В	С	D	Е	F	G	Н	J	K	L	М
2022	2026	2030	2034	2038	N	Р	Q	R	S	Т	U	V	W	Χ	Υ	Z
2023	2027	2031	2035	2039	а	b	С	d	е	f	g	h	j	k	I	m
2024	2028	2032	2036	2040	n	р	q	r	S	t	u	٧	W	Х	У	Z


DOC# 008-0330-1 Rev. C

www.ctscorp.com


Page 3 of 5



Packaging - Tape and Reel



Reel Drawing



Notes

- 1. Device quantity is 1k pieces minimum and 3k pieces maximum per 180mm reel.
- 2. Complete CTS part number, frequency value, date code and manufacturing site code information must appear on reel and carton labels.





Addendum

Common Frequencies and Frequency Codes - MHz

Common Wireless Frequencies Additional Frequencies

Common wheless rrequencies		ess rrequencies Additional rrequencies							
FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE		
16.000000	160	16.367600	16E	26.041660	26F	39.062500	39A		
19.200000	192	16.384000	163	27.000000	270	41.600000	41C		
20.000000	200	16.666700	16N	28.224000	282	44.000000	440		
24.000000	240	16.800000	168	28.322000	28C	45.000000	450		
25.000000	250	16.934400	169	28.375000	283	49.152000	491		
26.000000	260	18.000000	180	28.636360	286	50.000000	500		
27.120000	271	18.432000	184	29.491200	29B	54.000000	540		
30.000000	300	19.440000	194	30.400000	304				
32.000000	320	19.660800	19B	30.720000	307				
37.400000	374	19.680000	196	31.250000	312				
38.400000	384	20.480000	204	32.768000	327				
40.000000	400	20.736000	207	33.000000	330				
48.000000	480	22.118400	221	33.330000	333				
52.000000	520	22.579200	225	33.333000	33E				
		24.305000	243	33.333300	33A				
		24.545400	24F	33.868800	338				
		24.545454	24G	35.328000	353				
		24.553500	24B	36.000000	360				
		24.576000	24C	38.000000	380				
		25.000625	25A	38.880000	388				