

A Product Line of Diodes Incorporated

Description



PI3A6386

# USB Type-C Ultra-Low-THD Audio and Data Switch Array


### **Features**

- → Support USB High Speed (480Mbps) and Full Speed (12Mbps) Signaling Capability per USB 2.0
- → USB switches: High bandwidth (1 GHz) & Low On-Resistance (5 ohm).
- → Audio switches: Low On-Resistance (1 ohm).
- ➔ Support USB Type-C Audio Accessory Mode per USB Type-C Cable and Connector Specification 1.1
- → Low Distortion (THD: -110dB from 20Hz to 20kHz, 2.0VRMS, 320hm load)
- → Negative Signal (+/-3V) Handling Capability
- ➔ Programmable soft-start and soft-stop time to eliminate click/pop sounds of DC-coupled audio signals
- → High Off Isolation: -85dB @ 30kHz
- → High Crosstalk Rejection: -85dB @ 30kHz
- $\rightarrow$  Autonomous microphone and ground lines Switching
- ➔ Separate Ground switches for microphone and audio to minimize crosstalk
- ➔ Sideband switches
- ➔ I2C control
- → Wide VDD Range: 1.7V to 5.5V
- → ESD: 4kV for HBM mode, 1kV for CDM mode
- → Extended Industrial Temperature Range: –40°C to 85°C
- → Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- → Halogen and Antimony Free. "Green" Device (Note 3)
- → Packaging (Pb-free & Green): TQFN-24 (3mm x 3mm)

# Applications

- ➔ Notebook, PC
- → Cell Phones, PDAs, MP3 Players
- → Portable Instrumentation

# **Pin Assignment**




PI3A6386 includes a dual, single-pole double throw (SPDT) switch for high speed USB signal and high quality audio signal. It can be used in USB Type-C D+/D- switching for USB signal in data mode and analog audio signal in audio accessory mode.

The audio path with negative signal handling capability has a very low THD of -110dB for high quality audio requirement. It also has a programmable soft-start/soft-stop feature to eliminate the click/pop sounds of DC-coupled audio signals. The data path has a high USB bandwidth of 1 GHz for USB High Speed signals.

PI3A6386 can also detect the microphone signals in SBU1 and SBU2, and automatically route them to the correct inputs of microphone amplifier. Separate switches for microphone negative input and audio signal ground can minimize the crosstalk & echo between audio output signals and microphone input signals. Sideband switches can be configured to route SBU1 and SBU2 for sideband usage.

# **Functional Block Diagram**



Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.</li>






PI3A6386

# **Pin Description**

Pin#	Name	Description		
1	ISBU2	Sideband 2		
2	MIC+	Microphone +		
3	MIC-	Microphone -		
4	ADLGND	Ground for Audio Signal L		
5	SBU1	SBU1 of USB receptacle		
7	ADRGND	Ground for Audio Signal R		
8	SBU2	SBU2 of USB receptacle		
10	USB+	USB Signal +		
11	USB-	USB Signal -		
13	ADL	Audio Signal L		
14	D-	D- pin of USB receptacle		
15	D+	D+ pin of USB receptacle		
16	ADR	Audio Signal R		
17	SSCAP	Slew Rate Control		
18	SDA	I2C Data Input /Output		
19	SCL	I2C Clock Input		
20	ADD	I2C Slave Address Select		
22	VDD	Power Supply		
23	ISBU1	Sideband 1		
9, 21, Thermal Pad	GND	Ground		
6, 12, 24	NC	No Connection		







# **Maximum Ratings**

Storage Temperature	65℃ to +150℃
Ambient Temperature with Power Applied	40°℃ to +85°℃
Supply Voltage V <sub>DD</sub>	0.5Vto +6V
Input Voltage of All I/O Pins (Except Audio Path)	
Input Voltage of Audio Path (D+/D-)	3.5V to +6V
Input Voltage of Audio Path (ADR/ADL)	3.5V to +3.5V
Continuous Current of Audio Switches	±150mA
Continuous Current of All Switches	±20mA
Peak Current of Audio Switches (pulsed at 50% duty	cycle) ±200mA
Peak Current of All Switches (pulsed at 50% duty cy	cle) ±30mA
ESD HBM mode	4kV
CDM mode	1kV

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Control input must be held HIGH or LOW; it must not float.

# **Recommended Operating Conditions**

Symbol	Parameter	Min.	Тур.	Max.	Unit
V <sub>DD</sub>	Supply Voltage	1.7	-	5.5	V
V <sub>IO</sub>	Input Voltage of All I/O Pins (Except ADR/ADL/D+/D-)	-0.3	-	5.5	V
V <sub>AUDIO</sub>	Input Voltage of Audio Path (ADR/ADL)	-3	-	3	V
V <sub>D+/-</sub>	Input Voltage of D+/D-	-3	-	5.5	V
T <sub>A</sub>	Operating Temperature	-40	25	85	°C

### **Electrical Characteristics**

 $(T_A = -40 \degree C \text{ to } 85 \degree C$ , unless otherwise noted. Typical values are at 3.3V Vdd and +25 °C.)

Parameter	Symbol	Te	Min.	Typ.	Max.	Unit	
ANALOG SWITCH (AD	ANALOG SWITCH (ADR, ADL)						
Analog Signal Range	V <sub>ADR/ADL-</sub> , V <sub>D+/D-</sub>			-3	-	3	v
On-Resistance	R <sub>ON</sub>	$V_{ADR/ADL} = -3V$	to +3V, ILoad=-100mA	-	1	-	Ω
On-Resistance Match Between Channels	$\Delta R_{ON}$			-	0.05	0.2	Ω
On-Resistance Flatness	R <sub>ONF</sub>	$V_{ADR/ADL} = -3V$	to +3V		0.005	0.025	Ω
ANALOG GROUND SW	ITCH (ADRG	ND, ADLGND)					
On-Resistance	R <sub>ON</sub>	VADRGND/AD 100mA	-	0.2	-	Ω	
AUDIO SWITCH DYNA	MIC CHARAC	CTERISTICS					
Turn-Off Time	t <sub>OFF</sub>	$V_{AUDIO+/-} = 3V, I$ SSCAP=float	$R_L = 32\Omega$		30		μs
Turn-On Time	t <sub>ON</sub>	$V_{AUDIO+/-} = 3V, I$ SSCAP=float	$V_{AUDIO+/-} = 3V, R_L = 32\Omega$ SSCAP=float				μs
Soft-Start Time	t <sub>START</sub>		SSCAP= $0.01 \text{uF}$ V <sub>NC</sub> = $0.1 \text{V}$ , 10% to 90%				ms
Soft-Stop Time	t <sub>STOP</sub>	SSCAP=0.01uF V <sub>NC</sub> = 0.1V, 90		5		ms	
Off-Isolation (AUDIO+/- to D+/D-)	O <sub>ISO</sub>	V <sub>BIAS</sub> =0V, V <sub>IN</sub> =0dBm (NOTE1)	30kHz	-	-85	-	dB
Channel-to-Channel Crosstalk (AUDIO+ to AUDIO-)	X <sub>TALKD</sub>	V <sub>BIAS</sub> =0V, V <sub>IN</sub> =0dBm (NOTE1)	30kHz	-	-85	-	dB



A Product Line of Diodes Incorporated



PI3A6386


Parameter	Symbol	Те	Min.	Тур.	Max.	Unit	
-3dB Bandwidth	f <sub>3dB</sub>	V <sub>BIAS</sub> =0V, V <sub>IN</sub> =	-	1000	-	MHz	
Total Harmonic			$z, R_{\rm I} = 32\Omega, V_{\rm IN} = 2.0V_{\rm RMS},$				
Distortion	THD+N	V <sub>BIAS</sub> =0V (NOTE		-	-110	-	dB
DATA SWITCH (USB+, USB-)							
Data Signal Range	V <sub>USB+/-</sub> , V <sub>D+/-</sub>			-0.3	-	5.5	V
On-Resistance	R <sub>ON</sub>	$V_{USB+/} = 0V, 0.4$	V I <sub>load</sub> =-8mA	-	5	-	Ω
On-Resistance Match					0.025	0.05	0
Between Channels	$\Delta R_{ON}$	$V_{USB+/-}=0V\sim 1V,$	Iload=-8mA	-	0.025	0.25	Ω
DATA SWITCH DYNAM	<b>IIC CHARAC</b>	TERISTICS		•			
Turn-Off Time	t <sub>OFF</sub>	$V_{USB+/-} = 3V, R_{L}$	$=50\Omega$		1		μs
Turn-On Time	t <sub>ON</sub>	$V_{USB+/-} = 3V, R_{L}$			30		μs
		V <sub>BIAS</sub> =0V,					•
Off-Isolation (USB+/- to $D + D$ )	$O_{ISO}$	V <sub>IN</sub> =0dBm	240MHz	-	-25	-	dB
D+/D-)		(NOTE1)					
Channel-to-Channel		$V_{BIAS}=0V,$					
Crosstalk (USB+ to	X <sub>TALKD</sub>	V <sub>IN</sub> =0dBm	240MHz	-	-25	-	dB
USB-)		(NOTE1)					
-3dB Bandwidth	f <sub>3dB</sub>	$V_{BIAS}=0V, V_{IN}=$	OdBm (NOTE1)	-	1	-	GHz
Switch on capacitance	Con	Vcc=3.3V, frequ	ency :240MHz		6		pF
MICROPHONE SWITC	HES (MIC+, M	IC-)					
Microphone Signal	V			-0.3		3.6	V
Range	$V_{ m MIC}$ +/ -			-0.5	-	5.0	v
MIC+, MIC- On-	р	$V = 0V t_0 t_0$	CV II and Sm A	_	5	-	Ω
Resistance	R <sub>ON</sub>	$v_{\rm MIC+} = 0 v to + 10$	$V_{MIC+} = 0V$ to +2.6V, ILoad=-8mA			-	52
MIC+ On-Resistance		$V_{\rm MIC+} = 0V$ to +2		0.01	0.1	Ω	
Flatness	R <sub>ONF</sub>				0.01	0.25	Ω
			$V_{MIC+} = 0V$ to +2.6V, VDD<2.5V			0.23	52
Off-Isolation (MIC+,	O <sub>ISO</sub>	$V_{BIAS}=0V, V_{IN}=0$		-	-85	-	dB
MIC- to SBU1/SBU2)	100	(NOTE1) 30kHz	2				
Channel-to-Channel	N/	$V_{BIAS}=0V, V_{IN}=0$	0dBm		05		ID
Crosstalk (MIC+ to	$X_{TALKD}$	(NOTE1) 30kHz		-	-85	-	dB
MIC-)		£ 2011- to 201-11	- D = (000 V - 0.1V)				
Total Harmonic Distortion	THD+N		$z, R_L = 600\Omega, V_{IN} = 0.1V_{RMS},$	-	-90	-	dB
		V <sub>BIAS</sub> =2V (NOTE	51)				
SIDEBAND SWITCH (IS	, , , , , , , , , , , , , , , , , , , ,	VICDI1/2_0V	3.6V, ILoad=-8mA	_	5	-	0
On-Resistance -3dB Bandwidth	R <sub>ON</sub>			-	100	-	Ω MHz
	$f_{3dB}$	$V_{BIAS}=0V, V_{IN}=0$		-	100	-	MITZ
I2C INPUT (SCL, SDA)				0.7VD			
Input Logic High	$V_{\mathrm{IH}}$			D./VD			
						0.25V	
Input Logic Low	V <sub>IL</sub>					0.23 V DD	
SCL Frequency	f		0		1	MHz	
SCL Frequency SCL Input capacitance	f <sub>SCL</sub> C <sub>i</sub>	V <sub>I</sub> =GND	-	5	10	pF	
SDA Low level Output	$C_i$		1	5	10	pr.	
Current	I <sub>OL</sub>	$V_{OL}=0.4V$	20	-	-	mA	
CURRENT CONSUMPTION							
Operating Current	ICIN			-	100	250	μA
Shutdown Current	I <sub>CC</sub> I <sub>SD</sub>	+			100	1	μΑ μΑ
MICROPHONE DETEC						1	μΛ
Valid Headphone	R <sub>LR</sub>	TRRS connector	16	-	64-	Ω	
Impedance	R <sub>LR</sub>	TRS connector	16	-		Ω	
Valid Microphone					-	-	
Impedance	R <sub>MIC</sub>	TRRS connector	•	600	-	-	Ω
Impedance	1						

Note 1: These parameters are measured on TA=25 °C





# **Typical Application Circuit**



# **Function Description**

The PI3A6386 is a completed switch array to route the USB/AUDIO/Sideband signals between a Type-C receptacle and internal USB PHY/audio amplifier/microphone amplifier and other sideband circuits. It also includes the automatic microphone detection to detect the various configurations/orientations. It operates from a 1.8V to 5.5V supply and is controlled through I2C.

During Audio Accessory Mode, the PI3A6386 includes a pair of ultra-low THD, low on-resistance audio switches for highperformance audio applications to route the D+/D- to audio amplifier. The Beyond-the-Rails signal capability allows signals below ground and above Vdd to pass without distortion. Soft start/stop feature can minimize the click-and-pop sound due to the offset voltage of the audio amplifier. An automatic microphone detection can detect the configurations of the microphone and route SBU1/2 to the microphone amplifier and ground correspondingly. Separate grounds for microphone, audio L and audio R signals are provided to minimize the crosstalk/echo between them.

During DFP/UFP mode, the PI3A6386 has a pair of high bandwidth data switches to route D+/D- to USB PHY for USB 2.0 (High Speed and Full Speed) applications. Sideband crossbar switch is also provided to swap SBU1/2 based on the orientation of the Type-C plug.

When a device is attached to the USB Type-C port, the Type-C port controller can determine whether it is a DFP/UFP device or an audio accessory. In case of an audio accessory, the system controller will tell PI3A6386 to initialize the detection of the microphone connections through Bit 3 of the control register. After the detection is completed and the results are reported in Bit 2-0 of the





information register. The system controller can then enable the switch array and route the audio signals to the audio accessory with Bit 6,5,2,1 of the control register. In case of a DFP/UFP device, the system controller can directly enable the switch array and route the USB signals to the USB PHY, and route the Sideband signal to the internal circuits with Bit 6, 5, 4, 2, 1 of the control register.

# I2C Control

The PI3A6386 provides the I2C interface to control the connections of Audio/Data mux, Sideband/Microphone mux, Sideband crossbar switch and report how Mic+/Mic- connected to SBU1/SBU2. Max 2 I2C slave addresses can be configured by connecting ADD to VDD/GND.

### a. Device address

Table 1: Device address

	b7(MSB)	b6	b5	b4	b3	b2	b1	b0
Address Byte (ADDR = 0)	1	0	0	0	0	0	1	R/W
Address Byte (ADDR = 1)	1	0	0	1	0	0	1	R/W

Note: Read "1", Write "0"

#### **b.** Registers

#### **Command byte**

The command byte is the first byte to follow the address byte during a write transmission. It is used as a pointer to determine which of the following registers will be written or read.

#### Table 2: Command byte

Command	Register
0	Information register
1	Control register

#### **Register 0: Information register**

Table 3: Information register

	b7(MSB)-b3	b2	b1	b0
Name	Reserved	Mic detection Success	Mic present	Mic+/Mic- Connection
Description		1 : detection not successful 0 : detection successful ( only valid if Register 1 b1=1 )	1 : Mic not present 0 : Mic present ( only valid if Register 1 b1=1 )	1 : Mic+/Mic- connected to SBU1/SBU2 0 : Mic+/Mic- connected to SBU2/SBU1 ( only valid if Register 1 b1=1)
Туре	R	R	R	R
Default	1	1	1	1





### **Register 1: Control register**

Table 4: Control register

	b7(MSB)	b6	b5	b4	b3	b2	b1	b0
Name	Enable	USB/	Mic/Sideband	Sideband	Detection	USB/	Mic/Sideb	Reser
		AUDIO	Mux	Mux		AUDIO	and Mux	ved
		Mux				Mux	Connectio	
						Connect	n	
						ion		
Description	0 : IC	0 : D+/D-	0: SBU1/SBU2	0 : SBU1/SBU2	0 : Start Mic	0:	0: Closed	
	disabled	connected to	connected to	connected to	detection	Closed	1: Opened	
	and all	ADR/ARL	Mic+/Mic-,	ISBU2/ISBU1	(After the mic	1:		
	switches	1: D+/D-	ADLGND,	1: SBU1/SBU2	detection cycle,	Opened		
	disconnect	connected to	ADRGND or	connected to	b3 will be reset to			
	ed	USB+/USB-	Mic-, ADLGND,	ISBU1/ISBU2	1.)			
	1: IC	( only valid if	ADRGND /Mic+	( only valid if	1 : Stop Mic			
	enabled	Register 1 b2	1: SBU1/SBU2	Register 1 b1=0	detection/Detectio			
		= 0)	connected to	& b5 = 1)	n stop			
			ISBU1/ISBU2		(During mic			
			( only valid if		detection cycle,			
			Register 1 b1 = 0)		writing 1 to b3			
					can force mic			
					detection stop)			
Туре	R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W
Default	1	1	1	1	1	0	1	1

### **Part Marking**


Top mark not available at this time. To obtain advance information regarding the top mark, please contact your local sales representative.





# **Packaging Mechanical:**

TQFN-24 (ZL)



#### For latest package info.

please check: http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/

#### Ordering Information

Part Number	Package Code	Package
PI3A6386ZLEX	ZL	24-Contact, Very Thin Quad Flat No-Lead (TQFN)
Notes:		

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See http://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Thermal characteristics can be found on the company web site at www.diodes.com/design/support/packaging/

- 4. E = Pb-free and Green
- 5. X suffix = Tape/Reel





PI3A6386

#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the

failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated www.diodes.com