TOSHIBA Photocoupler IRED & Photo-MOSFET

TLP176D

Modem · Fax Card PBX

Telecommunication

The TOSHIBA TLP176D consists of an infrared emitting diode optically coupled to a photo-MOSFET in a SOP, which is suitable for surface mount assembly.


- SOP 4 pin (2.54SOP4): 1-form-A
- Peak off-state voltage: 200 V (min)
- Trigger LED current: 3 mA (max)
- On-state current: 200 mA (max)
- On-state resistance: 8 Ω (max)
- Isolation voltage: 1500 Vrms (min)
- UL-recognized: UL 1577, File No.E67349
- cUL-recognized: CSA Component Acceptance Service No.5A

File No.E67349

VDE-approved: EN 60747-5-5 (Note 1)


Note 1: When a VDE approved type is needed, please designate the **Option(V4)**.

Pin Configuration (top view)




- 1: Anode
- 2: Cathode
- 3: Drain
- 4: Drain

Internal Circuit



Unit: mm



Weight: 0.1 g (typ.)

Start of commercial production 1998-03

Absolute Maximum Ratings (Ta = 25°C)

	Characteristics	Symbol	Rating	Unit
	Forward current	lF	50	mA
	Forward current derating (Ta ≥ 25°C)	ΔI _F /°C	-0.5	mA/°C
	Pulse forward current (100 μs pulse, 100 pps)	IFP	1	А
LED	Reverse voltage	VR	5	V
	Diode power dissipation	PD	50	mW
	Diode power dissipation derating (Ta ≥25°C)	ΔP _D /°C	-0.5	mW/°C
	Junction temperature	Tj	125	°C
	Off-state output terminal voltage	Voff	200	V
	On-state current	Ion	200	mA
Detector	On-state RMS current derating (Ta ≥ 25°C)	ΔI _{ON} /°C	-2.0	mA/°C
Detector	Output power dissipation	Po	180	mW
	Output power dissipation derating (Ta ≥ 25°C)	ΔP _O /°C	-1.8	mW / °C
	Junction temperature	Tj	125	°C
Storage te	mperature range	T _{stg}	T _{stg} –55 to 125	
Operating	temperature range	Topr	T _{opr} -40 to 85	
Lead solde	ring temperature (10 s)	T _{sol}	T _{sol} 260	
Isolation vo	oltage (AC, 60 s, R.H. ≤ 60 %) (Note1)	BVs	1500	Vrms

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note1: Device considered a two-terminal device: pins1 and 2 shorted together and pins 3 and 4 shorted together.

Recommended Operating Conditions

Characteristics	Symbol	Min	Тур.	Max	Unit
Supply voltage	V_{DD}	_	150	200	V
Forward current	lF	5	7.5	25	mA
On-state current	Ion	_	_	130	mA
Operating temperature	T _{opr}	-20	_	65	°C

Note: Recommended operating conditions are given as a design guideline to obtain expected performance of the device. Additionally, each item is an independent guideline respectively. In developing designs using this product, please confirm specified characteristics shown in this document.

Individual Electrical Characteristics (Ta = 25°C)

Characteristics		Symbol	Test Condition	Min	Тур.	Max	Unit
LED	Forward voltage	VF	I _F = 10 mA	1.0	1.15	1.3	V
	Reverse current	IR	V _R = 5 V	_	_	10	μА
	Capacitance between terminals	Ст	VF = 0 V, f = 1 MHz	_	30	_	pF
Detector	Off-state current	loff	V _{OFF} = 200 V	_	_	1	μА
	Capacitance between terminals	COFF	V = 0 V, f = 1 MHz	_	100	-	pF

Coupled Electrical Characteristics (Ta = 25°C)

Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Trigger LED current	lfT	ION = 200 mA	_	1	3	mA
On-state resistance	Ron	$I_{ON} = 200 \text{ mA}, I_F = 5 \text{ mA}$	_	5	8	Ω
Return LED current	IFC	IOFF = 100 μA	0.1	_	_	mA


Isolation Characteristics (Ta = 25°C)


Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Capacitance input to output	Cs	V _S = 0 V, f = 1 MHz	_	0.8	_	pF
Isolation resistance	Rs	V _S = 500 V, R.H. ≤ 60 %	5 × 10 ¹⁰	10 ¹⁴	_	Ω
Isolation voltage	BVs	AC, 60 s	1500	_	_	Vrms


Switching Characteristics (Ta = 25°C)


Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Turn-on time	ton	$ \begin{array}{l} R_L = 200~\Omega \\ V_{DD} = 20~V,~I_F = 5~mA \end{array} \tag{Note} $	_	0.6	1.5	ms
Turn-off time	tOFF	$ \begin{array}{l} \text{RL} = 200 \; \Omega \\ \text{V}_{\text{DD}} = 20 \; \text{V}, \; \text{IF} = 5 \; \text{mA} \end{array} $	_	0.1	1.0	ms


Note: Switching time test circuit























NOTE: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.







NOTE: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE
 EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH
 MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT
 ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without
 limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical
 equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to
 control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE
 PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your
 TOSHIBA sales representative or contact us via our website.
- · Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE
 FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY
 WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR
 LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND
 LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO
 SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS
 FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor. Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of
 Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled
 substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES
 OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

https://toshiba.semicon-storage.com/