

DATA SHEET

SURGE CHIP RESISTORS

SR series
20%, 10%, 5%
sizes 0402/0603/0805/1206/1210/1218/2010/2512
RoHS compliant & Halogen free



SCOPE

This specification describes SR0402 to SR2512 chip resistors with lead-free terminations made by thick film process.

APPLICATIONS

- Telecommunications
- Power supplies
- Car electronics

FEATURES

- AEC-Q200 qualified
- Superior to SR series in pulse withstanding voltage and surge withstanding voltage.
- MSL class: MSL I
- Halogen free epoxy
- RoHS compliant
 - Products with lead-free terminations meet RoHS requirements
 - Pb-glass contained in electrodes, resistor element and glass are exempted by RoHS
- Reduce environmentally hazardous waste
- High component and equipment reliability

ORDERING INFORMATION - GLOBAL PART NUMBER

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

SR XXXX X X X XX XXXX L
 (1) (2) (3) (4) (5) (6) (7)

(1) SIZE

0402 / 0603 / 0805 / 1206 / 1210 / 1218 / 2010 / 2512

(2) TOLERANCE

J = $\pm 5\%$
 K = $\pm 10\%$
 M = $\pm 20\%$

(3) PACKAGING TYPE

R = Paper taping reel K = Embossed taping reel

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

– = Based on spec.

(5) TAPING REEL & POWER

07 = 7 inch dia. Reel 7W = 7 inch dia. Reel & 2 x standard power
 13 = 13 inch dia. Reel 7T = 7 inch dia. Reel & 3 x standard power
 47 = 7 inch dia. Reel & 4xstandard power

(6) RESISTANCE VALUE

1 $\Omega \leq R \leq 1M \Omega$
 There are 2~4 digits indicated the resistance value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. 1K2, not 1K20.
 Detailed coding rules of resistance are shown in the table of "Resistance rule of global part number".

(7) DEFAULT CODE

Letter L is the system default code for ordering only. (Note)

| Resistance coding rule | Example |
|----------------------------------|---|
| XXXX (1 to 9.76 Ω) | 1R = 1 Ω 1R5 = 1.5 Ω 9R76 = 9.76 Ω |
| XXRX (10 to 97.6 Ω) | 10R = 10 Ω 97R6 = 97.6 Ω |
| XXXR (100 to 976 Ω) | 100R = 100 Ω |
| XKXX (1 to 9.76 K Ω) | 1K = 1,000 Ω 9K76 = 9760 Ω |
| XXKX (10 to 97.6 K Ω) | 10K = 10,000 Ω 97K6 = 976,000 Ω |
| XXXXK (100 K Ω) | 100K = 100,000 Ω |

ORDERING EXAMPLE

The ordering code for an SR0805 chip resistor, value 10 K Ω with $\pm 5\%$ tolerance, supplied in 7-inch tape reel is: SR0805JR-0710KL.

MARKING

SR0402



No Marking

Fig. 1

SR1218



E-24 series: 3 digits
First two digits for significant figure and 3rd digit for number of zeros

Fig. 2 Value=10 KΩ

SR0603 / SR0805 / SR1206 / SR1210 / SR2010 / SR2512



E-24 series: 3 digits
First two digits for significant figure and 3rd digit for number of zeros

Fig. 3 Value=10 KΩ

NOTE

For further marking information, please refer to data sheet “Chip resistors marking”.

TAPING REEL & POWER

Table 1

| TYPE | POWER, W (P70) | | | |
|------|----------------|------|-----|-----|
| | CODING | | | |
| | 07 | 7W | 7T | 47 |
| 0402 | 1/16 | 1/8 | 1/5 | - |
| 0603 | 1/10 | 1/5 | 1/4 | - |
| 0805 | 1/8 | 1/4 | 1/3 | 1/2 |
| 1206 | 1/4 | 1/2 | 3/4 | 1 |
| 1210 | 1/2 | 1 | - | - |
| 1218 | 1 | 1.5 | - | - |
| 2010 | 3/4 | 1.25 | - | - |
| 2512 | 1 | 2 | - | - |

CONSTRUCTION

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive glaze. The resistive glaze is covered by a lead-free glass. The composition of the glaze is adjusted to give the approximately required resistance value. The whole element is covered by a protective overcoat. The top of overcoat is marked with the resistance value. Finally, the two external terminations (Ni/matte tin) are added, as shown in Fig.4.

OUTLINES



Fig. 4 Chip resistor outlines


Chip Resistor Surface Mount

SR SERIES **0402/0603/0805/1206/1210/1218/2010/2512**

DIMENSIONS

Table 2

| TYPE | L (mm) | W (mm) | H (mm) | I ₁ (mm) | I ₂ (mm) |
|--------|-----------|-----------|-----------|---------------------|---------------------|
| SR0402 | 1.00±0.05 | 0.50±0.05 | 0.35±0.05 | 0.20±0.10 | 0.25±0.10 |
| SR0603 | 1.60±0.10 | 0.80±0.10 | 0.45±0.10 | 0.25±0.15 | 0.25±0.15 |
| SR0805 | 2.00±0.10 | 1.25±0.10 | 0.50±0.10 | 0.35±0.20 | 0.35±0.20 |
| SR1206 | 3.10±0.10 | 1.60±0.10 | 0.55±0.10 | 0.45±0.20 | 0.40±0.20 |
| SR1210 | 3.10±0.10 | 2.60±0.15 | 0.55±0.10 | 0.45±0.15 | 0.50±0.20 |
| SR1218 | 3.10±0.10 | 4.60±0.10 | 0.55±0.10 | 0.45±0.20 | 0.40±0.20 |
| SR2010 | 5.00±0.10 | 2.50±0.15 | 0.55±0.10 | 0.55±0.15 | 0.50±0.20 |
| SR2512 | 6.35±0.10 | 3.10±0.15 | 0.55±0.10 | 0.60±0.20 | 0.50±0.20 |



ELECTRICAL CHARACTERISTICS

Table 3

| TYPE | POWER | RESISTANCE RANGE | CHARACTERISTICS | | | | |
|--------|-------|------------------------------------|-----------------------------|----------------------|-----------------------|---------------------------------|---------------------------------------|
| | | | Operating Temperature Range | Max. Working Voltage | Max. Overload Voltage | Dielectric Withstanding Voltage | Temperature Coefficient of Resistance |
| SR0402 | 1/16W | E24 5%, 10%, 20% 1 Ω ≤ R ≤ 1M Ω | -55 °C to +155 °C | 50 V | 100 V | 100 V | 10 Ω < R ≤ 1M Ω ±100 ppm/°C |
| | 1/8W | | | | | | |
| | 1/5W | | | | | | |
| SR0603 | 1/10W | | | 75V | 150V | 150V | |
| | 1/5W | | | | | | |
| | 1/4W | | | | | | |
| SR0805 | 1/8 W | | | 150V | 300V | 300V | |
| | 1/4W | | | | | | |
| | 1/3W | | | | | | |
| SR1206 | 1/2W | | | 200 V | 400 V | 500 V | |
| | 1/4 W | | | | | | |
| | 1/2W | | | | | | |
| | 3/4W | | | | | | |
| SR1210 | 1W | 200 V | 400 V | 500 V | | | |
| | 1/2W | | | | | | |
| SR1218 | 1W | 200 V | 400 V | 500 V | | | |
| | 1.5W | | | | | | |
| SR2010 | 3/4W | 200 V | 400 V | 500 V | | | |
| | 1.25W | | | | | | |
| SR2512 | 1 W | 200 V | 400 V | 500 V | | | |
| | 2W | | | | | | |

FOOTPRINT AND SOLDERING PROFILES

Recommended footprint and soldering profiles, please refer to data sheet “Chip resistors mounting”.

PACKING STYLE AND PACKAGING QUANTITY

Table 4 Packing style and packaging quantity

| PACKING STYLE | REEL DIMENSION | SR0402 | SR0603/0805/1206 | SR1210 | SR1218/2010/2512 |
|--------------------------|----------------|--------|------------------|--------|------------------|
| Paper taping reel (R) | 7" (178 mm) | 10,000 | 5,000 | 5,000 | --- |
| | 13" (330 mm) | 50,000 | 20,000 | 20,000 | --- |
| Embossed taping reel (K) | 7" (178 mm) | --- | --- | --- | 4,000 |

NOTE

I. For paper/embossed tape and reel specification/dimensions, please refer to data sheet “Chip resistors packing”.

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

Range: -55 °C to +155 °C

POWER RATING

Each type rated power at 70 °C:

SR0402: 1/16W, 1/8W, 1/5W

SR0603: 1/10W, 1/5W, 1/4W

SR0805: 1/8W, 1/4W, 1/3W, 1/2W

SR1206: 1/4W, 1/2W, 3/4W, 1W

SR1210: 1/2W, 1W

SR1218: 1W, 1.5W

SR2010: 3/4W, 1.25W

SR2512: 1W, 2W

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$

Where

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

R = Resistance value (Ω)



PULSE LOAD BEHAVIOR



Fig. 7 Pulse-Load behavior

TESTS AND REQUIREMENTS

Table 5 Test condition, procedure and requirements

| TEST | TEST METHOD | PROCEDURE | REQUIREMENTS |
|--|------------------------|--|------------------|
| Temperature Coefficient of Resistance (T.C.R.) | MIL-STD-202 Method 304 | At +25/-55 °C and +25/+125 °C Formula: $T.C.R = \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$ Where t ₁ = +25 °C or specified room temperature t ₂ = -55 °C or +125 °C test temperature R ₁ = resistance at reference temperature in ohms R ₂ = resistance at test temperature in ohms | Refer to table 2 |
| Short Time Overload | IEC60115-1 4.13 | 2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature | ±(2.0%+0.05 Ω) |
| High Temperature Exposure | IEC 60068-2-2 | 1,000 hours at T _A = 155 °C ±5 °C, unpowered | ±(3.0%+0.05 Ω) |
| Humidity | IEC 60115-1 4.24.2 | Steady state for 1,000 hours at 40 °C / 95% R.H. RCWW applied for 1.5 hours on and 0.5 hour off | ±(3.0%+0.05 Ω) |

| TEST | TEST METHOD | PROCEDURE | REQUIREMENTS |
|------------------------------|--|--|---|
| Life | IEC 60115-1 4.25.1 MIL-STD-202 Method 108 | 1,000 hours at 70±2 °C, RCWV applied for 1.5 hours on, 0.5 hour off, still-air required | ±(3.0%+0.05 Ω) |
| Resistance to Soldering Heat | IEC 60115-1 4.18 MIL-STD- 202 Method 210 | Condition B, no pre-heat of samples Lead-free solder, 260±5 °C, 10±1 seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol | ±(1.0%+0.05 Ω) No visible damage |
| Temperature Cycling | JESD22-A104C | -55/+125 °C for 1 cycle per hour, with 1,000 cycles. Devices mounted | ±(1.0%+0.05 Ω) |
| Solderability - Wetting | J-STD-002 | Electrical Test not required Magnification 50X SMD conditions: Immerse the specimen into the solder pot at 245±3°C for 2±0.5 seconds. | Well tinned (≥95% covered) No visible damage |
| Board Flex | IEC 60115-1 4.33 | Chips mounted on a 90mm glass epoxy resin PCB (FR4) Bending for 0402: 5mm 0603 & 0805: 3mm 1206 and above: 2mm Holding time: minimum 60 seconds | ±(1.0%+0.05 Ω) |

REVISION HISTORY

| REVISION | DATE | CHANGE NOTIFICATION | DESCRIPTION |
|-----------|---------------|---------------------|---|
| Version 8 | Jul. 22, 2019 | - | - Update power rating |
| Version 7 | Sep. 27, 2018 | - | - Extend resistance range of 0402 ~ 2512 to 1Mohm, - Tighten TCR of all sizes for $10\Omega < R \leq 1M\Omega$ from ± 200 ppm/°C to ± 100 ppm/°C - Add SR1210, SR1218, SR2010 7W (double power) |
| Version 6 | Oct. 02, 2017 | - | - Add SR0402 7T (triple power), SR0805 47 (quadruple power), SR2512 7W (double power) |
| Version 5 | Nov.11, 2016 | - | - Update 7T power for 1206 |
| Version 4 | Sep. 01, 2015 | - | - Update SR0603 Dielectric Withstanding Voltage to 150V - Update 7T power for 0603/0805 & 7W for 1210 |
| Version 3 | Jul. 31, 2015 | - | - Comply with AEC-Q200 standard |
| Version 2 | Jan. 06, 2014 | - | - Add SR0402/0603/1210 - Update electrical characteristic |
| Version 1 | Mar 18, 2011 | - | - Change to dual brand datasheet that describes SR0805 to SR2512 with RoHS compliant - Define global part number |
| Version 0 | Oct 19, 2004 | - | - |

“ Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products are unchanged. Any product change will be announced by PCN.”

"The reimbursement is limited to the value of the products."