


RF SAW FILTER RSF-915.000-26000-1411-TR

			page 1 of 3
	Parameters	Specification	Unit
Center frequency (Fo)		915.000	MHz
Bandwidth		26000	kHz
Insertion Loss in BW, Max		2.5	dB
Amplitude Ripple in BW, Max		1.8	dB
	10 MHz ~ 800 MHz	42	dB
	800 MHz ~ 845 MHz	40	dB
Attenuation,	845 MHz ~ 880 MHz	35	dB
Minimum	947 MHz ~ 970 MHz	13	dB
	970 MHz ~ 1020 MHz	33	dB
	1020 MHz ~ 1200 MHz	35	dB
DC voltage		0	V
Input Power, Max		15	dBm
In/Out Impedance		50	Ω
Operating temperature range		-40 to +85	°C
Storage Temperature		-40 to +85	°C

Dimension



RALTRON ELECTRONICS = 10400 N.W. 33rd Street = Miami, Florida 33172 = U.S.A. Tel: 305-593-6033 = Fax: 305-594-3973 = e-mail: sales@raltron.com = internet: http://www.raltron.com




RF SAW FILTER RSF-915.000-26000-1411-TR


page 2 of 3

Frequency Characteristics

Transfer function



Transfer function (wideband)




RALTRON ELECTRONICS = 10400 N.W. 33rd Street = Miami, Florida 33172 = U.S.A. Tel: 305-593-6033 = Fax: 305-594-3973 = e-mail: sales@raltron.com = internet: http://www.raltron.com



RF SAW FILTER RSF-915.000-26000-1411-TR

page 3 of 3

REFLOW PROFILE



Reflow profile				
Temperature Min Preheat	T _{SMIN}	150°C		
Temperature Max Preheat	T _{SMAX}	200°C		
Time (T _{SMIN} to T _{SMAX})	ts	60-180 sec.		
Temperature	TL	217°C		
Peak Temperature	TP	260°C		
Ramp-up rate	R _{UP}	3°C/sec max.		
Ramp-down rate	R _{DOWN}	6°C/sec max.		
Time within 5°C of Peak Temperature	t _P	10 sec.		
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.		
Time	t	60-150 sec.		

Environmental

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
TERMINATION FINISH	Au
REACH – SVHC	Compliant
RoHS	Compliant
PACKAGING	TAPE & REEL



Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not assume any liability arising out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.

February 2021

RALTRON ELECTRONICS = 10400 N.W. 33rd Street = Miami, Florida 33172 = U.S.A. Tel: 305-593-6033 = Fax: 305-594-3973 = e-mail: sales@raltron.com = internet: http://www.raltron.com