



ALUMINUM ELECTROLYTIC CAPACITORS

UWT

Chip Type, Wide Temperature Range




- Chip type operating over wide temperature range of to -55 to $+105^{\circ}\text{C}$.
- Designed for surface mounting on high density PC board.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU, (EU)2015/863).
- AEC-Q200 compliant. Please contact us for details.





Specifications

Item	Performance Characteristics																									
Category Temperature Range	-55 to $+105^{\circ}\text{C}$																									
Rated Voltage Range	4 to 50V																									
Rated Capacitance Range	1 to $1500\mu\text{F}$																									
Capacitance Tolerance	$\pm 20\%$ at 120Hz, 20°C																									
Leakage Current	After 2 minutes' application of rated voltage at 20°C , leakage current is not more than 0.01CV or $3(\mu\text{A})$, whichever is greater.																									
Tangent of loss angle (tan δ)	<table border="1"> <thead> <tr> <th>Rated voltage (V)</th> <th>4</th> <th>6.3</th> <th>10</th> <th>16</th> <th>25</th> <th>35</th> <th>50</th> </tr> </thead> <tbody> <tr> <td>tan δ (MAX.)</td> <td>0.40</td> <td>0.30</td> <td>0.24</td> <td>0.20</td> <td>0.16</td> <td>0.14</td> <td>0.14</td> </tr> </tbody> </table> <p>Measurement frequency : 120Hz at 20°C</p>		Rated voltage (V)	4	6.3	10	16	25	35	50	tan δ (MAX.)	0.40	0.30	0.24	0.20	0.16	0.14	0.14								
Rated voltage (V)	4	6.3	10	16	25	35	50																			
tan δ (MAX.)	0.40	0.30	0.24	0.20	0.16	0.14	0.14																			
Stability at Low Temperature	<table border="1"> <thead> <tr> <th>Rated voltage (V)</th> <th>4</th> <th>6.3</th> <th>10</th> <th>16</th> <th>25</th> <th>35</th> <th>50</th> </tr> </thead> <tbody> <tr> <td>Impedance ratio</td> <td>Z-25°C / Z$+20^{\circ}\text{C}$</td> <td>7</td> <td>4</td> <td>3</td> <td>2</td> <td>2</td> <td>2</td> </tr> <tr> <td>ZT / Z20 (MAX.)</td> <td>Z-40°C / Z$+20^{\circ}\text{C}$</td> <td>15</td> <td>8</td> <td>8</td> <td>4</td> <td>4</td> <td>3</td> </tr> </tbody> </table> <p>Measurement frequency : 120Hz</p>		Rated voltage (V)	4	6.3	10	16	25	35	50	Impedance ratio	Z -25°C / Z $+20^{\circ}\text{C}$	7	4	3	2	2	2	ZT / Z20 (MAX.)	Z -40°C / Z $+20^{\circ}\text{C}$	15	8	8	4	4	3
Rated voltage (V)	4	6.3	10	16	25	35	50																			
Impedance ratio	Z -25°C / Z $+20^{\circ}\text{C}$	7	4	3	2	2	2																			
ZT / Z20 (MAX.)	Z -40°C / Z $+20^{\circ}\text{C}$	15	8	8	4	4	3																			
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 105°C .	<table border="1"> <tbody> <tr> <td>Capacitance change</td> <td>Within $\pm 25\%$ of the initial capacitance value for capacitors of 16V or less. Within $\pm 20\%$ of the initial capacitance value for capacitors of 25V or more.</td> </tr> <tr> <td>tan δ</td> <td>200% or less than the initial specified value</td> </tr> <tr> <td>Leakage current</td> <td>Less than or equal to the initial specified value</td> </tr> </tbody> </table>	Capacitance change	Within $\pm 25\%$ of the initial capacitance value for capacitors of 16V or less. Within $\pm 20\%$ of the initial capacitance value for capacitors of 25V or more.	tan δ	200% or less than the initial specified value	Leakage current	Less than or equal to the initial specified value																		
Capacitance change	Within $\pm 25\%$ of the initial capacitance value for capacitors of 16V or less. Within $\pm 20\%$ of the initial capacitance value for capacitors of 25V or more.																									
tan δ	200% or less than the initial specified value																									
Leakage current	Less than or equal to the initial specified value																									
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C , they shall meet the specified values for the endurance characteristics listed above.																									
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C . The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C .	<table border="1"> <tbody> <tr> <td>Capacitance change</td> <td>Within $\pm 10\%$ of the initial capacitance value</td> </tr> <tr> <td>tan δ</td> <td>Less than or equal to the initial specified value</td> </tr> <tr> <td>Leakage current</td> <td>Less than or equal to the initial specified value</td> </tr> </tbody> </table>	Capacitance change	Within $\pm 10\%$ of the initial capacitance value	tan δ	Less than or equal to the initial specified value	Leakage current	Less than or equal to the initial specified value																		
Capacitance change	Within $\pm 10\%$ of the initial capacitance value																									
tan δ	Less than or equal to the initial specified value																									
Leakage current	Less than or equal to the initial specified value																									
Marking	Black print on the case top.																									

Chip Type



Type numbering system (Example : 16V 10μF)



	(mm)							
φD × L	4 × 5.4	5 × 5.4	6.3 × 5.4	6.3 × 5.8	6.3 × 7.7	8 × 5.4	8 × 10	10 × 10
A	1.8	2.1	2.4	2.4	2.4	3.3	2.9	3.2
B	4.3	5.3	6.6	6.6	6.6	8.3	8.3	10.3
C	4.3	5.3	6.6	6.6	6.6	8.3	8.3	10.3
E	1.0	1.3	2.2	2.2	2.2	2.3	3.1	4.5
L	5.4	5.4	5.4	5.8	7.7	5.4	10	10
H	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.8 to 1.1	0.8 to 1.1

Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

● Dimension table in next page.

UWT

■ Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μF)	Case Size φD×L (mm)	tan δ	Leakage Current (μA) (at 20°C after 2 minutes)	Rated Ripple (mArms) (105°C/120Hz)	Part Number
4 (0G)	22	4×5.4	0.40	3	22	UWT0G220MCL1GB
	33	5×5.4	0.40	3	30	UWT0G330MCL1GB
	47	5×5.4	0.40	3	36	UWT0G470MCL1GB
	100	6.3×5.4	0.40	4	60	UWT0G101MCL1GB
	150	6.3×5.8	0.40	6	86	UWT0G151MCL1GS
	220	8×5.4	0.40	8.8	102	UWT0G221MCL1GB
	220	6.3×5.8	0.40	8.8	91	UWT0G221MCL6GS
	330	6.3×7.7	0.40	13.2	105	UWT0G331MCL1GS
	470	8×10	0.40	18.8	210	UWT0G471MNL1GS
	680	8×10	0.40	27.2	210	UWT0G681MNL1GS
	1000	8×10	0.40	40	230	UWT0G102MNL1GS
1500	10×10	0.40	60	310	UWT0G152MNL1GS	
6.3 (0J)	22	4×5.4	0.30	3	22	UWT0J220MCL1GB
	33	5×5.4	0.30	3	30	UWT0J330MCL1GB
	47	5×5.4	0.30	3	36	UWT0J470MCL1GB
	100	6.3×5.4	0.30	6.3	60	UWT0J101MCL1GB
	150	6.3×5.8	0.30	9.45	86	UWT0J151MCL1GS
	220	8×5.4	0.30	13.86	102	UWT0J221MCL1GB
	220	6.3×5.8	0.30	13.86	91	UWT0J221MCL6GS
	330	6.3×7.7	0.30	20.79	105	UWT0J331MCL1GS
	470	8×10	0.30	29.61	210	UWT0J471MNL1GS
	680	8×10	0.30	42.84	210	UWT0J681MNL1GS
	1000	8×10	0.30	63	230	UWT0J102MNL1GS
1500	10×10	0.30	94.5	310	UWT0J152MNL1GS	
10 (1A)	22	5×5.4	0.24	3	27	UWT1A220MCL1GB
	33	5×5.4	0.24	3.3	35	UWT1A330MCL1GB
	47	6.3×5.4	0.24	4.7	46	UWT1A470MCL1GB
	100	6.3×5.4	0.24	10	60	UWT1A101MCL1GB
	150	6.3×5.8	0.24	15	86	UWT1A151MCL1GS
	220	6.3×7.7	0.24	22	105	UWT1A221MCL1GS
	330	8×10	0.24	33	195	UWT1A331MNL1GS
	470	8×10	0.24	47	210	UWT1A471MNL1GS
	680	10×10	0.24	68	310	UWT1A681MNL1GS
1000	10×10	0.24	100	310	UWT1A102MNL1GS	
16 (1C)	10	4×5.4	0.20	3	18	UWT1C100MCL1GB
	22	5×5.4	0.20	3.52	30	UWT1C220MCL1GB
	33	6.3×5.4	0.20	5.28	40	UWT1C330MCL1GB
	47	6.3×5.4	0.20	7.52	50	UWT1C470MCL1GB
	100	6.3×5.4	0.20	16	60	UWT1C101MCL1GB
	150	6.3×7.7	0.20	24	95	UWT1C151MCL1GS
	220	6.3×7.7	0.20	35.2	105	UWT1C221MCL1GS
	330	8×10	0.20	52.8	195	UWT1C331MNL1GS
	470	8×10	0.20	75.2	230	UWT1C471MNL1GS
680	10×10	0.20	108.8	310	UWT1C681MNL1GS	

UWT

■ Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μF)	Case Size φD×L (mm)	tan δ	Leakage Current (μA) (at 20°C after 2 minutes)	Rated Ripple (mArms) (105°C/120Hz)	Part Number
25 (1E)	4.7	4×5.4	0.16	3	13	UWT1E4R7MCL1GB
	10	5×5.4	0.16	3	23	UWT1E100MCL1GB
	22	6.3×5.4	0.16	5.5	38	UWT1E220MCL1GB
	33	6.3×5.4	0.16	8.25	48	UWT1E330MCL1GB
	47	8×5.4	0.16	11.75	66	UWT1E470MCL1GB
	47	6.3×5.8	0.16	11.75	59	UWT1E470MCL6GS
	100	6.3×7.7	0.16	25	91	UWT1E101MCL1GS
	150	8×10	0.16	37.5	140	UWT1E151MNL1GS
	220	8×10	0.16	55	155	UWT1E221MNL1GS
	330	8×10	0.16	82.5	190	UWT1E331MNL1GS
470	10×10	0.16	117.5	300	UWT1E471MNL1GS	
35 (1V)	4.7	4×5.4	0.14	3	15	UWT1V4R7MCL1GB
	10	5×5.4	0.14	3.5	25	UWT1V100MCL1GB
	22	6.3×5.4	0.14	7.7	42	UWT1V220MCL1GB
	33	8×5.4	0.14	11.55	59	UWT1V330MCL1GB
	33	6.3×5.8	0.14	11.55	52	UWT1V330MCL6GS
	47	6.3×5.8	0.14	16.45	63	UWT1V470MCL1GS
	100	6.3×7.7	0.14	35	84	UWT1V101MCL1GS
	150	8×10	0.14	52.5	155	UWT1V151MNL1GS
	220	8×10	0.14	77	190	UWT1V221MNL1GS
	330	10×10	0.14	115.5	300	UWT1V331MNL1GS
50 (1H)	1	4×5.4	0.14	3	6.2	UWT1H010MCL1GB
	2.2	4×5.4	0.14	3	11	UWT1H2R2MCL1GB
	3.3	4×5.4	0.14	3	14	UWT1H3R3MCL1GB
	4.7	5×5.4	0.14	3	19	UWT1H4R7MCL1GB
	10	6.3×5.4	0.14	5	30	UWT1H100MCL1GB
	22	8×5.4	0.14	11	51	UWT1H220MCL1GB
	22	6.3×5.8	0.14	11	45	UWT1H220MCL6GS
	33	6.3×7.7	0.14	16.5	60	UWT1H330MCL1GS
	47	6.3×7.7	0.14	23.5	63	UWT1H470MCL1GS
	100	8×10	0.14	50	140	UWT1H101MNL1GS
	150	10×10	0.14	75	180	UWT1H151MNL1GS
	220	10×10	0.14	110	220	UWT1H221MNL1GS

- Taping specifications are given in page 20.
- Recommended land size, soldering by reflow are given in page 16, 17.
- Please select UUX(p.174), UUU(p.184) series if high C/V products are required.
- Please refer to page 3 for the minimum order quantity.