

ER3A(H) THRU ER3J(H)


3.0AMP SURFACE MOUNT SUPERFAST RECTIFIERS


Features

- · Glass passivated junction chip
- · Low Power Loss, High Efficiency
- Ideally Suited for Automatic Assembly
- Guard Ring Die Construction
- Plastic Case Material has UL Flammability Classification Rating 94V- 0

Mechanical Data

- · Case: Molded plastic SMB
- Terminals: Plated leads solderable per MIL-STD-750, Method 2026 guaranteed
- · Polarity: Color band dentes cathode end
- Mounting Position: AnyMaking: Type Number





Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load

For capacitive load derate current by 20%

Type Number (Note 4)	SYMBOL	ER3A(H)	ER3B(H)	ER3C(H)	ER3D(H)	ER3E(H)	ER3G(H)	ER3J(H)	Unit
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	150	200	300	400	600	V
Maximum RMS Voltage	VRMS	35	70	105	140	210	280	420	V
Maximum DC Blocking Voltage	V _{DC}	50	100	150	200	300	400	600	V
Average Rectified Output Current @TL =100°C	İ F(AV)	3.0							Α
Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	lfsм	110							Α
Forward Voltage @IF=3.0A	V _{FM}	0.95 1.25 1.7					1.7	V	
Peak Reverse Current @T _A =25 ℃	5.0								
At Rated DC Blocking Voltage @T₄ =125 ℃	I _R	100							uA
I ² t Rating for fusing (t <8.3ms)	I ² t	50.2							A^2s
Maximum Reverse Recovery Time (Note 1)	Trr	35							ns
Typical Junction Capacitance (Note 2)	Сı	50 25					pF		
Typical Thermal Resistance Junction to Ambient(Note 3)	Re JA	65							°C/W
Operating Temperature Range	TJ	-55 to+150							${\mathbb C}$
Storage Temperature Range	Тѕтс	-55 to +150							${\mathbb C}$

Note: 1.Reverse Recovery Test Conditions:IF=0.5A,IR=1.0A,IRR=0.25A.

- 2. Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C.
- 3. Thermal Resistance from Junction to lead mounted on P.C.B. with 0.3" x 0.3" (8.0 mm x 8.0 mm) copper pad areas.
- 4."H":Halogen Free.

version:03 1 of 3 www.dyelec.com



ER3A(H) THRU ER3J(H)

AVERAGE FORWARD RECIFIED CURRENT (A)

FORWARD SURGE CURRENT (A)

INVSTANTANEOUS REVERSE CURRENT (uA)

FIG.1MAXIMUM AVERAGE FORWARD CURRENT DERATING







FIG.3MAXIMUM NON-REPEITIVE SURGE CURRENT





PERCENT OF RATED PEAK INVERSE VOLTGE (V)

INSTANTANEOUS FORWARD CURRENT (A)



INSTANTANEOUS FORWARD VOLTAGE (V)

FIG.4TYPICAL JUNCTION CAPACITANCE





FIG.6 MOUNTING PAD LAYOUT





ER3A(H) THRU ER3J(H)

Important Notice and Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from DIYI.
- DIYI reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- DIYI disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.

specified use without further testing or modification.

- DIYI does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.
 DIYI makes no representation or warranty that such applications will be suitable for the
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify DIYI for any damages resulting from such improper use or sale.
- Since DIYI uses lot number as the tracking base, please provide the lot number for tracking when complaining.

version:03 3 of 3 www.dyelec.com