CL0608 Multi-phase power inductors



Product features

- High current multi-phase inductor
- 100 nH per phase coupled inductor
- 10.8 mm x 6.35 mm footprint surface mount package in an 8.2 mm height
- Ferrite core material
- Moisture Sensitivity Level (MSL): 1

Applications

- For exclusive use with Maxim® Multi-phase controllers
- Voltage Regulator Modules (VRMs) and high power density VRMs
 - Server and desktop
 - Central processing unit (CPU)
 - Graphics processing unit (GPU)
 - Application specific integrated circuit (ASIC)
- Data networking and storage systems
- High current Point-of-Load (POL) modules
- Vcore regulators

Environmental data

- Storage temperature range (Component): -40 °C to +125 °C
- Operating temperature range: -40 °C to +125 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant
- · Halogen free, lead free, RoHS compliant



Maxim® is a registered trademark of Maxim Integrated Devices, Inc.



Product specifications

| Part Number⁵ | Inductor Phases | OCL ¹ (nH) ±20% | FLL² (nH) minimum | I _{sat} 1² (A) | DCR (mΩ) ±10% @ 20 ℃ | SCL ³ (nH) ±20% | I _{sat} 2 ⁴ (A) |
|--|--------------------------|---|----------------------|----------------------------|--|-------------------------------|--|
| CL0608- 2- 100TR-R | 2 | 380 | 300 | 15 | 0.89 | 100 | 38 |
| Open Circuit Inductance (C Full Load Inductance (FLL) | Test Parameters: 1.0 MHz | z, 0.1 V _{ms} , I _{sat} 1, +25 °C | | | efinition: CL0608-x-100TR-F ict code and size | | |

3. Short Circuit Inductance (SCL) Test Parameters: 1.0 MHz, 0.1 Vms, 0.0 Adc, +25 °C CL0608-2-100TR-R short (1 & 4), measure (2 & 3), and divide by 2.

4. I_{sat} 2: Peak current where SCL drops approximately 20% @ +25 °C

x = Number of phases


100 = Inductance value per phase in nH


TR = Tape and reel packaging


-R suffix = RoHS compliant

Note: This device is licensed for use only when incorporated within a voltage regulator employing power regulating devices manufactured by Maxim Integrated Devices, Inc. No license is granted expressly or by implication to use this device with power regulating devices manufactured by any company other than Maxim.


Dimensions (mm)








Schematic




Part marking: CL0608-x-100TR-R (x = number of phases), xxxx = lot code Tolerances are ±0.25 millimeters unless stated otherwise All soldering surfaces to be coplanar within 0.13 millimeters PCB tolerances are ±0.1 millimeters unless stated otherwise DCR measured from point "a" to point "b' Do not route traces or vias underneath the inductor

Packaging information (mm)

Supplied in tape and reel packaging , 500 parts per 13" diameter reel Drawing not to scale



Inductance characteristics - SCL vs. current



Inductance characteristics - OCL vs. current

450 400 350 300 (H) 250 100 200 150 +25 ℃ 2 100 +105 ℃ +125 °C 50 0 0 2 4 6 8 10 . 12 . 14 16 18 20 22 . 24 I_{dc} (A)

CL0608-2-100TR-R

Solder reflow profile




Table 1 - Standard SnPb Solder (T_c)

| Package Thickness | Volume mm ³ <350 | Volume mm³ ≥350 |
|----------------------|-----------------------------------|-----------------------|
| <2.5mm) | 235 °C | 220 °C |
| ≥2.5mm | 220 °C | 220 °C |

Table 2 - Lead (Pb) Free Solder (T_c)

| Package Thickness | Volume mm ³ <350 | Volume mm ³ 350 - 2000 | Volume mm ³ >2000 |
|----------------------|-----------------------------------|---|------------------------------------|
| <1.6mm | 260 °C | 260 °C | 260 °C |
| 1.6 – 2.5mm | 260 °C | 250 °C | 245 °C |
| >2.5mm | 250 °C | 245 °C | 245 °C |

Reference JDEC J-STD-020

Powerina Business Worldwide

| Profile Feature | Standard SnPb Solder | Lead (Pb) Free Solder | |
|---|-------------------------|-------------------------|--|
| Preheat and Soak • Temperature min. (T _{smin}) | 100 °C | | |
| • Temperature max. (T _{smax}) | 150 °C | 200 °C | |
| • Time (T _{smin} to T _{smax}) (t _s) | 60-120 Seconds | 60-120 Seconds | |
| Average ramp up rate T _{smax} to T _p | 3 °C/ Second Max. | 3 °C/ Second Max. | |
| Liquidous temperature (Tı) Time at liquidous (tլ) | 183°C 60-150 Seconds | 217°C 60-150 Seconds | |
| Peak package body temperature (T _P)* | Table 1 | Table 2 | |
| Time $(t_p)^{**}$ within 5 °C of the specified classification temperature (T_c) | 20 Seconds** | 30 Seconds** | |
| Average ramp-down rate (T _p to T _{smax}) | 6 °C/ Second Max. | 6 °C/ Second Max. | |
| Time 25 °C to Peak Temperature | 6 Minutes Max. | 8 Minutes Max. | |
| | | | |

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

** Tolerance for time at peak profile temperature (t_n) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122 United States www.eaton.com/electronics

© 2016 Eaton All Rights Reserved Printed in USA Publication No. 10578 BU-MC16092 December 2016

Eaton is a registered trademark.

All other trademarks are property of their respective owners.