





SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PBT
 Max.Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information



2285 01 XX X N XX S Y X 01

No.of Pins Per Row 1*40

Insulator Material Option
 A=BK-PBT
 B=BK-PA66
 C=BK-PA6T
 D=BK-PA46
 F=BK-LCP

Contact Plating
 G1:1U" Gold
 G2:1.5U" Gold
 G3:2U" Gold
 G4:3U" Gold
 G5:5U" Gold
 S0:Gold Flash/Tin
 SN:Tin

Packing
 O=PE Bag
 A=Tray
 T=Tube
 P=Tube+Cap
 R=Reel+Cap
 M=Reel+Mylar



		OPERATION		DRAW	卢能	2016.9.11	SCALE	FIT	深圳市连盛精密连接器有限公司			
		X.X	±0.30				UNIT	mm				
		X.XX	±0.20	CHECK			SIZE	A4			PART NO.	FH-00882
A0	2012.03.28	NEW DRAWING					APPROVE					SHEET
REV	DATE	MODIFICATION DESCRIPTION		CHANGE			PROJ.	◆				