





RoHS

SPECIFICATIONS

Rated Current:1.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Alternate	3.00	2.00	7.00

OPERATION		DRAW	SCALE	FIT
X.X	±0.30		UNIT	mm
X.XX	±0.20	CHECK	SIZE	A4
X.XXX	±0.10		SHEET	1/1
Angle	±3°	APPROVE	PROJ.	☉
DIM	TOL			

深圳市连盛精密连接器有限公司

PART NO.

PH-00742

TITLE:

1.27PH H2.0mm 2x4pin DIP

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.03.28	NEW DRAWING	