1. SCOPE

This specification shall cover the characteristics of 1-port SAW resonator with used for remote-control security.

2. ELECTRICAL SPECIFICATION

DC Voltage VDC	10V
AC Voltage Vpp	10V50Hz/60Hz
Operation temperature	-40°℃ to +85°℃
Storage temperature	-45 °C to +85 °C
RF Power Dissipation	0dBm

2.2Electronic Characteristics

Item		Unites	Minimum	Typical	Maximum
Center Frequency		MHz	433.845	433.920	433.995
Insertion Loss		dB		1.5	2.5
Quality Factor Unload Q			5000	12800	
50 Ω Loaded Q			1000	2000	
Temperature	Turnover Temperature	°C	10	25	40
Stability	tability Freq.temp.Coefficient			0.032	
Frequency Aging		ppm/yr		<±10	
DC. Insulation Resistance		MΩ	1.0		
RF Equivalent	Motional Resistance R1	Ω		19	26
	Motional Inductance L1	μH		92.929	
KLC Model	Motional Capacitance C1	fF		1.4475	
Transducer Static Capacitance		pF		1.95	

3. TEST CIRCUIT



TAE 雅晶鑫

4. **DIMENSION**



4.2 Materials



序号	名称	材质	数量
1	基座材料	SPCC	1
2	绝缘体材料	玻璃粉	2
3	引出脚材料	4J29	4
4	引出脚搪锡	Tin 与表導距离<0.8mm	4
	基座电镀	NI >2.5um	1

5. ENVIRONMENTAL CHARACTERISTICS

5-1 High temperature exposure

Subject the device to +85 °C for 16 hours. Then release the resonator into the room conditions for 24 hours prior to the measurement. It shall fulfill the specifications in 2.2.

5-2 Low temperature exposure

Subject the device to -40° C for 16 hours. Then release the device into the room conditions for 24 hours prior to the measurement. It shall fulfill the specifications in 2.2.

5-3 Temperature cycling

Subject the device to a low temperature of -45 $^{\circ}$ C for 30 minutes. Following by a high temperature of +85 $^{\circ}$ C for 30 Minutes. Then release the device into the room conditions for 24 hours prior to the measurement. It shall meet the specifications in 2.2.

5-4 Resistance to solder heat

Dip the device terminals no closer than 1.5mm into the solder bath at 260° C $\pm 10^{\circ}$ C for 10 ± 1 sec. Then release the device into the room conditions for 4 hours. The device shall meet the specifications in 2.2.

5-5 Solderability

Subject the device terminals into the solder bath at 245° C $\pm 5^{\circ}$ C for 5s, More than 95% area of the terminals must be covered with new solder. It shall meet the specifications in 2.2.

5-6 Mechanical shock

Drop the device randomly onto the concrete floor from the height of 1m 3 times. the device shall fulfill the specifications in 2.2.

5-7 Vibration

Subject the device to the vibration for 1 hour each in x,y and z axes with the amplitude of 1.5 mm at 10 to 55 Hz. The device shall fulfill the specifications in 2.2.

6. REMARK

6.1 Static voltage

Static voltage between signal load & ground may cause deterioration & destruction of the component. Please avoid static voltage.

6.2 Ultrasonic cleaning

Ultrasonic vibration may cause deterioration & destruction of the component. Please avoid ultrasonic cleaning

6.3 Soldering

Only leads of component may be soldered. Please avoid soldering another part of component.

7.TYPCIAL APPLICATION CIRCUITS

Typical low-power Transmitter Application



Typical Local Oscillator Application

