

**1-Line Bi-directional TVS Diode** 

### www.sot23.com.tw

### Features

- Ultra small package: 1.0x0.6x0.5mm
- Ultra low capacitance: 5pF typical
- Ultra low leakage: nA level
- Low operating voltage: ±5V
- Low clamping voltage
- 2-pin leadless package
- Complies with following standards:
- - IEC 61000-4-2 (ESD) immunity test

Air discharge: ±20kV

Contact discharge: ±15kV

- - IEC61000-4-5 (Lightning)4.5A (8/20µs)
- RoHS Compliant
- Lead Finish: NiPdAu


# **Mechanical Characteristics**


- Package: DFN1006-2 (0402)
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound.
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminal Connections: See Diagram Below
- Shipping Qty : 10000pcs/7Inch Tape & Reel

## Applications


- Smart Phone and Tablet PC
- TV and Set Top Box
- Wearable Devices
- PDA

## **Dimensions and Pin Configuration**





Marking: B4



#### WWW.TECHPUBLIC.COM.TW



**1-Line Bi-directional TVS Diode** 

### www.sot23.com.tw

#### Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20µs)	Ppk	75	W
Peak Pulse Current (8/20µs)	Ірр	4.5	Α
ESD per IEC 61000-4-2 (Air)	VED	±20	kV
ESD per IEC 61000-4-2 (Contact)	VESD	±15	
Operating Temperature Range	ТЈ	-55 to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C

### Electrical Characteristics (TA=25°C unless otherwise specified)

 $\langle \rangle$ 

Parameter	Symbol	Min	Тур	Max	Unit	Test Condition
Reverse Working Voltage	VRWM	X		5	V	
Breakdown Voltage	VBR	6	K		V	IT = 1mA
Reverse Leakage Current	I <sub>R</sub>	$\bigvee$		0.08	uA	VRWM = 5V
Clamping Voltage	Vc			10	V	lpp=1A(8x 20us pulse)
Clamping Voltage	Vc			14	V	Ipp=4.5A(8x 20us pulse)
Junction Capacitance	CJ		5		pF	VR = 0V, f = 1MHz

WWW.TECHPUBLIC.COM.TW


2




**1-Line Bi-directional TVS Diode** 

### www.sot23.com.tw

#### Typical Performance Characteristics (T<sub>A</sub>=25°C unless otherwise Specified)










**1-Line Bi-directional TVS Diode** 


### www.sot23.com.tw

#### DFN1006-2 Package Outline Drawing (0402)



			DIMEN	SIONS		
	MI	LLIMETER	S	INCHES		
SYM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.45	0.50	0.55	0.018	0.020	0.022
A1	0.00	0.02	0.05	0.000	0.001	0.002
b	0.45	0.50	0.55	0.018	0.020	0.022
С	0.12	0.15	0.18	0.005	0.006	0.007
D	0.95	1.00	1.05	0.037	0.039	0.041
е		0.65 BSC		C	.026 BS0	2
E	0.55	0.60	0.65	0.022	0.024	0.026
L	0.20	0.25	0.30	0.008	0.010	0.012
h	0.07	0.12	0.17	0.003	0.005	0.007

### Suggested Land Pattern



SYM	DIMENSIONS			
	MILLIMETERS	INCHES		
X	0.60	0.024		
Y1	0.50	0.020		
Y2	0.30	0.012		
Y3	0.80	0.032		
Z	1.30	0.052		

4

#### WWW.TECHPUBLIC.COM.TW