





# RoHS

## SPECIFICATIONS

Rated Current:1.5AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:−40°c to +105°c

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30–60 seconds  
 (260°C for 5 seconds)



Dimension antitheses list			
ITEM	PC	PA	L
Alternate	3.00	3.00	7.50

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30			UNIT	mm				
X.XX	±0.20	CHECK		SIZE	A4				A0001-PH-00380
X.XXX	±0.10			SHEET	1/1			TITLE:	2.0PH 2x10pin H1.5mm 180°
Angle	±3°	APPROVE		PROJ.	◆				
DIM	TOL								
OPERATION		DRAW		SCALE		FIT		PART NO.	
DRAW		CHECK		UNIT		mm			
CHECK				SIZE		A4			
				SHEET		1/1		TITLE:	
		APPROVE		PROJ.		◆			

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.04.11	NEW DRAWING	
1			