

PVR14D Series MOV Devices


Features

- Wide operating voltages ranging from 10 Vrms to 1000 Vrms (14 Vdc to 1465 Vdc).
- Fast response time of less than 25 ns, instantly clamping the transient over voltage.
- High surge current handling capability.
- High energy absorption capability.
- Low clamping voltages, providing better surge protection.
- Low capacitance values, providing digital switching circuitry protection.
- High insulation resistance, preventing electric arcing to the adjacent devices or circuits.



Applications

- Transistor, diode, IC, Thyristor or Triac semiconductor protection.
- Surge protection in consumer electronics.
- Surge protection in industrial electronics.
- Surge protection in electronic home appliances, gas and petroleum appliances.
- Relay and electromagnetic valve surge absorption.



General Characteristics Definition


- | | |
|--|--|
| <ul style="list-style-type: none"> ● Operating temperature: <ul style="list-style-type: none"> ■ Standard coating: -40 ~ 85°C ■ High temp coating: -40 ~ 125°C ● Storage temperature: -40 ~ 125°C | <ul style="list-style-type: none"> ● Working surface temperature: 115°C ● Insulation resistance: >100 MΩ ● Coating (Epoxy resin): Flame-Retardant to UL 94 V-0 |
|--|--|

Material

- | | |
|--|--|
| <ul style="list-style-type: none"> ● Coating: Epoxy resin ● Lead wire: Tin plated copper | <ul style="list-style-type: none"> ● Electrode: Silver solder ● Disk: Zinc oxide |
|--|--|

Part Number Code

PVR 14 D □ □ □ □ □ - □ □



PVR14D Series MOV Devices

Electrical Characteristics (Standard Product)

Part Number	Max Allowable Voltage		Varistor Voltage V_b @ 1 mA	Energy 10/1000 μ S	Withstand Surge Current 8/20 μ S	Rated Power (W)	Max Leakage Current @ V_{DC} (μ A)	Max Clamping Voltage		Typical Capacitance (pF)	Safety Certification	
	V_{RMS}	V_{DC}						V	I		UL/CSA	VDE
	(V)	(V)						(V)	(A)		(V)	(A)
PVR14D180L	10	14	18	6.6	1000	0.1	30	38	10.0	11100	✓	-
PVR14D220K	14	18	22	7.6	1000	0.1	30	43	10.0	9100	✓	-
PVR14D270K	17	22	27	9.7	1000	0.1	30	53	10.0	7400	✓	✓
PVR14D330K	20	26	33	12.3	1000	0.1	30	65	10.0	6100	✓	✓
PVR14D390K	25	31	39	13.0	1000	0.1	30	77	10.0	5100	✓	✓
PVR14D470K	30	38	47	16.8	1000	0.1	30	93	10.0	4300	✓	✓
PVR14D560K	35	45	56	19.6	1000	0.1	30	110	10.0	3600	✓	✓
PVR14D680K	40	56	68	23.8	1000	0.1	30	135	10.0	2900	✓	✓
PVR14D820K	50	65	82	29.4	4500	0.6	20	135	50.0	2400	✓	✓
PVR14D101K	60	85	100	33.6	4500	0.6	20	165	50.0	2000	✓	✓
PVR14D121K	75	100	120	40.6	4500	0.6	20	200	50.0	1700	✓	✓
PVR14D151K	95	125	150	51.8	4500	0.6	20	250	50.0	1300	✓	✓
PVR14D181K	115	150	180	58.8	4500	0.6	20	300	50.0	1100	✓	✓
PVR14D201K	130	170	200	75.2	4500	0.6	20	330	50.0	1000	✓	✓
PVR14D221K	140	180	220	79.8	4500	0.6	20	360	50.0	900	✓	✓
PVR14D241K	150	200	240	82.6	4500	0.6	20	395	50.0	830	✓	✓
PVR14D271K	175	225	270	84.0	4500	0.6	20	455	50.0	740	✓	✓
PVR14D301K	190	250	300	103.0	4500	0.6	20	505	50.0	670	✓	✓
PVR14D331K	210	275	330	112.0	4500	0.6	20	550	50.0	610	✓	✓
PVR14D361K	230	300	360	123.0	4500	0.6	20	595	50.0	560	✓	✓
PVR14D391K	250	320	390	135.0	4500	0.6	20	650	50.0	510	✓	✓
PVR14D431K	275	350	430	145.0	4500	0.6	20	710	50.0	460	✓	✓
PVR14D471K	300	385	470	147.0	4500	0.6	20	775	50.0	430	✓	✓
PVR14D511K	320	415	510	148.0	4500	0.6	20	845	50.0	390	✓	✓
PVR14D561K	350	460	560	150.0	4500	0.6	20	920	50.0	360	✓	✓
PVR14D621K	385	505	620	155.0	4500	0.6	20	1025	50.0	320	✓	✓
PVR14D681K	420	560	680	160.0	4500	0.6	20	1120	50.0	290	✓	✓
PVR14D751K	460	615	750	180.0	4500	0.6	20	1240	50.0	270	✓	✓
PVR14D781K	485	640	780	190.0	4500	0.6	20	1290	50.0	260	✓	-
PVR14D821K	510	670	820	203.0	4500	0.6	20	1355	50.0	230	✓	-
PVR14D911K	550	745	910	208.0	4500	0.6	20	1500	50.0	220	✓	-
PVR14D102K	625	825	1000	212.0	4500	0.6	20	1650	50.0	200	✓	-
PVR14D112K	680	895	1100	217.0	4500	0.6	20	1815	50.0	180	✓	-
PVR14D152K	900	1200	1500	266.0	4500	0.6	20	2475	50.0	130	✓	-
PVR14D182K	1000	1465	1800	336.0	4500	0.6	20	2970	50.0	110	✓	-


PVR14D Series MOV Devices

Electrical Characteristics (High Surge Product)


Part Number	Max Allowable Voltage		Varistor Voltage V_b @ 1 mA	Energy 10/1000 μ S	Withstand Surge Current 8/20 μ S	Rated Power (W)	Max Leakage Current @ V_{DC} (μ A)	Max Clamping Voltage		Typical Capacitance (pF)	Safety Certification	
	V_{RMS}	V_{DC}						V	I		UL/CSA	VDE
	(V)	(V)						(V)	(A)			
PVR14D180LJ	10	14	18	7.0	2000	0.1	30	38	10.0	11100	✓	-
PVR14D220KJ	14	18	22	8.0	2000	0.1	30	43	10.0	9100	✓	-
PVR14D270KJ	17	22	27	10.0	2000	0.1	30	53	10.0	7400	✓	✓
PVR14D330KJ	20	26	33	12.5	2000	0.1	30	65	10.0	6100	✓	✓
PVR14D390KJ	25	31	39	13.2	2000	0.1	30	77	10.0	5100	✓	✓
PVR14D470KJ	30	38	47	17.0	2000	0.1	30	93	10.0	4300	✓	✓
PVR14D560KJ	35	45	56	20.0	2000	0.1	30	110	10.0	3600	✓	✓
PVR14D680KJ	40	56	68	24.0	2000	0.1	30	135	10.0	2900	✓	✓
PVR14D820KJ	50	65	82	30.0	6000	0.6	20	135	50.0	2400	✓	✓
PVR14D101KJ	60	85	100	35.0	6000	0.6	20	165	50.0	2000	✓	✓
PVR14D121KJ	75	100	120	42.0	6000	0.6	20	200	50.0	1700	✓	✓
PVR14D151KJ	95	125	150	53.0	6000	0.6	20	250	50.0	1300	✓	✓
PVR14D181KJ	115	150	180	74.0	6000	0.6	20	300	50.0	1100	✓	✓
PVR14D201KJ	130	170	200	78.6	6000	0.6	20	330	50.0	1000	✓	✓
PVR14D221KJ	140	180	220	80.5	6000	0.6	20	360	50.0	900	✓	✓
PVR14D241KJ	150	200	240	86.0	6000	0.6	20	395	50.0	830	✓	✓
PVR14D271KJ	175	225	270	94.0	6000	0.6	20	455	50.0	740	✓	✓
PVR14D301KJ	190	250	300	105.0	6000	0.6	20	505	50.0	670	✓	✓
PVR14D331KJ	210	275	330	115.0	6000	0.6	20	550	50.0	610	✓	✓
PVR14D361KJ	230	300	360	130.0	6000	0.6	20	595	50.0	560	✓	✓
PVR14D391KJ	250	320	390	140.0	6000	0.6	20	650	50.0	510	✓	✓
PVR14D431KJ	275	350	430	155.0	6000	0.6	20	710	50.0	460	✓	✓
PVR14D471KJ	300	385	470	175.0	6000	0.6	20	775	50.0	430	✓	✓
PVR14D511KJ	320	415	510	180.0	6000	0.6	20	845	50.0	390	✓	✓
PVR14D561KJ	350	460	560	186.0	6000	0.6	20	920	50.0	360	✓	✓
PVR14D621KJ	385	505	620	188.0	6000	0.6	20	1025	50.0	320	✓	✓
PVR14D681KJ	420	560	680	190.0	6000	0.6	20	1120	50.0	290	✓	✓
PVR14D751KJ	460	615	750	210.0	6000	0.6	20	1240	50.0	270	✓	✓
PVR14D781KJ	485	640	780	211.0	6000	0.6	20	1290	50.0	260	✓	-
PVR14D821KJ	510	670	820	235.0	6000	0.6	20	1355	50.0	230	✓	-
PVR14D911KJ	550	745	910	255.0	6000	0.6	20	1500	50.0	220	✓	-
PVR14D102KJ	625	825	1000	280.0	6000	0.6	20	1650	50.0	200	✓	-
PVR14D112KJ	680	895	1100	310.0	6000	0.6	20	1815	50.0	180	✓	-
PVR14D152KJ	900	1200	1500	420.0	6000	0.6	20	2475	50.0	130	✓	-
PVR14D182KJ	1000	1465	1800	510.0	6000	0.6	20	2970	50.0	110	✓	-

PVR14D Series MOV Devices

Marking Definitions



Physical Dimensions



Symbol	Dimension	
	(mm)	
D	17.0 max.	
H	S type	19.0 max.
	C type	22.0 max.
L	15.0 min.	
F	7.5±0.8	
d	0.8±0.05	


Part Number	T (Max)
	(mm)
PVR14D180L	4.0
PVR14D220K	4.0
PVR14D270K	4.0
PVR14D330K	4.2
PVR14D390K	4.5
PVR14D470K	4.5
PVR14D560K	4.1
PVR14D680K	4.1
PVR14D820K	4.1
PVR14D101K	4.3
PVR14D121K	4.5
PVR14D151K	4.8

Part Number	T (Max)
	(mm)
PVR14D181K	4.1
PVR14D201K	4.1
PVR14D221K	4.2
PVR14D241K	4.3
PVR14D271K	4.5
PVR14D301K	4.7
PVR14D331K	4.8
PVR14D361K	5.0
PVR14D391K	5.1
PVR14D431K	5.3
PVR14D471K	5.6
PVR14D511K	5.8

Part Number	T (Max)
	(mm)
PVR14D561K	6.2
PVR14D621K	6.4
PVR14D681K	6.4
PVR14D751K	6.5
PVR14D781K	6.8
PVR14D821K	7.2
PVR14D911K	7.6
PVR14D102K	7.8
PVR14D112K	8.5
PVR14D152K	11.0
PVR14D182K	12.5

PVR14D Series MOV Devices

Recommended Pad Layout




Symbol	Dimension (mm)
A	7.5 typ.
ΦD1	1.3 typ.
ΦD2	2.8 typ.

Part Number	B (Typ)
	(mm)
PVR14D180L	1.5
PVR14D220K	1.6
PVR14D270K	1.8
PVR14D330K	2.0
PVR14D390K	2.2
PVR14D470K	2.3
PVR14D560K	2.4
PVR14D680K	1.7
PVR14D820K	1.8
PVR14D101K	1.8
PVR14D121K	1.9
PVR14D151K	2.0

Part Number	B (Typ)
	(mm)
PVR14D181K	1.8
PVR14D201K	1.8
PVR14D221K	1.9
PVR14D241K	2.0
PVR14D271K	2.0
PVR14D301K	2.0
PVR14D331K	2.1
PVR14D361K	2.3
PVR14D391K	2.4
PVR14D431K	2.6
PVR14D471K	2.7
PVR14D511K	2.9

Part Number	B (Typ)
	(mm)
PVR14D561K	3.1
PVR14D621K	3.4
PVR14D681K	3.6
PVR14D751K	3.9
PVR14D781K	4.0
PVR14D821K	4.2
PVR14D911K	4.5
PVR14D102K	4.8
PVR14D112K	5.2
PVR14D152K	6.2
PVR14D182K	6.5


Peak Pulse Current Test Waveform



O_1 = Virtual Origin of Wave
 T = Time from 10% to 90% of Peak
 T_1 = Rise Time = $1.25 \times T$
 T_2 = Decay Time


Example - For an $8/20 \mu s$ current waveform
 $8 \mu s = T_1 = \text{Rise Time}$
 $20 \mu s = T_2 = \text{Decay Time}$

Power Derating Curve




PVR14D Series MOV Devices

Taping Dimensions



Symbol	Dimension (mm)	Symbol	Dimension (mm)
P	25.4±1.0	W ₂	3.0 max.
P ₀	12.7±0.3	H	20.0±2.0
P ₁	8.95±0.7	H ₀	16.0±1.0
P ₂	12.7±1.3	H ₁	36.0 max.
F	7.5±0.8	h	0±0.2
W	18.0±1.0	L	1.0 max.
W ₀	12.5 max.	D ₀	4.0±0.2
W ₁	9.0±0.5	t	0.6±0.3

Lead Free Wave Soldering Recommendations




Preheat	
- Temperature Min (T _{s_min})	110°C
- Temperature Max (T _{s_max})	150°C
- Time (T _{s_min} to T _{s_max})	30-90 seconds
- Average Ramp-Up Rate	1~3°C/second
Peak Temperature	260°C
Max Time at Peak Temperature	5 seconds
Ramp-Down Rate	5 °C /second max.


Note: If the wave soldering temperatures exceed the recommended profile, devices may not meet the performance requirements.

PVR14D Series MOV Devices

Reel and Ammo Packing Dimensions/Quantity




Symbol	Dimension (mm)
W ₁	46±1
a	340±10
c	31±1



Symbol	Dimension (mm)
W	348±5
L	275±5
H	60±5

Part Number	Reel pack		Ammo pack	
	Box	Carton	Box	Carton
180L - 561K	500	2000	1000	10000
621K - 821K	300	1200	800	8000

Bulk Packing Quantity



Part Number	Bulk pack			
	Type	Bag	Small Carton	Carton
180L - 681K	Long leg	500	3000	6000
	Short leg	500	4000	8000
751K - 182K	Long leg	500	2500	5000
	Short leg	500	3000	6000

PVR14D Series MOV Devices

Reliability Test

Mechanical Ratings										
Test Parameter	Test Condition / Description	Performance Requirements								
Terminal Pull Strength	<p>After gradually applying the load specified below and keeping the unit fixed for ten seconds, the terminal shall be visually examined for any damage.</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td style="text-align: center;">Diameter</td> <td style="text-align: center;">Loading</td> </tr> <tr> <td style="text-align: center;">0.6 mm</td> <td style="text-align: center;">1.0 kg</td> </tr> <tr> <td style="text-align: center;">0.8 mm</td> <td style="text-align: center;">1.0 kg</td> </tr> <tr> <td style="text-align: center;">1.0 mm</td> <td style="text-align: center;">2.0 kg</td> </tr> </table>	Diameter	Loading	0.6 mm	1.0 kg	0.8 mm	1.0 kg	1.0 mm	2.0 kg	No visible damage
Diameter	Loading									
0.6 mm	1.0 kg									
0.8 mm	1.0 kg									
1.0 mm	2.0 kg									
Terminal Bending Strength	<p>The unit shall be secured with its terminal kept vertical and the weight specified below be applied in axial direction. The terminal shall gradually be bent by 90° in one direction, then 90° in the opposite direction, and again back to the original position. The damage of the terminal shall be visually examined.</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td style="text-align: center;">Diameter</td> <td style="text-align: center;">Loading</td> </tr> <tr> <td style="text-align: center;">0.6 mm</td> <td style="text-align: center;">0.5 kg</td> </tr> <tr> <td style="text-align: center;">0.8 mm</td> <td style="text-align: center;">0.5 kg</td> </tr> <tr> <td style="text-align: center;">1.0 mm</td> <td style="text-align: center;">1.0 kg</td> </tr> </table>	Diameter	Loading	0.6 mm	0.5 kg	0.8 mm	0.5 kg	1.0 mm	1.0 kg	No visible damage
Diameter	Loading									
0.6 mm	0.5 kg									
0.8 mm	0.5 kg									
1.0 mm	1.0 kg									
Vibration	The specimen shall be vibrated by its lead wires with a total amplitude of 1.5 mm and a varying frequency of 10~55~10Hz (each minutes) for a period of 2 hours respectively in each X, Y and Z directions.	No Visible damage $\Delta V_b/V_b \leq 5\%$								
Solderability	After dipping the terminal the depth of approximately 3 mm from the specimen in a soldering bath of 260°C for 10±1 (D5: 5±1) seconds. Thereafter the terminal shall be visually examined.	Terminations shall be uniformly covered by solder								
Resistance to solder heat	After preheating the specimen, the specimen shall be completely immersed into a soldering bath having a temperature of 260±5°C for 10±1 (D5: 5±1) seconds or iron of 400±5°C for 3±0.5 seconds. Thereafter the change of V_b and mechanical damage shall be examined.	No Visible damage $\Delta V_b/V_b \leq 5\%$								
Environmental Ratings										
Test Parameter	Test Condition / Description	Performance Requirements								
Dry Heat Loading	<p>The specimen shall be applied continuously the maximum allowable voltage at the specified conditions for specified period and then stored at room temperature and normal humidity over 2 hours. Thereafter, the change of V_b and mechanical damage shall be examined.</p> <p>Ambient temp: 125±2°C / Period: 1000±24hours</p>	$\Delta V_b/V_b \leq 10\%$								
High Temp Storage	<p>In a dry oven without load.</p> <p>Ambient temp: 125±2°C / Period: 1000±24hours</p>	$\Delta V_b/V_b \leq 5\%$								
Damp Heat Loading	<p>The specimen shall be applied continuously the maximum allowable voltage at the specified conditions for specified period and then stored at room temperature and normal humidity over 2 hours. Thereafter, the change of V_b and mechanical damage shall be examined.</p> <p>Ambient temp: 40±2°C, 90~95%RH / Period: 1000±24hours</p>	$\Delta V_b/V_b \leq 10\%$								
Temperature Cycle	<p>Condition the specimen to each temperature from step 1 to step 4 in this order for the period shown in the table of specifications. The change of V_b and mechanical damage shall be examined after 2 hours.</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td style="text-align: center;">Step 1</td> <td style="text-align: center;">-40±3°C / 30min.</td> </tr> <tr> <td style="text-align: center;">Step 2</td> <td style="text-align: center;">Room temp / 15min.</td> </tr> <tr> <td style="text-align: center;">Step 3</td> <td style="text-align: center;">85±2°C / 30min.</td> </tr> <tr> <td style="text-align: center;">Step 4</td> <td style="text-align: center;">Room temp / 15min.</td> </tr> </table>	Step 1	-40±3°C / 30min.	Step 2	Room temp / 15min.	Step 3	85±2°C / 30min.	Step 4	Room temp / 15min.	No Visible damage $\Delta V_b/V_b \leq 10\%$
Step 1	-40±3°C / 30min.									
Step 2	Room temp / 15min.									
Step 3	85±2°C / 30min.									
Step 4	Room temp / 15min.									
Surge Lifetime Rating	The change of V_b shall be measured after the impulse listed below is applied 10,000 times continuously with the interval of ten seconds at room temperature.	No Visible damage $\Delta V_b/V_b \leq 10\%$								
Voltage Proof	Voltage: 2500 Vac / Leakage current ≤ 0.5 mA / Time: 60 seconds	No Breakdown								