



PT3617

Hi-sensitivity Hall-effect Latch

Applications

- DC brushless motors
- Proximity Sensor
- Tachometers
- Magnetic encoders
- Automotive systems

Features

- 4.0V to 38V wide operation voltage
- High sensitivity
- Reverse polarity protection (up to -60V)
- Built-in dynamic offset cancellation
- Open drain output
- High balance and low thermal drift magnetic sensing
- Support 40V load dump test

Ordering information

- PT3617-PA-T
Package(PA):UA & LH
Temperature(T): A

Specifications**Absolute Maximum Ratings (Ta=25°C)**

Parameter	Symbol	Conditions	Rating	Unit
Maximum supply voltage	V_{DDMAX}		40	V
Minimum supply voltage	V_{DDMIN}		-60	V
Allowable power dissipation	P_D	TO-92(UA)	550 ^{*1}	mW
		SOT-23(LH)	500 ^{*1}	mW
Operating temperature range	T_A	Suffix 'A'	-40~+150	°C
Storage temperature range	T_S		-65~+150	°C
Relative Humidity	R_H		20~90	%
Max. output current	I_{OMAX}		50	mA

*1: On 50mm x 50mm x 1.6mm glass epoxy board

P/N: PT3617-XX-X

TO92-3L (UA)



1 : VDD
2 : GND
3 : OUT

1 2 3

SOT23-3L (LH)



1 : VDD
2 : OUT
3 : GND

1 2 3

- ◆ All PROLIFIC products described or contained herein do not have specifications that can handle applications require extremely high levels of reliability, such as life-support systems, aircraft control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your PROLIFIC representative nearest you before using any PROLIFIC products described or contained herein in such applications.
- ◆ PROLIFIC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, the rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all PROLIFIC products described or contained herein.

PROLIFIC TECHNOLOGY INC.

7F, No.48,Sec.3, Nan Kang Rd., Nan Kang, Taipei, 115, Taiwan.

Electrical Characteristics (T_A=+25°C)

Characteristic	Symbol	Test Condition	Min.	Typ.	Max.	Units
Supply Voltage	V _{DD}		4.0		38	V
Output Sink Voltage	V _{OL}	@ I _{OUT} =20mA		130	280	mV
Output Leakage Current	I _{OH}	Output switch off			0.1	uA
Output Clamp Voltage	V _{BV}			40	42	V
Supply Current	I _{DD}	Output open		4	6	mA

Magnetic Characteristics (T_A=+25°C, V_{DD}=5V)

Operate Point	B _{OP}		10	22	45	G
Release Point	B _{RP}		-45	--22	-10	G
Hysteresis	B _{HYS}		25	44	62	G

Magnetic Characteristics (T_A=+25°C, V_{DD}=12V)


Operate Point	B _{OP}		10	22	42	G
Release Point	B _{RP}		-42	-22	-10	G
Hysteresis	B _{HYS}		28	44	60	G

Magnetic Characteristics (T_A=-40°C~150°C, V_{DD}=12V)


Operate Point	B _{OP}		10	22	50	G
Release Point	B _{RP}		-50	-22	-10	G
Hysteresis	B _{HYS}		35	44	72	G

Output Behavior versus Polarity (T_A=-40°C~150°C, V_{DD}=4.0V~38V)

Parameters	Test Conditions(LH)	Output(LH)	Test Conditions(UA)	Output(UA)
South pole	B>Bop	Low	B>Bop	Low
North pole	B<Brp	High	B<Brp	High




Output = Low




Output = High

SOT-23(LH) Package



Output =Low



Output = High

TO-92(UA) Package

General Specifications

The PT3617 is designed for magnetic actuating using a bipolar magnetic field. The built-in dynamic offset cancellation of pre-amplifier stage achieves optimal symmetrical magnetic sensing. This Hall effect IC is optimal for DC brushless fan application. The supply voltage range is from 4.0V to 38V and the maximum output current is 50mA. The internal protection device could benefit PT3617 to survive up to -32V in reversed battery situation.

This Hall effect sensor IC integrate the sensor, pre-amplifier with dynamic offset cancellation and the hysteresis comparator in single chip. The architecture block diagram is shown in Fig. 1.




Fig. 1. Functional diagram









Fig. 2. Output behavior

General Characteristics



Application circuits



NOTE :

D0: general diode

C0: decoupling capacitor 0.1uF(recommended)


R1: 1K~10Kohm (recommended)

Packing Specification


Type	Package	Packing Quantity (EA)	Quantity per Box (EA)	MOQ
TO-92	Box	1000	20000	80000
SOT-23	Reel	3000	12000	168000

Packing dimension


TO-92






BAG



BOX





CARTON

Packing dimension
SOT-23


SOT-23

3000 EA/PER REEL 4 REEL/BOX



**Package Outline
 TO-92(UA)**



Marking:
 Part Number : 617
 Date Code : X(Year) XX(Week)

1. VDD/DC power supply
2. GND/DC ground
3. OUT/output pin

SYMBOLS	DIMENSIONS IN MILLIMETERS(mm)		
	MIN	NOM	MAX
A	3.90	4.00	4.10
B	2.80	2.90	3.00
C	0.38	0.42	0.47
D	14.30	14.50	14.70
E	1.25	1.28	1.31
F	1.40	1.50	1.60
G	0.67	0.72	0.77
H	0.33	0.38	0.43
I	0.38	0.45	0.52
θ		45°	

Package Outline
SOT-23(LH)

Sensor Location



Marking:
Part Number : 617
Date Code : X(Year) XX(Week)

- 1. VDD/DC power supply
- 2. OUT/output pin
- 3. GND/DC ground

SYMBOLS	DIMENSIONS IN MILLIMETERS(mm)		
	MIN	NOM	MAX
A	1.10	1.20	1.30
A1	0.11	0.12	0.13
A2	1.05	1.10	1.15
b	0.35	0.40	0.45
C	0.15	0.20	0.25
D	2.90	3.00	3.10
E	1.50	1.60	1.70
F	0.35	0.40	0.45
H	2.70	2.80	2.90
e	1.80	1.90	2.00
L	0.35	0.40	0.45


Thermal resistance

TO92-3L

Parameter	Symbol	Conditions	Rating	Units
Allowable power dissipation	P_d		550 ^{*1}	mW
Junction to ambient thermal resistance	θ_{JA}		255	°C/W
Junction to case thermal resistance	θ_{JC}		90	°C/W
Maximum junction temperature	T_J		165	°C

*1: Reduced by 14.3mW for each increase in T_a of 1°C over 25°C When mounted on 50mm x 50mm x 1.6mm glass epoxy board

Pd versus Ambient temperature




SOT-23

Parameter	Symbol	Conditions	Rating	Units
Allowable power dissipation	P_d		500 ^{*1}	mW
Junction to ambient thermal resistance	θ_{JA}		280	°C/W
Junction to case thermal resistance	θ_{JC}		110	°C/W
Maximum junction temperature	T_J		165	°C

*1: Reduced by 14.3mW for each increase in T_a of 1°C over 25°C When mounted on 50mm x 50mm x 1.6mm glass epoxy board

Pd versus Ambient temperature



Order information

Part Number	Temperature Range	Package Type	Package Qty	Prolific Type Code
PT3617UAA	-40°C~+150°C	TO92-3L	1000pcs/Bulk	PT3617E1OAG7D2
PT3617LHA	-40°C~+150°C	SOT23-3L	3000pcs/Reel	PT3617E1SAG8D2

- ◆ Specifications of any and all PROLIFIC products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- ◆ PROLIFIC Technology Inc. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- ◆ In the event that any and all PROLIFIC products described or contained herein fall under strategic products (including services) controlled under the Foreign Exchange and Foreign Trade Control Law of Taiwan, such products must not be exported with our obtaining export license from the Ministry of international Trade and Industry in accordance with the above law.
- ◆ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of PROLIFIC Technology Inc.
- ◆ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the Delivery Specification for the PROLIFIC product that you intend to use.
- ◆ Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. PROLIFIC believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

Specifications and information herein are subject to change without notice.