

## DESCRIPTION


The SRV05-4 has a low capacitance of 0.4pF maximum and operates with virtually no insertion loss to 1GHz. This makes the device ideal for protection of high-speed data lines such as USB 2.0, Firewire, DVI, and gigabit Ethernet interfaces. The low capacitance array configuration allows the user to protect four high-speed data or transmission lines. The low inductance construction minimizes voltage overshoot during high current surges. They may be used to meet the ESD immunity requirements of IEC61000-4-2, Level 4 ( $\pm 15\text{kV}$  air,  $\pm 8\text{kV}$  contact discharge). This device has been specifically designed to protect sensitive components which are connected to high-speed data and transmission lines from overvoltage caused by ESD (electrostatic discharge), CDE (Cable Discharge Events), and lightning.

## APPLICATIONS

- ✧ Digital Visual Interface (DVI).
- ✧ USB 1.1/2.0/OTG.
- ✧ IEEE 1394 Firewire Ports.
- ✧ Notebooks & Handhelds.
- ✧ Projection TV & Monitors.
- ✧ Set-top box.
- ✧ Flat Panel Displays.
- ✧ PCI Express.

## FEATURES

- ✧ Protects four I/O lines and one Vcc line.
- ✧ Low capacitance.
- ✧ Working voltages : 5V.
- ✧ Low leakage current.
- ✧ Low capacitance for high-speed interfaces.
- ✧ No insertion loss to 2.0GHz.
- ✧ Response Time is < 1 ns.
- ✧ Solid-state silicon avalanche technology.
- ✧ ROHS compliant.



## MECHANICAL CHARACTERISTICS

- ✧ SOT-23-6L package.
- ✧ Flammability Rating: UL 94V-0.
- ✧ Terminal: Matte tin plated.
- ✧ Packaging: Tape and Reel.
- ✧ High temperature soldering guaranteed:  $260^{\circ}\text{C}/10\text{s}$ .
- ✧ Reel size: 7 inch.
- ✧ Material: Halogen free.
- ✧ Quantity per reel: 3,000pcs.

**DEVICE CHARACTERISTICS**


<b>Absolute Maximum Ratings (T<sub>A</sub>=25°C unless otherwise specified)</b>			
<b>Parameter</b>	<b>Symbol</b>	<b>Value</b>	<b>Unit</b>
Peak Pulse Power (8/20μs)	P <sub>PP</sub>	150	W
Peak Pulse Current (8/20μs)	I <sub>PP</sub>	5	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD	±15 ±8	kV
Operating Temperature Range	T <sub>J</sub>	-55 to +150	°C
Storage Temperature Range	T <sub>stg</sub>	-55 to +150	°C

**ELECTRICAL CHARACTERISTICS(T<sub>A</sub>=25°C unless otherwise specified)**


<b>Symbol</b>	<b>Parameter</b>	<b>Test Condition</b>	<b>Min</b>	<b>Typ</b>	<b>Max</b>	<b>Units</b>
V <sub>RWM</sub>	Reverse Working Voltage	Any I/O pin to GND			5.0	V
V <sub>BR</sub>	Reverse Breakdown Voltage	I <sub>T</sub> = 1mA Any I/O pin to GND	6.0			V
I <sub>R</sub>	Reverse Leakage Current	V <sub>RWM</sub> = 5V Any I/O pin to GND			1	μA
V <sub>F</sub>	Diode Forward Voltage	I <sub>F</sub> = 15mA			1.2	V
V <sub>C1</sub>	Clamping Voltage 1	I <sub>PP</sub> = 1A, t <sub>p</sub> = 8/20μs Any I/O pin to GND			15	V
V <sub>C2</sub>	Clamping Voltage 2	I <sub>PP</sub> = 5A, t <sub>p</sub> = 8/20μs Any I/O pin to GND			28	V
C <sub>J1</sub>	Junction Capacitance 1	V <sub>R</sub> = 0V, f = 1MHz Between I/O pins			0.4	pF
C <sub>J2</sub>	Junction Capacitance 2	V <sub>R</sub> = 0V, f = 1MHz Any I/O pin to GND			0.8	pF

Note: I/O pins are pin 1,3,4,6.


**TYPICAL CHARACTERISTICS**( $T_A=25^\circ\text{C}$  unless otherwise Specified)




**Pulse Waveform**




**Non-Repetitive Peak Pulse Power vs. Pulse Time**




**Power Derating Curve**



**Junction Capacitance vs. Reverse Voltage**

**SOLDERING PARAMETERS**


Reflow Condition		Pb-Free assembly (see FIG.5)
Pre Heat t	-Temperature Min ( $T_{s(min)}$ )	+150°C
	-Temperature Max( $T_{s(max)}$ )	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp ( $T_L$ ) to peak)		3°C/sec. Max
$T_{s(max)}$ to $T_L$ - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature( $T_L$ )(Liquid us)	+217°C
	-Temperature( $t_L$ )	60-150 secs.
Peak Temp ( $T_p$ )		+260(+0/-5)°C
Time within 5°C of actual Peak Temp ( $t_p$ )		30 secs. Max
Ramp-down Rate		6°C/sec. Max
xTime 25°C to Peak Temp ( $T_p$ )		8 min. Max
Do not exceed		+260°C

**SOT-23-6L PACKAGE OUTLINE & DIMENSIONS**


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100		0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0,950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
	0°	8°	0°	8°

Website: <http://www.jksemi.com>

For additional information, please contact your local Sales Representative.

©Copyright 2016, jksemi