



Product data sheet

www.msksemi.com





	5	4	; [3] ; ⊨→ –	
	4	LÅ	نے ہے	
10 9 8 7	6			



DFN-2510-10L

Features

- ♦ 150 Watts peak pulse power (tp = 8/20µs)
- Transient protection for high speed data lines to IEC 61000-4-2 (ESD) ±15kV (air), ±8kV (contact) IEC 61000-4-4 (EFT) 40A (5/50ns)
- Working voltages : 5V
 - Protects two or four I/O lines
- Ultra Low capacitance:0.3pf (typical between I/O channel)
- Low operating and clamping voltages
- Solid-state silicon avalanche technology

Applications

- High Definition Multi-Media Interface (HDMI)
- USB 1.1/2.0/3.0/OTG
- IEEE 1394 Firewire Ports
- Projection TV Monitors and Flat Panel Displays
- Notebook Computers
- Set Top Box

Maximum Rating @ Ta=25°C unless otherwise specified

Symbol	Parameter	Ratings	Units
Ррк	Peak Pulse Power (tp = 8/20µs)	150	Watts
Τι	Lead Soldering Temperature	260(10sec.)	°C
TJ	Operating Temperature	-55 to +125	°C
Тѕтс	Storage Temperature	-55 to +150	°C






Electrical Characteristics@ Ta=25 $^\circ\!\!\mathbb{C}$ unless otherwise


Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
VRWM	Reverse Working Voltage	Any I/O to Ground			5.0	V
VBR	Reverse Breakdown Voltage	l⊤= 1mA, Any I/O to Ground	6.0			V
IR	Reverse Leakage Current	$V_{\rm RWM} = 5V,$			1	
IR	Neverse Leakage Current	Any I/O to Ground			1	μA
VF	Diode Forward Voltage	l⊧ = 15mA		0.85	1.2	V
		I _{PP} = 1A, tp =8/20μs,			9.8	V
Vc	Clamping Voltage	any I/O pin to Ground			3.0	v
vc	Clamping voltage	I _{PP} = 3A, tp =8/20µs,			15	V
		any I/O pin to Ground			15	v
		V _R = 0V, f = 1MHz,		0.25	0.3	nΕ
CJ	Junction Capacitance	between I/O pins		0.25	0.5	pF
CJ		$V_R = 0V$, f = 1MHz,		0.5	0.6	nΕ
		any I/O pin to Ground		0.5	0.6	pF







Typical Characteristics@ Ta=25 $^{\circ}$ C unless otherwise specified












ESD5344D-MS HF 🐼

Semiconductor

Compiance

PACKAGE MECHANICAL DATA




Dimensions in millimeters

A	► D	В
		T E

DIMENSI ON						
DIM	INCHES		MILLIMETERS			
	MIN	NOM	MAX	MIN	NOM	MAX
А	.020	.023	.026	0.50	0.58	0.65
A1	0.00	.001	.002	0.00	0.03	0.05
A2	(.0	005)		(0	.13)	
b	.006	.008	.010	0.15	0.20	0.25
b1	.014	.016	.018	0.35	0.40	0.45
D	.094	.098	.102	2.40 2.50 2.		2.60
E	.035	.039	.043	0.90	1.00	1.10
е	.020 BSC			0.50 BSC		
L	.012	.015	.017	0.30	0.38	0.425
N		8			8	
aaa	.003		0.08			
bbb	.004		.004 0.10			

Suggested Pad Layout



	DIMENSIONS				
DIM	INCHES	MILLIMETERS			
С	(.034)	(0.875)			
G	.008	0.20			
Р	.020	0.50			
P1	.039	1.00			
Х	.008	0.20			
X1	.016	0.40			
Y	.027	0.675			
Y1	(.061)	(1.55)			
Z	.061	1.55			

NOTES:

CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES). THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY. CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR COMPANY'S MANUFACTURING GUIDELINES ARE MET.

REEL SPECIFICATION

P/N	PKG	QTY
ESD5344D-MS	DFN-2510-10L	3000



<u>Attention</u>

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications f any and all MSKSEMI Semiconductor products described orcontained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuits for safedesign, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. Whendesigning equipment, referto the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.