


产品型号: 17-MUB/-MUG



RoHS
WEEE Pb
free
compliant

产品说明

Dimensions: mm (in.)

The grounding terminals were developed and patented by WECO. The upper section encompasses the lower section and thus prevents the limbs from bending outwards. The terminals guarantee a high degree of operational reliability and meet the requirements of the corresponding VDE regulations.

The flat clamping member which is mounted in the upper section in such a way that it can rotate reliably prevents damage to the wires. This design is thus particularly suitable for stranded conductors

Three base designs are available for different scopes of applications.

- Single Grounding Terminal
- Dual Wire Clamping
- Threaded Hole or Threaded Post
- With Locking Cap
- MU: with flat, stationary clamping mechanism

$$D = 8.0 (0.31)$$

$$d = 7.0 (0.28)$$

$$H = 22.0 (0.87)$$

$$Z = 11.0 (0.43)$$

$$e = 4.5 (0.18)$$

$$17\text{-MUB } h = n/a$$

$$g = M4$$

$$17\text{-MUG } h = 8.0 (0.31)$$

$$g = M4$$

Max. Terminal space a x b
3.1 x 5.5 (0.12 x 0.22)

技术参数

额定截面: 2 x 4
mm² (2 x 6199 mils²)

剥线长度: 9 mm
(0.35 in.)

推荐工作电流: 39A

推荐线径: 2 x 12
AWG

Base Style Options B: Threaded Hole G: Threaded Post

材料

M4, 黄铜镀镍

接线端子本
体:

温度上限: 200°C

应用

螺帽: 黄铜镀镍
螺纹孔或螺纹柱: M4

This design is thus particularly suitable for stranded conductors

