


## Power MOSFET

PRODUCT SUMMA	RY		
V <sub>DS</sub> (V)	900		
R <sub>DS(on)</sub> (Ω)	$V_{GS} = 10 V$	2.5	
Q <sub>g</sub> (Max.) (nC)	12	20	
Q <sub>gs</sub> (nC)	16		
Q <sub>gd</sub> (nC)	6	7	
Configuration	Sin	gle	



### S

#### **FEATURES**

- Dynamic dV/dt Rating
- Repetitive Avalanche Rated
- Isolated Central Mounting Hole
- Fast Switching
- Ease of Paralleling
- Simple Drive Requirements
- Compliant to RoHS Directive 2002/95/EC

#### DESCRIPTION

Third generation Power MOSFETs from Vishay provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The **TO-247AC** package is preferred for commercial-industrial applications where higher power levels preclude the use of TO-220AB devices. The TO-247AC is similar but superior to the earlier TO-218 package because of its isolated mouting hole. It also provides greater creepage distance between pins to meet the requirements of most safety specifications.

ORDERING INFORMATION	
Package	TO-247AC
Lead (Pb)-free	IRFPF40PbF
	SiHFPF40-E3
SnPb	IRFPF40
	SiHFPF40

PARAMETER			SYMBOL	LIMIT	UNIT
Drain-Source Voltage			V <sub>DS</sub>	900	V
Gate-Source Voltage		V <sub>GS</sub>	± 20	v	
Continuous Drain Current	V <sub>GS</sub> at 10 V	T <sub>C</sub> = 25 °C	L.	4.7	
Continuous Drain Current	V <sub>GS</sub> at 10 V	$T_C = 100 \ ^\circ C$	ID	2.9	А
Pulsed Drain Current <sup>a</sup>		I <sub>DM</sub>	19		
Linear Derating Factor				1.2	W/°C
Single Pulse Avalanche Energy <sup>b</sup>			E <sub>AS</sub>	500	mJ
Repetitive Avalanche Current <sup>a</sup>			I <sub>AR</sub>	4.7	А
Repetitive Avalanche Energy <sup>a</sup>			E <sub>AR</sub>	15	mJ
Maximum Power Dissipation	T <sub>C</sub> =	25 °C	PD	150	W
Peak Diode Recovery dV/dt <sup>c</sup>			dV/dt	1.5	V/ns
Operating Junction and Storage Temperature Range		T <sub>J</sub> , T <sub>stg</sub>	- 55 to + 150	- °C	
Soldering Recommendations (Peak Temperature) for 10 s			300 <sup>d</sup>		
Mounting Torque	6.22 or 1	12 001014		10	lbf ∙ in
Mounting Torque	6-32 or M3 screw			1.1	N · m

#### Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).

b.  $V_{DD} = 50 \text{ V}$ , starting  $T_J = 25 \text{ °C}$ , L = 42 mH,  $R_g = 25 \Omega$ ,  $I_{AS} = 4.7 \text{ A}$  (see fig. 12). c.  $I_{SD} \le 4.7 \text{ A}$ , dI/dt  $\le 110 \text{ A/}\mu\text{s}$ ,  $V_{DD} \le V_{DS}$ ,  $T_J \le 150 \text{ °C}$ . d. 1.6 mm from case.

\* Pb containing terminations are not RoHS compliant, exemptions may apply

Document Number: 91250 S11-0441-Rev. B, 14-Mar-11 www.vishay.com



THE PRODUCT DESCRIBED HEREIN AND THIS DATASHEET ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000

Vishay Siliconix



THERMAL RESISTANCE RATI	NGS							
PARAMETER	SYMBOL	TYP.		MAX.			UNIT	
Maximum Junction-to-Ambient	R <sub>thJA</sub>	-		40				
Case-to-Sink, Flat, Greased Surface	R <sub>thCS</sub>	0.24		-			°C/W	
Maximum Junction-to-Case (Drain)	R <sub>thJC</sub>	-		0.83				
		·						
<b>SPECIFICATIONS</b> ( $T_J = 25 \ ^{\circ}C$ ,	unless otherw	/ise noted)						
PARAMETER	SYMBOL	TEST	CONDIT	ONS	MIN.	TYP.	MAX.	UNIT
Static								
Drain-Source Breakdown Voltage	V <sub>DS</sub>	$V_{GS} = 0$	V, I <sub>D</sub> = 2	50 µA	900	-	-	V
V <sub>DS</sub> Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Reference t	o 25 °C,	I <sub>D</sub> = 1 mA	-	1.0	-	V/°C
Gate-Source Threshold Voltage	V <sub>GS(th)</sub>	$V_{DS} = V_0$	<sub>GS</sub> , I <sub>D</sub> = 2	250 μA	2.0	-	4.0	V
Gate-Source Leakage	I <sub>GSS</sub>	V <sub>G</sub>	$s = \pm 20^{\circ}$	V	-	-	± 100	nA
Zara Cata Valtaga Drain Current		V <sub>DS</sub> = 90	00 V, V <sub>GS</sub>	s = 0 V	-	-	100	
Zero Gate Voltage Drain Current	IDSS	V <sub>DS</sub> = 720 V, V	<sub>GS</sub> = 0 V	, T <sub>J</sub> = 125 °C	-	-	500	μA
Drain-Source On-State Resistance	R <sub>DS(on)</sub>	$V_{GS} = 10 V$	ار	<sub>D</sub> = 2.8 A <sup>b</sup>	-	-	2.5	Ω
Forward Transconductance	9 <sub>fs</sub>	V <sub>DS</sub> = 50	0 V, I <sub>D</sub> =	2.8 A <sup>b</sup>	2.5	-	-	S
Dynamic							•	
Input Capacitance	C <sub>iss</sub>	$V_{GS} = 0 V$ ,		-	1600	-		
Output Capacitance	C <sub>oss</sub>	V	<sub>os</sub> = 25 V		-	180	-	pF
Reverse Transfer Capacitance	C <sub>rss</sub>	f = 1.0 M	MHz, see	e fig. 5	-	63	-	
Total Gate Charge	Qg				-	-	120	
Gate-Source Charge	Q <sub>gs</sub>	V <sub>GS</sub> = 10 V		A, V <sub>DS</sub> = 360 V, ig. 6 and 13 <sup>b</sup>	-	-	16	nC
Gate-Drain Charge	Q <sub>gd</sub>		300 1	ig. o and to	-	-	67	
Turn-On Delay Time	t <sub>d(on)</sub>				-	15	-	
Rise Time	t <sub>r</sub>	V <sub>DD</sub> = 45	0 V I= -	470	-	36	-	
Turn-Off Delay Time	t <sub>d(off)</sub>	$V_{DD} = 43$ $R_g = 9.1 \Omega, R_f$			-	110	-	ns
Fall Time	t <sub>f</sub>				-	32	-	
Internal Drain Inductance	L <sub>D</sub>	Between lead, 6 mm (0.25") from	m		-	5.0	-	
Internal Source Inductance	Ls	package and cer die contact	nter of		-	13	-	nH
Drain-Source Body Diode Characteristic	cs						•	
Continuous Source-Drain Diode Current	I <sub>S</sub>	MOSFET symbol showing the		-	-	4.7	А	
Pulsed Diode Forward Currenta	I <sub>SM</sub>	integral reverse p - n junction did	ode	a la	-	-	19	
Body Diode Voltage	$V_{SD}$	T <sub>J</sub> = 25 °C, I <sub>S</sub>	; = 4.7 A,	$V_{GS}=0 \ V^{b}$	-	-	1.8	V
Body Diode Reverse Recovery Time	t <sub>rr</sub>	T <sub>J</sub> = 25 °C, I <sub>F</sub> = 4	170 di/	dt – 100 A/ueb	-	510	770	ns
Body Diode Reverse Recovery Charge	Q <sub>rr</sub>	$r_{\rm J} = 20$ 0, $r_{\rm F} = 2$	., A, Ul/	αι – 100 Αγμο-	-	2.2	3.3	μC
Forward Turn-On Time	t <sub>on</sub>	Intrinsic turn-	on time	is negligible (turn	-on is doi	minated b	y L <sub>S</sub> and	L <sub>D</sub> )

#### Notes


a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).

b. Pulse width  $\leq$  300 µs; duty cycle  $\leq$  2 %.

www.vishay.com 2 Document Number: 91250 S11-0441-Rev. B, 14-Mar-11



**Vishay Siliconix** 



### TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)






Fig. 2 - Typical Output Characteristics, T<sub>C</sub> = 150 °C




Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Normalized On-Resistance vs. Temperature

### Vishay Siliconix






Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 7 - Typical Source-Drain Diode Forward Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 8 - Maximum Safe Operating Area

Document Number: 91250 S11-0441-Rev. B, 14-Mar-11



Vishay Siliconix




Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case

### Vishay Siliconix






Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms





Fig. 12c - Maximum Avalanche Energy vs. Drain Current










Fig. 13b - Gate Charge Test Circuit

www.vishay.com 6 Document Number: 91250 S11-0441-Rev. B, 14-Mar-11





#### Peak Diode Recovery dV/dt Test Circuit



a. V<sub>GS</sub> = 5 V for logic level devices

Fig. 14 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <u>www.vishay.com/ppg?91250</u>.

Document Number: 91250 S11-0441-Rev. B, 14-Mar-11 www.vishay.com



# TO-247AC (High Voltage)

#### VERSION 1: FACILITY CODE = 9





Section C--C, D--D, E--E

	MILLIN	IETERS	
DIM.	MIN.	MAX.	NOTES
А	4.83	5.21	
A1	2.29	2.55	
A2	1.50	2.49	
b	1.12	1.33	
b1	1.12	1.28	
b2	1.91	2.39	6
b3	1.91	2.34	
b4	2.87	3.22	6, 8
b5	2.87	3.18	
С	0.55	0.69	6
c1	0.55	0.65	
D	20.40	20.70	4

	MILLIN	IETERS	
DIM.	MIN.	MAX.	NOTES
D1	16.25	16.85	5
D2	0.56	0.76	
E	15.50	15.87	4
E1	13.46	14.16	5
E2	4.52	5.49	3
е	5.44	BSC	
L	14.90	15.40	
L1	3.96	4.16	6
ØP	3.56	3.65	7
Ø P1	7.19	) ref.	
Q	5.31	5.69	
S	5.54	5.74	

#### Notes

- <sup>(1)</sup> Package reference: JEDEC<sup>®</sup> TO247, variation AC
- (2) All dimensions are in mm
- <sup>(3)</sup> Slot required, notch may be rounded
- <sup>(4)</sup> Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm per side. These dimensions are measured at the outermost extremes of the plastic body
- <sup>(5)</sup> Thermal pad contour optional with dimensions D1 and E1
- (6) Lead finish uncontrolled in L1
- (7) Ø P to have a maximum draft angle of 1.5° to the top of the part with a maximum hole diameter of 3.91 mm
- (8) Dimension b2 and b4 does not include dambar protrusion. Allowable dambar protrusion shall be 0.1 mm total in excess of b2 and b4 dimension at maximum material condition

For technical questions, contact: <u>hvm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



#### VERSION 2: FACILITY CODE = Y



	MILLIN	IETERS	
DIM.	MIN.	MAX.	NOTES
A	4.58	5.31	
A1	2.21	2.59	
A2	1.17	2.49	
b	0.99	1.40	
b1	0.99	1.35	
b2	1.53	2.39	
b3	1.65	2.37	
b4	2.42	3.43	
b5	2.59	3.38	
с	0.38	0.86	
c1	0.38	0.76	
D	19.71	20.82	
D1	13.08	-	

	MILLIN	IETERS	
DIM.	MIN.	MAX.	NOTES
D2	0.51	1.30	
E	15.29	15.87	
E1	13.72	-	
е	5.46	BSC	
Øk	0.2	254	
L	14.20	16.25	
L1	3.71	4.29	
ØΡ	3.51	3.66	
Ø P1	-	7.39	
Q	5.31	5.69	
R	4.52	5.49	
S	5.51	BSC	

#### Notes

- <sup>(1)</sup> Dimensioning and tolerancing per ASME Y14.5M-1994
- <sup>(2)</sup> Contour of slot optional
- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- <sup>(4)</sup> Thermal pad contour optional with dimensions D1 and E1
- <sup>(5)</sup> Lead finish uncontrolled in L1
- <sup>(6)</sup> Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- <sup>(7)</sup> Outline conforms to JEDEC outline TO-247 with exception of dimension c



#### VERSION 3: FACILITY CODE = N



	MILLIN	IETERS		MILLIN	IETERS
DIM.	MIN.	MAX.	DIM.	MIN.	MAX.
А	4.65	5.31	D2	0.51	1.35
A1	2.21	2.59	E	15.29	15.87
A2	1.17	1.37	E1	13.46	-
b	0.99	1.40	е	5.46	BSC
b1	0.99	1.35	k	0.:	254
b2	1.65	2.39	L	14.20	16.10
b3	1.65	2.34	L1	3.71	4.29
b4	2.59	3.43	N	7.62	BSC
b5	2.59	3.38	Р	3.56	3.66
С	0.38	0.89	P1	-	7.39
c1	0.38	0.84	Q	5.31	5.69
D	19.71	20.70	R	4.52	5.49
D1	13.08	-	S	5.51	BSC

Notes

<sup>(1)</sup> Dimensioning and tolerancing per ASME Y14.5M-1994

<sup>(2)</sup> Contour of slot optional

(3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body

<sup>(4)</sup> Thermal pad contour optional with dimensions D1 and E1

<sup>(5)</sup> Lead finish uncontrolled in L1

<sup>(6)</sup> Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.