

承認書

SPECIFICATION FOR APPROVAL

CUSTOMER: 铭易轩

DESCRIPTION: COMMON MODE CHOKE

DDY PART NO: WBA4532L系列

CUSTOMER MODEL NO: _____

DRAWING		
MADE	CHECKED	APPROVED
聂旭彬	黄志伟	陈启善
DATE:	2021年8月26日	

CUSTOMER APPROVE




惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD

廣東省博羅縣洲際工業園梅園三路
NO.3 MEI YUAN ROAD,ZHOU JI INDUSTRIAL AREA,BOLUO COUNTY GUANGDON

傳真：0752-6207969

郵編：516100

Http://ddycoils.com




惠州市德立电子有限公司

HUIZHOU DELI ELECTRONICS CO., LTD

CUSTOMER:		REV NO:	A1.0
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 1 OF 6
PART NO:	WBA4532L系列	SN.	
CUSTOMER NO:		DATE:	2021年8月26日

CATALOG


Resume	P2
Shape & Dimension	P3
Characteristic	P3
Part numbering system	P3
General specification	P3
Electrical Characteristics List	P4
Soldering Conditions	P5
Package Information	P6



CUSTOMER:		REV NO:	A1.0
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 3 OF 6
PART NO:	WBA4532L系列	SN.	
CUSTOMER NO:		DATE:	2021年8月26日

1. SHAPE & DIMENSION

UNIT:mm



CODE	A	B	C	D1	D2	E
DIMENSION	4.50±0.20	3.20±0.20	2.80±0.2	1.00 Typ.	1.20Typ.	0.50Typ.

2. PART NUMBERING SYSTEM


WBA □□□□ □ □□□ □ □ — □ — □□
 1 2 3 4 5 6 7 8

- 1 PRODUCT SYMBOL (产品代号)
- 2 DIMENSIONS (规格尺寸)
- 3 MATERIAL (芯片类型)
- 4 INDUCTANCE VALUE (感量)
- 5 TOLERANCE (公差) : +50%/-30%(省略不标识)
- 6 PACKAGING (包装方式) : T-编带盘装; B-散装
- 7 INTERNAL CODE (内部代码) : 无特殊要求, 缺省此项
- 8 E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

3. GENERAL SPECIFICATION

- a. Rating DC current: Temperature rise(ΔT) is 40°C approximately at Irms
- b. Operating temp.: -40°C ~ +85°C
- c. Storage temp.: -10°C ~ +40°C R.H.: 65% Max
- d. Moisture sensitivity level (MSL) 2 (1 year floor life at <30°C/65% relative humidity)

APPROVED BY	CHECKED BY	DRAFT
陈启善	黄志伟	聂旭彬




惠州市德立电子有限公司

HUIZHOU DELI ELECTRONICS CO., LTD


CUSTOMER:		REV NO:	A1.0
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 4 OF 6
PART NO:	WBA4532L系列	SN:	
CUSTOMER NO:		DATE:	2021年8月26日

4. Electrical Characteristics List

NO.	Part Number	Z (Ω)	L (μH)	Rdc	Idc	Rated Voltage	Insulation Resistance
		10MHz	100KHz/0.1V	(Ω)Max	(mA)Max	Volts	(MΩ) Min
1	WBA4532L110T-G-HF	300 min	11	0.6	360	50	10
		600 typ					
2	WBA4532L220T-G-HF	500 min	22	1	310	50	10
		1200 typ					
3	WBA4532L510T-G-HF	1000 min	51	1	230	50	10
		2800 typ					
4	WBA4532L101T-G-HF	2000 min	100	2	200	50	10
		5800 typ					
5	WBA4532L201T-G-HF	5000 min	200	4.5	100	50	10
		14000 typ					




APPROVED BY	CHECKED BY	DRAFT
陈启善	黄志伟	聂旭彬



CUSTOMER:		REV NO:	A1.0
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 5 OF 6
PART NO:	WBA4532L系列	SN.	
CUSTOMER NO:		DATE:	2021年8月26日

5. SOLDERING CONDITIONS


**Figure 1.
Re-flow Soldering
(Lead Free)**



Note:

- Preheat circuit and products to 150°C
- 260°C tip temperature (max)
- Reflow times: no more than 2 times
- Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

**Figure 2.
Hand Soldering**



Note:


- Use a 20 watt soldering iron with tip diameter of 1.0mm
- Limit soldering time to 3 sec.

6.MATERIAL LIST

NO	DESCRIPTION	DESCRIPTION	SUPPLIER	REMARK
1	Upper Plate	Ferrite	Flag Magnetic or equivalent	or equivalent
2	Core	Ferrite Core	Flag Magnetic	or equivalent
3	Wire	Enameled Copper Wire	Elektrisola	or equivalent

REMARK:

APPROVED BY	CHECKED BY	DRAWN BY
陈启善	黄志伟	聂旭彬



惠州市德立电子有限公司


HUIZHOU DELI ELECTRONICS CO., LTD

CUSTOMER:		REV NO:	A1.0
DESCRIPTION:	COMMON MODE CHOKE	PAGE NO:	PAGE 6 OF 6
PART NO:	WBA4532L系列	SN:	
CUSTOMER NO:		DATE:	2021年8月26日

6. PACKAGING(unit: mm)


Type	4532
Quantity	500

TAPING DRAWINGS




REEL DIMENSIONS(UNIT:mm)


	A	B	C	N	G
CF-12	178±2.0	22±2.0	12.5±1.5	98±2.0	12



LEADER AND BLANK PORTION



PEELLING OFF FORCE:0.05 to 0.7N in the direction show below.



注意:

此物料不涉及汽车或相关产品方面的应用，否则，由此引起的一切品质和责任问题，我司将概不承担。

APPROVED BY	CHECKED BY	DRAFT
陈启善	黄志伟	聂旭彬