




ABIDE BY ROHS




SECTION C-C




SECTION B-B

Specification :




- 1. Rating:  
Voltage : 12V AC/DC max., 2V DC min.  
Current : 10mA AC/DC max., 10µA DC min.
- 2. Contact Resistance : 100mΩ Max
- 3. Insulation Resistance : 100MΩ at 500V
- 4. Withstand Voltage : AC100V(50-60Hz) for 1 minute
- 5. Finishing: gold-plating for contact area;  
Nickle-plating all over;  
Sn-plating for Weld area;
- 6. Insertion Force : 3.0kgf max(match with Kailih Mx switch only and without controlling force could be after 100 cycles life).
- 7. Operating Life : 100 Cycles.



SECTION A-A



PCB LAYOUT



②	contact	2	Copper Alloy	plating gold		
①	Base	1	Nylon	Black		
ITEM	PART NAME	TER'NO	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE	DONGGUAN CITY KAIHUA ELECTRONICS CO.,LTD		
DRAWN			Tangjia	2017.07.06	Kailih	
CHECKED				TITLE: PG1511 KeySwitches Contact II		
APPROVALS				PART NO. CPG151101S11		
TOLERANCES ARE		30<L	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10<L	±0.20		DRAWING NO.	KHA-PG1511-094EN
		5<L	±0.15	±2'	PROJECT	
		L	±0.10	SHEET 1 OF 1		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	B	2019.01.03	Modified tolerance		Wu chuandong	
	A	2018.06.29	NEW			




**凱華電子**  
KAIHUA EEELETRONICS

Document Number:

**KH-PS1607-10**

# 产品规格书

## Product Specification



P/N: **CPG151101S11**

Title : **1511 Connector**

Rev.	ECN	Release and Revision Description:	Prepared By /Date:	Checked By/Date:	Approved By/Date:
<b>A</b>	_____	New releasing 初版发行	吴川东 2018-09-07	易平 2018-09-07	王锋 2018-09-07



P/N: CPG151101S11	DOC. No.: KH-PS1607-10	Rev.: A	Page: 2/10
----------------------	---------------------------	------------	---------------

## Content

### 目录

1. Scope/范围:.....	3
2. Product Application/产品应用 : .....	3
3. Technology Parameters/技术参数 .....	3
4. Ratings/额定性能要求.....	3
5. Electrical Performance/电气性能 .....	4
6. Mechanical Performance/机械性能.....	5
7. Environmental Performance/环境性能.....	6
8. Recommended PCB Layout/推荐的 PCB 安装焊盘规格 .....	9
9. Packaging/包装.....	9
10. Precaution/注意事项 .....	10



<b>P/N:</b> CPG151101S11	<b>DOC. No.:</b> KH-PS1607-10	<b>Rev.:</b> A	<b>Page:</b> 3/10
-----------------------------	----------------------------------	-------------------	----------------------

**1. Scope/范围:**

This Product Specification covers the requirement of Mechanical keyboard Connector switch on product performance, test methods and quality assurance provisions.  
本规格书内容涵盖机械键盘连接器产品的要求, 包括性能指标、测试方法及质量保证方面等。

**2. Product Application/产品应用:**

Mainly applied on computer keyboards, cash registers equipment and Man-Machine interface.


主要适用于电脑, 收银机, 工业设备和人机界面

**3. Technology Parameters/技术参数**

Ambient Humidity 工作湿度:	45~95% R.H.;
Operating Temperature Range 使用温度范围:	-10℃~+60℃;
Storage Temperature Range 保存温度范围:	-20℃~+70℃;
Normal Condition:	
Ambient temperature 环境温度:	20±2℃
Relative humidity 相对湿度:	85%±5% R.H.;
Air pressure 气压:	86~101KPa;
Contact Resistance 接触阻抗:	100 mΩ Max;
Solder Ability 可焊性:	260±5℃, 3±0.5s;
Withstand Soldering Temperature 耐焊接热:	260±5℃, 5±1s;

**4. Ratings/额定性能要求**

Rating Voltare 额定电压:	12V AC/DC max; 2V DC min
Rating Current 额定电流	10mA AC/DC max; 10uA DC min
InsulationResistance 绝缘电阻:	≥100MΩ/DC 500V;
Withstand Voltage 耐电压:	AC 100V 1 Minute;
Mechanical Life 机械寿命:	100Cycles .
Profile Dimensions /外形尺寸	





**5. Electrical Performance/电气性能**

Item 项目	Description 项目描述	Test Condition 测试条件	Requirement 规格要求
5.1	Contact Resistance 接触电阻	<p>Static load: (Operation force)x2, which is applied on the center of Switch stem. 静态负载: 动作力的 2 倍, 施加在手柄中心.</p> <p>Measurement tool: Contact resistance Meter. 测量工具: 微电流接触电阻计(1KHz, 20mV,5~50mA)</p>	<p>100mΩ Max 100mΩ 以下</p>
5.2	Insulation Resistance 绝缘电阻	<p>Apply a Voltage of DC 500 V for 1 minute, according to the below method. (1) Between terminals. (2) Between terminal and Body.</p> <p>输入 500V DC 电压 1 分钟, 按如下接触方法测试: (1) 端子与端子之间. (2) 端子与外壳之间.</p>	<p>100MΩ Min 100 兆欧以上</p>
5.3	Dielectric withstanding voltage 耐电压	<p>Apply a Voltage of AC 100 V (50~60Hz) for 1 minute, according to the below method. (1) Between terminals. (2) Between terminal and Body.</p> <p>输入 100V AC 电压 1 分钟, 按如下接触方法测试: (1) 端子与端子之间. (2) 端子与外壳之间.</p>	<p>No evidence of breakdown 无瞬断、击穿等破坏.</p>



**6. Mechanical Performance/机械性能**

Item 项目	Description 项目描述	Test Condition 测试条件	Requirement 规格要求
6.1	Insertion force 插入力	At 16in/minute.actuation speed	Insertion force (match with Kailh Mx switch only) 插入力 3KG max (仅与凯华 MX 开关匹配)
6.2	Life Test 寿命测试	(1) without load 无负载 (2) Mating force: Maximum value of operation force. 插入力: 操作力规格值的上限. (3) Cycles: 100 Min 操作次数: 100 次以上	Contact resistance: 1000 mΩ Max 接触电阻: 1000 毫欧以下 Bouncing: 10ms Max Insertion force: 3kg max 插入力: 3kg 最大。 bouncing time: ≤10ms。 触点抖动: ≤10ms, (match with Kailh Mx switch only)。 仅与凯华 MX 开关匹配)



**7. Environmental Performance/环境性能**

Item 项目	Description 项目描述	Test Condition 测试条件	Requirement 规格要求												
7.1	Cold test 耐寒性	(1) Temperature : - 20±2℃ 温度: - 20±2℃ (2) Duration of test: 48h 持续时间: 48 小时 (3) Take off a drop water 去掉水珠 (4) Standard conditions after test : 1h 试验后的放置条件: 1 小时	Contact resistance: 200mΩ Max 接触电阻 200mΩ 以下												
7.2	Heat test 耐热性	(1) Temperature : 70±2℃ 温度: 70±2℃ (2) Duration of test: 48h 持续时间: 48 小时 (3) Take off a drop water 去掉水珠 (4) Standard conditions after test : 1h 试验后的放置条件: 1 小时	Contact resistance: 200mΩ Max Shall meet : No. 6.2 接触电阻 200mΩ 以下 满足: No. 6.2												
7.3	Temperature cycle 温度循环	(1) Test cycles:20 cycles 试验周期: 20 个周期 (2) Standard condition after test:1h 试验后的放置条件: 1 小时 <table border="1" data-bbox="432 1346 987 1536"> <thead> <tr> <th></th> <th>Temperature 温度</th> <th>Duration of test 持续时间</th> </tr> </thead> <tbody> <tr> <td rowspan="4">1 cycle 一次循环</td> <td>20±5℃</td> <td>1h</td> </tr> <tr> <td>-20±5℃</td> <td>1h</td> </tr> <tr> <td>20±5℃</td> <td>1h</td> </tr> <tr> <td>70±5℃</td> <td>1h</td> </tr> </tbody> </table>		Temperature 温度	Duration of test 持续时间	1 cycle 一次循环	20±5℃	1h	-20±5℃	1h	20±5℃	1h	70±5℃	1h	Contact resistance: 200mΩ Max Shall meet : No. 6.2 接触电阻 200mΩ 以下 满足: No. 6.2
	Temperature 温度	Duration of test 持续时间													
1 cycle 一次循环	20±5℃	1h													
	-20±5℃	1h													
	20±5℃	1h													
	70±5℃	1h													
7.4	Soldering heat test 耐焊接热	Soldering area: T/2 of PWB thickness. (PWB: T=1.6mm) 焊接面积: 印刷基板的 1/2 厚度处 Soldering temperature: 260±5℃ Soldering time: 5±0.5s 焊接温度: 260±5℃ 焊接时间: 5±0.5 秒	Appearance: No abnormality. 外观无异常												




7.5

Solderability  
可焊性

- Hand soldering 手工焊接:  
Please practice according to below condition:  
(1) Soldering Temperature :  $350 \pm 5^{\circ}\text{C}$   
焊接温度:  $350 \pm 5^{\circ}\text{C}$   
(2) Continual soldering time:  $3 \pm 0.5\text{s}$   
连续焊接时间:  $3 \pm 0.5$  秒  
(3) Capacity of soldering iron:  $\leq 20\text{w}$   
电烙铁功率: 20 瓦以下
- Automatic Reflow soldering 自动回流焊接:  
For the product of SMT, according to below condition:

SMT 回流焊温度曲线图



At least 95% of surface area of immersed portion shall be covered by solder.  
侵焊面积大于 95%以上。

7.6

Humidity test  
耐湿性

- Temperature :  $60 \pm 2^{\circ}\text{C}$   
温度:  $60 \pm 2^{\circ}\text{C}$
- relative humidity: 90~95% R.H.  
相对湿度: 90~95% R.H.
- Duration of test: 48h  
持续时间: 48 小时
- Take off a drop water  
去掉水珠
- Standard conditions after test: 1h  
试验后的放置条件: 1 小时

Contact resistance:  
 $200\text{m}\Omega$  Max  
Shall meet :  
No. 6.2  
接触电阻  $200\text{m}\Omega$  以下  
满足:  
No. 6.2






7.7	Salt Spray 盐雾测试	Apply the following environment to test: 根据下列条件进行测试:  (1) Temperature : 35±5℃ 温度: 35±5℃; (2) Salt water density: 5±1% 盐水浓度: 5±1%; (3) Duration: 12 hours 持续时间: 12 小时; (4) After test, the salt deposit shall be removed by running water. 实验后将盐沉积物用水冲掉	Appearance: No corrosion spot, no crack, no base plate naked. 外观: 无腐蚀点, 无裂纹, 无裸露基材.  Contact Resistance: 200 mΩ Max 接触电阻: 200 毫欧以下
7.8	Withstand K <sub>2</sub> S 硫化测试	Apply the following environment to test: 根据下列条件进行测试  (1) Temperature: 35±5℃ 温度: 35±5℃ (2) K <sub>2</sub> S Density: 2%; 硫化钾浓度: 2% (3) Duration: 2 minute. 持续时间: 2 分钟	Appearance: No corrosion spot, no crack, no base plate naked. 外观: 无腐蚀点, 无裂纹, 无裸露基材.  Contact Resistance: 1000 mΩ Max 接触电阻: 1000 毫欧以下



**8. Recommended PCB Layout 推荐的 PCB 安装焊盘规格**

(Top View)  
(Single face board T=1.6mm)






PCB LAYOUT

**9. Packaging 包装**

Packaging type: 13Tray, 26000Pcs/Carton.

包装方式:13 /盘, 26000Pcs/箱.



**10.Precaution 注意事项**

**10.1 Soldering condition 回流焊条件**

ITEM 项目		CONDITION 条件
Preheating zone 预热区	Heating zone 升温区	Speed <math>< 2^{\circ}\text{C}/\text{S}</math>, Preheating time 15 S Max, temperature 150°C 速度 <math>< 2^{\circ}\text{C}/\text{S}</math>, 预热时间 15 S 最多, 温度 150°C
	Heatpreservati on area 保温区	Speed 1.2~3.5°C/S, Preheating time 120 S Max, temperature 180°C 速度 1.2~3.5°C/S, 预热时间 120 S 最多, 温度 180°C



<b>P/N:</b> CPG151101S11	<b>DOC. No.:</b> KH-PS1607-10	<b>Rev.:</b> A	<b>Page:</b> 10/10
-----------------------------	----------------------------------	-------------------	-----------------------

	Fast heating zone 快速升温区	Speed 3.5~4.5°C/S, Preheating time 140 S Max, temperature 230°C 速度 3.5~4.5°C/S, 预热时间 140 S 最多, 温度 230°C
Weld area 焊接区		Welding time 40 S Max, welding temperature peak value, 3 sec Max. 焊接时间 40 S 最多, 焊接温度峰值 260°C 最大, 3 S 最多
Area of flux 助焊剂面积		1/2 Max of PWB Thickness 印刷基板厚度的 1/2 以内
Temperature of solder 焊锡温度		260±5°C 260±5°C
Number of soldering 焊接次数		2time Max (But should down heat of the first soldering) 2 次以内
Printed wiring board 印刷基板		Single side copper-clad laminates 单面铜箔

- (1) After reflow, be careful not to clean switches with solvent  
回流焊后, 注意不要用溶剂清洗.
- (2) Under the condition of using soldering iron, soldering temperature shall be 350°C max within 3 sec.  
在使用烙铁的情况下, 焊锡温度应在 350°C 以下, 焊接时间 3 秒以内.

**10.2 Notes 注意点**

- (1) Please be cautious not to give excessive static load connector.  
注意不要施加超负荷的压力或晃动连接器.
- (2) Connector be careful not to stack up P. W. B. after switches were soldered.  
连接器焊接以后, 印刷基板注意不要叠放.
- (3) Preservation under high temperature and high humidity or corrosive gas should be avoided  
Especially. When you need to preserve for a long period, do not open the carton.  
保管时尤其应注意避开高湿高温和有腐蚀性气体的环境. 如需长时间保存, 请不要打开包装箱.
- (4) Products meet the ROHS & REACH environmental management substances control standards  
产品满足 ROHS & REACH 环境管理物质管制标准



P/N: CPG151101S11	DOC. No.: KH-PS1607-10	Rev.: A	Page: 11/11
----------------------	---------------------------	------------	----------------

Temperature of solder 焊锡温度	260±5℃ 260±5℃
Number of soldering 焊接次数	2time Max (But should down heat of the first soldering) 2 次以内
Printed wiring board 印刷基板	Single side copper-clad laminates 单面铜箔

- (1) After reflow, be careful not to clean switches with solvent  
回流焊后,注意不要用溶剂清洗.
- (2) Under the condition of using soldering iron, soldering temperature shall be 350℃ max within 3 sec.  
在使用烙铁的情况下,焊锡温度应在350℃以下,焊接时间3秒以内.

### 10.2 Notes 注意点

- (1) Please be cautious not to give excessive static load connector.  
注意不要施加超负荷的压力或晃动连接器.
- (2) Connector be careful not to stack up P. W. B. after switches were soldered.  
连接器焊接以后,印刷基板注意不要叠放.
- (3) Preservation under high temperature and high humidity or corrosive gas should be avoided  
Especially. When you need to preserve for a long period, do not open the carton.  
保管时尤其应注意避开高湿高温和有腐蚀性气体的环境.如需长时间保存,请不要打开包装箱.
- (4) Products meet the ROHS & REACH environmental management substances control standards  
产品满足 ROHS & REACH 环境管理物质管制标准