

Features

- Fast, 91ns Propagation Delay
- 22uA (Typ.) Low Power Consumption
- Single-Supply Operation from +2.7V ~ +5.5V
- Low Offset Voltage: 5mV (Max.)
- Rail-to-Rail Input and Output
- CMOS/TTL-Compatible Output
- Internal Hysteresis for Clean Switching

Small Package:

GS8746 Available in SOT23-5 and SC70-5 Packages GS8747 Available in SOT23-5 and SC70-5 Packages GS8748 Available in SOP-8 and MSOP-8 Packages

No Phase Reversal for Overdriven Inputs

Operating Temperature: -40°C ~ +85°C

General Description

The GS8746 family are low-power, high-speed comparators with internal hysteresis, optimized for systems powered from a 3V or 5V supply. The device features high-speed response, low-power consumption, low offset voltage, and rail-to-rail input and output range. Propagation delay is 91ns (100mV overdrive), while supply current is 22uA per comparator. The internal input hysteresis eliminates output switching due to internal input noise voltage. The maximum input offset voltage is 5mV, and the operating range is from 2.7V to 5.5V.

All devices are specified for the temperature range of -40°C to +85°C. The GS8746 and GS8747 single is available in Green SC70-5 and SOT23-5 packages. The GS8748 Dual is available in Green SOP-8 and MSOP-8 packages.

Applications

- Line Receivers
- Battery-Powered Systems
- Threshold Detectors/Discriminators

- 3V/5V Systems
- Zero-Crossing Detectors
- Sampling Circuits





Figure 1. Pin Assignment Diagram





Absolute Maximum Ratings

Condition	Min	Max	
Power Supply Voltage (V _{DD} to Vss)	-0.5V	+7.5V	
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	V _{DD} +0.5V	
PDB Input Voltage	Vss-0.5V	+7V	
Operating Temperature Range	-40°C	+85°C	
Junction Temperature	+160	0°C	
Storage Temperature Range	-55°C	+150°C	
Lead Temperature (soldering, 10sec)	+260°C		
Package Thermal Resistance (T _A =+25°C)			
SOP-8, θ _{JA}	125°C/W		
MSOP-8, θ _{JA}	216°C/W		
SOT23-5, θ _{JA}	190°C/W		
SC70-5, θ _{JA}	333°C/W		
ESD Susceptibility			
НВМ	4KV		
MM 300V		V	

Note: Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.







Package/Ordering Information

MODEL	CHANNEL	ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION	MARKING INFORMATION
000740	Cinale	GS8746-CR	SC70-5	Tape and Reel,3000	8746
GS8746 Single	GS8746-TR	SOT23-5	Tape and Reel,3000	8746	
000747		GS8747-CR	SC70-5	Tape and Reel,3000	8747
GS8747 Single	GS8747-TR	SOT23-5	Tape and Reel,3000	8747	
000740		GS8748-SR	SOP-8	Tape and Reel,4000	GS8748
GS8748 Dual	GS8748-MR	MSOP-8	Tape and Reel,3000	GS8748	









Electrical Characteristics

(At Vs = +5V, VcM = 0V, CL = 15pF, and TA = +25°C	, unless otherwise noted.)
---	----------------------------

			GS8743/8744/8745			
PARAMETER	SYMBOL	CONDITIONS	ТҮР	MIN	МАХ	UNITS
INPUT CHARACTERISTICS	1	l		•	1	
Input Offset Voltage	V _{os}	V _{CM} = 0V	0.4		5	mV
Input Bias Current	IB		6			pА
Input Offset Current	I _{OS}		4			pА
Input Hysteresis	V _{hys}		2.6			mV
Common-Mode Voltage Range	V _{CM}	V _S = 5.5V	-0.1 to +5.6			V
Common-Mode Rejection Ratio	CMRR	$V_{\rm S}$ = 5V, $V_{\rm CM}$ = 0V to 5V	77	60		dB
OUTPUT CHARACTERISTICS		·				
Output Maltana Output from Dail	V _{OH}		Vs - 0.200		Vs - 0.275	V
Output Voltage Swing from Rail	Vol	vs=5v, i _o = 4mA	159		222	mV
	ISOURCE		35.4	22.5		mA
Output Snort-Circuit Current	I _{SINK}	$V_{\rm S} = 5V$, Out to $V_{\rm S}/2$	36.3	25.5		
POWER SUPPLY				_		
			2.7			V
Operating voltage Range			5.5			V
Power Supply Rejection Ratio	PSRR	$V_{\rm S}$ = +2.7V to +5.5V, $V_{\rm CM}$ = 0V	71	58		dB
Quiescent Current / Comparator	Ι _Q	V _S = +3V	22			uA
DYNAMIC PERFORMANCE (CL	= 15pF)					
	T _{dLH}	V _S = 3V, Overdrive = 10mV	173			ns
Propagation Delay (Low to High)		V _S = 3V, Overdrive = 100mV	91			ns
Deen en effere Deleve (High te Leve)	T _{dHL}	V _S = 3V, Overdrive = 10mV	206		1	ns
Propagation Delay (High to Low)		V _S = 3V, Overdrive = 100mV	64			ns
	Tr	V _S = 3V, Overdrive = 10mV	7.6			ns
Rise lime		V _S = 3V, Overdrive = 100mV	7.5			ns
	T _f	$V_{S} = 3V$, Overdrive = 10mV	6.5			ns
Fall Time		V _S = 3V, Overdrive = 100mV	6.4			ns







Typical Performance characteristics



Vour(1V/div) V_{IN}(100mV/div)

Sinusoid Response at 0.5MHz

Time(1us/div)

Output Short-Circuit (Source) Current vs. Temperature



Output Short-Circuit (Sink) Current vs. Temperature



l_{sınk}(5mA/div)







Typical Performance characteristics

At T_A =+25°C, V_S =+3V, and C_L =15pF, unless otherwise noted.









Application Note

Size

GS8746 family series comparators are low-power, high-speed and suitable for a wide range of general-purpose applications. The small footprints of the GS8746 family packages save space on printed circuit boards and enable the design of smaller electronic products. The GS8746 family interfaces directly to CMOS and TTL logics.

Power Supply Bypassing and Board Layout

GS8746 family series operates from a single 2.7V to 5.5V supply or dual $\pm 1.35V$ to $\pm 2.75V$ supplies. For best performance, a 0.1µF ceramic capacitor should be placed close to the V_{DD} pin in single supply operation. For dual supply operation, both V_{DD} and V_{SS} supplies should be bypassed to ground with separate 0.1µF ceramic capacitors.

Low Supply Current

The low supply current (typical 22uA per channel) of GS8746 family will help to maximize battery life. They are ideal for battery powered systems.

Operating Voltage

GS8746 family operates under wide input supply voltage (2.7V to 5.5V). In addition, all temperature specifications apply from -40 °C to +85 °C. Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-lon battery lifetime

Rail-to-Rail Input

The input common-mode range of GS8746 family extends 100mV beyond the supply rails (V_{SS} -0.1V to V_{DD} +0.1V). This is achieved by using complementary input stage. For normal operation, inputs should be limited to this range.

Internal Hysteresis

Because of noise or undesired parasitic feedback, high-speed comparators oscillate in the linear region. Oscillation tends to occur when the voltage on one input is at or equal to the voltage on the other input. The GS8746 family eliminates this undesired oscillation by integrating an internal hysteresis of 2.6mV.

The hysteresis in a comparator creates two trip points: one for the rising input voltage and one for the falling input voltage (Figure 1). The difference between two trip points is the hysteresis, while the average of two trip points is the offset voltage. When the comparator's input voltages are equal, the hysteresis effectively causes one comparator input voltage to move quickly past the other, thus taking the input out of the region where oscillation occurs.



Figure 1. Comparator's hysteresis and offset

External Hysteresis

Greater flexibility in selecting hysteresis is achieved by using external resistors. Hysteresis reduces output chattering when one input is slowly moving past the other.







Non-Inverting Comparator with Hysteresis



Figure 2. Non-Inverting Comparator with Hysteresis

A non-inverting comparator with hysteresis requires a two-resistor network, as shown in Figure 2 and a voltage reference (V_R) at the inverting input.

$$\begin{split} \mathbf{V}_{\mathrm{TH}} &= \frac{R_{\mathrm{G}} + R_{\mathrm{F}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{R}} \\ \mathbf{V}_{\mathrm{TL}} &= \frac{R_{\mathrm{G}} + R_{\mathrm{F}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{R}} - \frac{R_{\mathrm{G}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{DD}} \\ \mathbf{V}_{\mathrm{HYS}} &= \frac{R_{\mathrm{G}}}{R_{\mathrm{F}}} \times \mathbf{V}_{\mathrm{DD}} \end{split}$$

Inverting Comparator with Hysteresis



Figure 3. Inverting Comparator with Hysteresis

The inverting comparator with hysteresis requires a three-resistor network that is referenced to the comparator supply voltage (V_{DD}) , as shown in Figure 3.

$$\begin{aligned} \mathbf{V}_{\text{TH}} &= \frac{R_{\text{G2}}}{R_{\text{G1}} \parallel R_{\text{F}} + R_{\text{G2}}} \times \mathbf{V}_{\text{DD}} \\ \mathbf{V}_{\text{TL}} &= \frac{R_{\text{G2}} \parallel R_{\text{F}}}{R_{\text{G2}} \parallel R_{\text{F}} + R_{\text{G1}}} \times \mathbf{V}_{\text{DD}} \\ \mathbf{V}_{\text{HYS}} &= \frac{R_{\text{G1}} \parallel R_{\text{G2}}}{R_{\text{G1}} \parallel R_{\text{G2}} + R_{\text{F}}} \times \mathbf{V}_{\text{DD}} \end{aligned}$$







Typical Application Circuits

Line Receiver

A Line Receiver using GS8746 family is shown in Figure 4. Resistors R_{G1} and R_{G2} set the bias point at the comparator's inverting input. R_{IN} should be same as $R_{G1}||R_{G2}$ to get a better match. GS8746 family detects the voltage of the Coax Line, and outputs logic high or logic low quickly with no glitch.



Figure 4. Line Receiver

IR Receiver

GS8746 family is an ideal candidate to be used as an infrared receiver shown in Figure 5. The infrared photo diode creates a current relative to the amount of infrared light present. The current creates a voltage across R_{IN} . When this voltage level cross the voltage applied by the voltage divider to the inverting input, the output transitions. Optional R_F provides additional hysteresis for noise immunity.



Figure 5. IR Receiver







Oscillator

A oscillator using GS8746 family is shown in Figure 6. Resistors R_{G1} and R_{G2} set the bias point at the comparator's inverting input. The period of oscillator is set by the time constant of R_C and C_{IN} . The maximum frequency is limited by the large signal propagation delay of the comparator. GS8746 family's low propagation delay guarantees the high frequency oscillation. If $R_{G1}=R_{G2}=R_F$, then the frequency of the oscillator is:





Figure 6. Oscillator







Package Information

MSOP-8







Symbol	Dimensions In Millimeters		Dimensions In Inches	
-,	MIN	MAX	MIN	MAX
А	0.820	1.100	0.032	0.043
A1	0.020	0.150	0.001	0.006
A2	0.750	0.950	0.030	0.037
b	0.250	0.380	0.010	0.015
с	0.090	0.230	0.004	0.009
D	2.900	3.100	0.114	0.122
E	2.900	3.100	0.114	0.122
E1	4.750	5.050	0.187	0.199
e	0.650 BSC		0.026	BSC
L	0.400	0.800	0.016	0.031
θ	0°	6°	0°	6°







SOP-8





Symbol	Dimensions In Millimeters		Dimensions In Inches	
-	MIN	MAX	MIN	MAX
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
с	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.27 BSC		0.050 BSC	
L	0.400	1.270	0.016	0.050
6	0°	8°	0°	8°

 $\begin{bmatrix} A1^{J} \\ A2^{J} \end{bmatrix}$







SOT23-5







L

Symbol	Dimensions In Millimeters		Dimensions In Inches	
-,	MIN	MAX	MIN	MAX
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
с	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950 BSC		0.037	BSC
e1	1.900 BSC		0.075 BSC	
L	0.300	0.600	0.012 0.024	
θ	0°	8°	0° 8°	







SC70-5





GS8746/8747/8748

	Dimensions		Dimensions	
Symbol	In Millimeters		In Inches	
	Min	Мах	Min	Max
А	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
С	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
e	0.650TYP		0.026TYP	
e1	1.200	1.400	0.047	0.055
L	0.525REF		0.021R	EF
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°





