

深圳市索瑞达电子有限公司

承 认 书 SPECIFICATION FOR APPROVAL

客户名称: Customer Name:	GSLC1712	
客户料号: Customer P/N:	C2942325	
产 品 名 称 : Product Name:	功率电感	
索瑞达料号: Sorede P/N:	SDRH.1209.LF330MT00	





地址:深圳市观澜镇福城街道新塘村8号源创园陆号A6栋3楼.

Address: 3Rd Floor, Building A6, Yuanchuangyuanlu, No. 8 Xintang Village, Fucheng Street, Guanlan Town, Shenzhen.

电话 Tel: 0755-29803356 传真 Fax: 0755-29803506

电子邮件 E-mail: sorde@vip.163.com

网址 http://www.szsorede.com


修改履历表

Modify Resume

	Wiodity Resume	
修改日期	修改明细	修改后版本号
Date modified	Modify Details	Version No.
2022-03-01	文件新制订 File formulation	A
	<u> </u>	

文件编号	SRD-WI-15691	版本号	A	页码	1/8
File Number		Version Number		page	

1、外形尺寸 Dimension:



A	12.0±0.3
В	12.0±0.3
С	10.0Max
D	7.6±0.2
Е	5.0 Ref.
F	2.8 Ref.
G	7.0 Ref.
Н	5.4 Ref.

单位Unit: mm

2、产品品名构成 Product Spec. Model


<u>SDRH</u>. <u>1209</u>. <u>L</u>. <u>F</u> <u>330</u> <u>M</u> <u>T</u> <u>00</u> a b c d e f g h

- a: 系列名称Series name
- b: 产品尺寸Product dimensions (A x B x C)
- c: 密封方式Sealing way (L: 冷封Cold seal Y: 热封Heat seal)
- d: 印字方向 Lettering direction ▶
- e: 电感值Inductance Value

(1R0:1.0uH; 100: 10uH; 101:100uH)

- f: 电感公差Inductance Tolerance (K:10%; M:20%; N:30%)
- g: 包装Package(T:磁带/卷轴Tape/Reel、B: 散装Bulk)
- h: 编号Numbering (标准standard)

► Lettering direction



3、材料清单MATERIAL LIST

NO.	PARTS	MATERIAL SPECIFICATIONS	UL FILE NO.	TEMP. CLASS
1	CORE	DR 10*9.0 B:6.5 F:6.5 RI 12.2*8.8*10.85 OR EQUIVALENT	NA	NA
2	WIRE	G1 P180 OR EQUIVALENT	E258243	180°C
3	ADHESIVE	G500, 602H-6-5 OR EQUIVALENT	NA	NA
4	BASE	C-1200MS-5 P1	NA	NA
5	SOLDER	Sn99.3-Cu0.7 OR EQUIVALENT	NA	NA

^{*}NA:NOT APPLICABLE.

文件编号	SRD-WI-15691	版本号	A	页码	2/8
File Number		Version Number		page	

4、电性能参数表 Electrical Characteristics List

現務型号	4、电性能参数表 Elec	uricai Character	ISUCS LIST		
SDRH.1209.LF330MT00 33 100/0.25 0.053 4.25			测试频率 Test Freq. (kHz/v)	DCR	饱和电流 Isat (A)
	SDRH.1209.LF330MT00	33	100/0.25	0.053	4.25

[※]公差Tolerance: N:±30%、M:±20%、K:±10%.

Isat电流:指使电感量比初始值下降25%Max (The rated DC current is that which cause at 25%Max inductance reduction from the initial value)。


[※]工作温度Operating temperature rang: -40 $^{\circ}$ C to +105 $^{\circ}$ C (Including Self-heating)

[※]储存温度Storage termperature rang: -40 ℃ to +125℃

	文件编号	SRD-WI-15691	版本号	A	页码	3/8
F	ile Number	3165 10091	Version Number	7 1	page	


5、产品包装 Packaging

1) 载带包装示意图 Tape packing diagram




Series	A0	В0	W	E	F	∮ f
Series	12.6±0.1	12.6±0.1	24.0±0.3	11.5±0.1	1.75±0.1	1.5±0.1
CDDU 1200 LE	Р	P1	P2	K0	Т	
SDRH.1209.LF	16.0±0.1	4.0±0.1	2.0±0.1	10.3±0.1	0.40±0.1	

2)卷盘包装示意图 Tape packing diagram



А	330±0.5		
В	100±0.5		
С	13.5±0.5		
W	24.5±0.5		

3) 卷盘包装示意图 Tape packing diagram




文件编号	SRD-WI-15691	版本号	A	页码	4/8
File Number		Version Number		nage	


4) 剥离强度要求Peeling required

①F 力大小: 20~100g;

②面带剥离角度: 165°~180°。



5) 包装数量 Packing quantity



项目 (Project)	数量(PCS)	尺寸规格(Size:mm)
盘(Reel)	350	13"
内盒 (Inner box)	700	340mm*340mm*65mm
外箱 (Out box)	2100	360mm*360mm*225mm

文件编号 File Number	SRD-WI-150	691	版本号 Version Number	A	页码 page	5/8		
6.RELIABILI	TY TEST METHOD				1 0			
MECHANICA								
TESTITEM	SPECIFICATION	TEST DETAILS						
Substrate bend	ir △ L/Lo≦±5%	onto the printed o	circuit board					
		in figure 1 and a load applied unitil the figure in the arrow						
	There shall be	direction	is made approximate	ely 3mm.(keep tin	ne 30 seconds)			
	no mechanical	PCB din	nension shall the pag	e 7/9				
damage or elec- F(Pressurization)								
	trical damege.							
			251	<u> </u>				
			R5 45±2	2 45±2				
				. -	- ⊢ 1 20			
					10			
			PRESSURE I figure-1	ROD	D0.10			
					R340			
Vibration	△ L/Lo ≦ ±5%	The sam	nple shall be soldered	onto the printed o	eircuit hoard			
Vibration	Z 2720 = 20 70		en a vibration having a	·				
	There shall be		•	•				
There shall be and a frequency of from 10 to 55Hz/1 minute repeated should no mechanical be applied to the 3 directions (X,Y,Z) for 2 hours each.								
	damage.	(A total of 6 hours)						
			,					
Solderability	New solder	Flux (rosin, isopropyl alcohol{JIS-K-1522}) shall be coated						
More than 90% over the whole of the sample before hard, the sample shall								
	then be preheated for about 2 minutes in a temperature of							
130∼150°C and after it has been immersed to a depth 0.5r								
		below for 3±0.2 seconds fully in molten solder M705 with						
		a temperature of 245±2℃.						
More than 90% of the electrode sections shall be couered								
	with new solder smoothly when the sample is taken out of							
		the sold	er bath.					

文件编号	SRD-WI-15691	版本号		页码	6/8
File Number	SKD-W1-13091	Version Number	A	page	0/8

File Number	SIGD WI 13071	Version Number	A	page	0,0		
MECHANIC	AL						
TEST ITEM	SPECIFICATION						
Resistance to	There shall be Temperature profile of reflow soldering						
Soldering heat	no damage or						
(reflow soldering)	problems.	150	Pe-heating 2 min passed through the above profile for 1 stored at standard	(Store temper) 10 sec. 2 min. on the reflow oven with time. rd atmospheric co	th the		
ELECTRICA	L						
TEST ITEM	SPECIFICATION		TEST DETAI	LS			
	There shall be no other	Do 400\/ #					

TEST ITEM	SPECIFICATION	TEST DETAILS
Insulation	There shall be no other	DC 100V voltage shall be applied across this sample of top
resistance	damage or problems.	surface and the terminal.
		The insulation resistance shall be more than 1 \times 10 ⁸ Ω .
Dielectric	There shall be	AC 100V voltage shall be applied for 1 minute acrosset the top
withstand	no other	surface and the terminal of this sample
voltage	damage or	
	problems.	
Temperature	△ L/L20°C ≦ ±10%	The test shall be performed after the sample has stabilized in
characteristics	0~2000 ppm/℃	an ambient temperature of - 40 to + 105℃ ,and the value
		calculated based on the value applicable in a normal
		temperature and narmal humidity shall be △L/L 20℃ ≦± 10%.

文件编号 File Number	SRD-WI-1:	5691	版本号 Version Number	A	页码 page	7/8				
FNVIROME	NT CHARAC	TEDISTI	rs	l	1 0	1				
TEST ITEM	INT CHAIRAG	ILINOTI	SPECIFIC	CATION						
High temperature	△L/Lo≦±5%	The sample shall be left for 500hours in an atmospere with								
storage		a tempera	a temperature of 105±2℃ and a normal humidity.							
	There shall be	Upon completion of the measurement shall be made after the								
	no mechanical	sample has been left in a normal temperature and normal								
	damage.	humidity f	humidity for 1 hour.							
Low temperature	△ L/Lo≦ ±5%	The samn	le shall be left for 500	hours in an atmosp	here with					
storage	Z L/L0 = 15 /6			nours in an atmosp	nere with					
Storage	There shall be	a temperature of -40±3°C.								
	no mechanical	Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and								
	damage.	normal humidity for 1 hour.								
Change of	△L/Lo≦±5%			5 continuos cycles	such as shown					
temperature		The sample shall be subject to 5 continuos cycles, such as shown in the table 2 below and then it shall be subjected to standard								
	There shall be	stmospheric conditions for 1 hour, after which measurement								
	no other dama-	shall be made.								
	ge of problems									
		table 2								
				table 2						
			Temperatur	1	Duration					
			Temperatur 1 −40±3°C	1	Duration 10 min.					
				е						
			1 −40±3°C	e o. 1)						
			1 — 40±3℃ (Themostat N	e o. 1) 5 s	10 min.					
			1 — 40±3℃ (Themostat N 2 Standard	e	10 min. ec. or less					
			1 — 40±3℃ (Themostat N 2 Standard atmospheric	e	10 min. ec. or less o.1→No.2					
			1 — 40±3°C (Themostat N 2 Standard atmospheric 3 105±2°C	e	10 min. ec. or less o.1→No.2					
			1 — 40±3°C (Themostat No.) 2 Standard atmospherical 3 105±2°C (Themostat No.)	e	10 min. ec. or less p.1→No.2 30 min.					
			1 — 40±3℃ (Themostat N 2 Standard atmospheric 3 105±2℃ (Themostat N 4 Standard	e	10 min. ec. or less o.1→No.2 30 min. ec. or less					
Moisuture storage	△L/Lo≦±5%	The samp	1 — 40±3℃ (Themostat N 2 Standard atmospheric 3 105±2℃ (Themostat N 4 Standard	e	10 min. ec. or less 5.1→No.2 30 min. ec. or less 5.2→No.1					
Moisuture storage	△L/Lo≦±5%		1 — 40±3℃ (Themostat N 2 Standard atmospheric 3 105±2℃ (Themostat N 4 Standard atmospheric	e o.1) 5 s c No o.2) 5 s c No hours in a temperat	10 min. ec. or less 5.1→No.2 30 min. ec. or less 5.2→No.1					
Moisuture storage	△L/Lo≦±5% There shall be	40±2℃ ar	1 — 40±3℃ (Themostat N 2 Standard atmospheric 3 105±2℃ (Themostat N 4 Standard atmospheric	e	10 min. ec. or less b.1→No.2 30 min. ec. or less b.2→No.1					
Moisuture storage		40±2℃ ar	1 — 40±3°C (Themostat Note: 100 of 90 of	e o.1) 5 s c No o.2) 5 s c No hours in a temperat 0~95%.	10 min. ec. or less b.1→No.2 30 min. ec. or less b.2→No.1					

The sample shall be reflow soldered onto the printed circuit board in every test.

文件编号		SRD-WI-15691	版本号	А	页码	8/8
File Numb	er	2161 10 09 1	Version Number	71	page	

7、注意事项 Note

①本承认书保证我司产品作为一个单体时的质量情况。当我司产品被安装到贵司产品上时,请保证 贵司的产品已根据贵司的规范进行了有效评估和确认。

This product specification guarantees the quality of our product as a single unit. Please make sure that your product is evaluated and confirmed against your specifications when our product is mounted to your product.

②如果贵司对我司产品的使用已超过了本承认书所界定的产品功能,那么对于由此引发的失效, 我司将不予保证。

We cannot warrant against failure caused by any use of our product that deviates from the intended use as described in this product specification.

- ③为了保持终端电极的焊接性,并使包装材料保持良好状态,必须控制储存区的温度和湿度。
 To maintain the solderabilty of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled.
 - ※建议的条件: -10~+40℃, 30~70%RH。

Recommended conditions: -10 \sim +40 $^{\circ}$ C, 30 \sim 70%RH.

※储存超过六个月的,应在实际使用前进行焊接检验。
In case of storage over 6 months, soldrability shall be checked before actual usage.

※即使在理想的储存条件下,产品的可焊性也随着时间的推移而降低。因此,产品应从交货时算起, 建议8个月之内使用完。

Even under ideal storage conditions, the weldability of the product decreases over time. therefore, the product should be From the time of delivery, it is recommended that it be used within 8 months.

④本承认书在客户收到30天之内,必须签章返回,逾期视为默认。

The Specification Approval should be sent back to the supplier with customer's chop on it within 30 days after receiving it, or we will take it as approved by customer's automatically.

⑤如有特殊规格要求,请事前联络我司技术部人员。

In case of special specifications please contact our technical department prior staff.