

## MUR1010CT THRU MUR1060CT

Ultra-Fast Recovery Rectifier Diodes

#### **Features**

- Super-fast recovery time for high efficiency
- Glass passivated chip junction
- Low leakage current
- High forward surge capability

### **Typical Application**


For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer ,computer and telecommunication.

#### **Mechanical Data**

 Package: TO-220AB
 Molding compound meets UL 94 V-0 flammability rating,RoHS-compliant

 Terminals: Tin plated leads, solderable per J-STD-002 and JESD22-B102

Polarity: Color Band denotes cathode end



■ Maximum Ratings (Ta=25°C Unless otherwise specified)

| PARAMETER                              | Symbol | Unit         | Conditions                                 | MUR-CT             |      |      |      |      |  |
|--|--------|--------------|--|--------------------|------|------|------|------|--|
| PARAMETER                              |        |              | Conditions                                 | 1010               | 1015 | 1020 | 1040 | 1060 |  |
| Repetitive Peak Reverse Voltage        | VRRM   | V            |  | 100                | 150  | 200  | 400  | 600  |  |
| Average Forward Current                | lo     | Α            | Half-sine wave, Resistance load, Ta(Fig 1) | 10                 |      |      |      |      |  |
| Surge(Nonrepetitive)Forward<br>Current | IFSM   | А            | 60HZ sine wave, 1 cycle,<br>Ta=25°C        | 55                 |      |      |      |      |  |
| Current Squared Time                   | l² t   | A²s          | 1ms≤t<8.3ms<br>Tj=25°C,Rating of per diode | 12                 |      |      |      |      |  |
| Storage Temperature                    | Tstg   | $^{\circ}$ C |  | -55 ~ <b>+</b> 150 |      |      |      |      |  |
| Junction Temperature                   | Tj     | $^{\circ}$   |  | -55 ~ +175         |      |      |      |      |  |

## Electrical Characteristics (Ta=25°C Unless otherwise specified)

| DADAMETER                     | 0 h . l       | 11!4          | it Conditions  |         | MUR-CT |      |      |      |      |
|-------------------------------|---------------|---------------|--|---------|--------|------|------|------|------|
| PARAMETER                     | Symbol        | Unit          |  |         | 1010   | 1015 | 1020 | 1040 | 1060 |
| Peak Forward Voltage          | VFM           | V             | I <sub>FM</sub> =  | 5.0A    | 0.975  |      | 1.30 | 1.7  |      |
| Peak Reverse Current          | IRRM1         |               | Vrm=Vrrm   | Ta=25℃  |        |      | 10   |      |      |
| Peak Reverse Current          | IRRM2         | - μA          | VRM-VRRM   | Ta=125℃ |        |      | 500  |      |      |
| Maximum reverse recovery time | Trr           | ns            | I <sub>F</sub> =0.5A,I <sub>R</sub> =1.0A,I <sub>rr</sub> =0.25A |         | 35     |      |      | 50   |      |
| Thermal Resistance            | <b>R</b> өJ-С | <b>R</b> өJ-с | Between junction and case  |         | 2.0    |      |      |      |      |

Revised: 2021-11-29










# MUR1010CT THRU MUR1060CT


#### ■ Characteristics (Typical)









**FIG4:Typical Reverse Characteristics** 



### FIG5:Diagram of circuit and Testing wave form of reverse recovery time

Revised: 2021-11-29












# MUR1010CT THRU MUR1060CT

#### ■ Ordering Information (Example)

| PREFERED            | PACKAGE CODE | MINIMUM PACKAGE(pcs) | INNER BOX QUANTITY(pcs) | OUTER CARTON QUANTITY(pcs) | DELIVERY MODE |  |
|---------------------|--------------|----------------------|-------------------------|----------------------------|---------------|--|
| MUR1010CT~MUR1060CT | TO-220AB     | 50                   | 1000                    | 5000                       | Tube          |  |

#### ■ Outline Dimensions



Revised: 2021-11-29



