



SPECIFICATIONS

Current Rating: Lamps
 Insulator Resistance: 5000Megaohms min.
 Dielectric Withstanding: AC 500v
 Contact Material: Brass
 Operating Temperature: -40 ° ~ +105°C
 Max Processing Temp: 230° T0 260° for 30-60 seconds
 Insulator Material: NYLON-6T
 PLTAING: GOLD FLASH
 UNSPECIFIED TOLERANCE: ±0.20

Dimensions list

Contacts Per row	Dimensions		Contacts Per row	Dimensions	
	A	B		A	B
1	2.0	0	21	42.0	40.0
2	4.0	2.0	22	44.0	42.0
3	6.0	4.0	23	46.0	44.0
4	8.0	6.0	24	48.0	46.0
5	10.0	8.0	25	50.0	48.0
6	12.0	10.0	26	52.0	50.0
7	14.0	12.0	27	54.0	52.0
8	16.0	14.0	28	56.0	54.0
9	18.0	16.0	29	58.0	56.0
10	20.0	18.0	30	60.0	58.0
11	22.0	20.0	31	62.0	60.0
12	24.0	22.0	32	64.0	62.0
13	26.0	24.0	33	66.0	64.0
14	28.0	26.0	34	68.0	66.0
15	30.0	28.0	35	70.0	68.0
16	32.0	30.0	36	72.0	70.0
17	34.0	32.0	37	74.0	72.0
18	36.0	34.0	38	76.0	74.0
19	38.0	36.0	39	78.0	76.0
20	40.0	38.0	40	80.0	78.0

APPROVALS		DATE				
DRAWN	ZHIWEI, CHEN	2015.07.07				
CHECKED				TITLE: 2.0mm DIP 180°		
APPROVALS				PART NO. GP26-2020WV-NP		
TOLERANCES ARE		30~Ø1.1	±0.30	ANGLE		
		10~30	±0.20	UNIT: mm	SCALE: 1:1	
		5~10	±0.15	DRAWING NO.	PROJ.	
		~ 5	±0.10		SHEET 1 OF 1	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			