


# JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

# AD-BAW56/V70/V99 Plastic-Encapsulated Diode

# AD-BAW56/V70/V99 Switching diode

#### **FEATURES**

- High switching speed
- For general purpose switching applications
- High conductance
- AEC-Q101 qualified



## MARKING AND EQUIVALENT CIRCUIT

AD-B	AW56	AD-B	AV70	AD-BAV99		
Marking	Equivalent circuit	Marking	Equivalent circuit	Marking AD-BAV70	Equivalent circuit	
Ā1	1 0 3	Ā4	100000000000000000000000000000000000000	Ā7	1 0 3	

 $\bar{A}^*$  = Device code

# MAXIMUM RATINGS (T<sub>j</sub> = 25°C unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak repetitive reverse voltage	$V_{RRM}$	70	V
Forward continuous current	I <sub>FM</sub>	200	mA
Non-repetitive peak forward surge current @ t = 8.3ms	I <sub>FSM</sub>	2	Α
Power dissipation	$P_D$	225	mW
Thermal resistance from junction to ambient	R <sub>θJA</sub> <sup>1)</sup>	556	°C/W
Operating junction and storage temperature range	T <sub>j</sub> , T <sub>stg</sub>	-55 ~ 150	°C


# **ELECTRICAL CHARACTERISTICS (Tj = 25°C unless otherwise specified)**


Parameter	Symbol	Test condition	Min	Тур	Max	Unit
Reverse breakdown voltage	$V_{BR}$	$I_R = 100 \mu A$	70			V
	$V_{F1}$	I <sub>F</sub> = 1mA	ı	-	0.715	
Forward voltage	V <sub>F2</sub>	I <sub>F</sub> = 10mA	-	-	0.855	
Forward voltage	V <sub>F3</sub>	I <sub>F</sub> = 50mA	-		1	V
	V <sub>F4</sub>	I <sub>F</sub> = 150mA			1.25	
Reverse current	I <sub>R</sub>	V <sub>R</sub> = 70V		1-/	2.5	μA
Capacitance between terminals	Ст	V <sub>R</sub> = 0V, f = 1MHz	3-1	-	1.5	pF
Reverse recovery time	t <sub>rr</sub>	$I_F = I_R = 10 \text{mA}, I_{rr} = 1 \text{mA}, R_L = 100 \Omega$	-	-	6	ns


<sup>1)</sup> Measured with the device mounted on 1 inch<sup>2</sup> FR-4 board with 1oz. single-side copper, in a still air environment with  $T_a = 25$ °C.

### TYPICAL CHARACTERISTICS












## **SOT-23 PACKAGE OUTLINE DIMENSIONS**








Combal	Dimensions	In Millimeters	Dimensions In Inches			
Symbol	Min	Max	Min	Max		
Α	0.900	1.150	0.035	0.045		
A1	0.000	0.100	0.000	0.004		
A2	0.900	1.050	0.035	0.041		
b	0.300	0.500	0.012	0.020		
С	0.080	0.150	0.003	0.006		
D	2.800	3.000	0.110	0.118		
E	1.200	1.400	0.047	0.055		
E1	2.250	2.550	0.089	0.100		
е	0.950	TYP	0.037	7 TYP		
e1	1.800	2.000	0.071	0.079		
L	0.550	REF	0.022	REF		
L1	0.300	0.500	0.012	0.020		
θ	0°	8°	0°	8°		

# **SOT-23 SUGGESTED PAD LAYOUT**




## Note:

- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

### **SOT-23 TAPE AND REEL**

## SOT-23 Embossed Carrier Tape





#### Packaging Description:

SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

	Dimensions are in millimeter									
Pkg type         A         B         C         d         E         F         P0         P         P1         W							W			
SOT-23	3.15	2.77	1.22	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

### SOT-23 Tape Leader and Trailer





Dimensions are in millimeter									
Reel Option	Reel Option         D         D1         D2         G         H         I         W1         W2								
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30	

REEL	Reel Size	Вох	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	

#### **PUBLISHED BY**

JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

13th Floor, C Block, Tengfei Building, Yan Chuang Yuan, Nanjing Jiangbei New Area, China

#### **LEGAL DISCLAIMER**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples, hints or typical values stated herein and/or any information regarding the application of the device, JSCJ hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of JSCJ in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

#### **INFORMATION**

For further information on technology, delivery terms and conditions as well as prices, please contact your nearest JSCJ office (<a href="https://www.jscj-elec.com">www.jscj-elec.com</a>).

#### **WARNINGS**

Due to technical requirements, products may contain dangerous substances. For information on the types in question, please contact your nearest JSCJ office.

Except as otherwise explicitly approved by JSCJ in a written document signed by authorized representatives of JSCJ, JSCJ's products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.