



Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
 - 2.Current rating:1A AC/DC
额定电流: 1A AC/DC
 - 3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
 - 4.Temperature range:-40 °C-+105 °C
温度范围: -40 °C-+105 °C
 - 5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
 - 6.Contact resistance:20mΩMax
接触电阻: ≥20mΩ
- Material:
材料:
- 7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
 - 8.The iron shell:SPCC Nivkel Plating/Tin Plating
铁壳: SPCC, 镀镍/镀锡
- B、成品不能有弯针，R角不一致等不良。

X07 XX F X X X 5
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09;15;25;37
- ③ Welding Board Angle :F-Female
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Categoty: 1:1U 2:2U 3:3U 4:4U 5:5U 6:6U 7:AuSn
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5

NUMBER OF POSITIONS	DIMENSION				
	A±0.40	B±0.30	C±0.30	D±0.25	E±0.25
9	30.80	25.00	16.35	11.08	10.16
15	39.14	33.30	24.75	19.39	17.78
25	53.05	47.04	38.35	33.24	30.38
37	69.32	63.50	54.75	49.86	45.72

X07XXFXXX5	XDBLS	XDBLM
PART NO	SCREW	NUT

						DSND		SCALE: N/A	MODEL TYPE: D-USB
Δx					ANGULAR	DWN		VIEW:	PART NO.: X07XXFXXX5
Δx					L ≤ 4	CHKD		UNIT: mm/in	DWG NO.: X-X07XXFXXX5
Δx					4 < L ≤ 16	APPD		SIZE: A4	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63				
					L > 63				
					UNSPECIFIED TOLERANCES				
					XKB INDUSTRIAL PRECISION CO.,LIMITED	WEIGHT	SHEET	REVISION	
					www.helloxkb.com www.helloxkb.cn www.xk-dg.cn		1/1	A0	