



Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压：250V AC/DC
- 2.Current rating:1A AC/DC
额定电流：1A AC/DC
- 3.Withstanding voltage:500V AC/minute
耐受电压：≥500V AC/分钟
- 4.Temperature range:-40℃~+105℃
温度范围：-40℃~+105℃
- 5.Insulation resistance:1000MΩMIN
绝缘电阻：≥1000MΩ
- 6.Contact resistance:20mΩMax
接触电阻：≥20mΩ

Material:

材料:

- 7.Rubber core:PBT UL94V-0
胶芯：PBT UL94V-0
 - 8.The iron shell:SPCC Nivkel Plating/Tin Plating
铁壳：SPCC,镀镍/镀锡
- B、成品不能有弯针，R角不一致等不良。

X08 XX W X X X 5
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09;15;25;37
- ③ Welding Board Angle :W-Male
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Categoty: 1:1U 2:2U 3:3U 4:4U 5:5U 6:6U 7:AuSn
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5

NUMBER OF POSITIONS	DIMENSION				
	A±0.40	B±0.30	C±0.30	D±0.65	E±0.25
9	30.80	25.00	16.35	11.08	10.16
15	39.14	33.30	24.75	19.39	17.78
25	53.05	47.04	38.35	33.24	30.38
37	69.32	63.50	54.75	49.86	45.72

X08XXWXXX5	XDBLS	XDBLM
PART NO	SCREW	NUT

										DSND		SCALE: N/A	MODEL TYPE: D-USB		
						ANGLAR	±5°			DWN		VIEW:	PART NO.: X08XXWXXX5		
ΔX						L ≤ 4	±0.2			CHKD		UNIT: mm/in	DWG NO.: X-X08XXWXXX5		
ΔX						4 < L ≤ 16	±0.3			APPD		SIZE: A4			
ΔX						16 < L ≤ 63	±0.4								
MARK						L > 63	±0.5								
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn														1/1	A0

