GL34A, GL34B, GL34D, GL34G, GL34J

Vishay General Semiconductor

Surface-Mount Glass Passivated Junction Rectifier

F


Superectifier®



GL34 (DO-213AA)

PRIMARY CHARACTERISTICS						
I _{F(AV)}	0.5 A					
V_{RRM}	50 V, 100 V, 200 V, 400 V, 600 V					
I _{FSM}	10 A					
V _F	1.2 V, 1.3 V					
I _R	5.0 μA					
T _J max.	175 °C					
Package	GL34 (DO-213AA)					
Circuit configurations	Single					

FEATURES





• Low forward voltage drop

• Low leakage current

w leakage current

 Meets MSL level 1, per J-STD-020, LF maximum COMPLIANT peak of 260 °C

 Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, automotive and telecommunication.

MECHANICAL DATA

Case: GL34 (DO-213AA), molded epoxy over glass body Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: two bands indicate cathode end - 1st band denotes device type and 2nd band denotes repetitive peak reverse voltage rating

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)							
PARAMETER	CVAIDOL	01.044	GL34B	GL34D	GL34G	GL34J	UNIT
STANDARD RECOVERY DEVICE: 1ST BAND IS WHITE	SYMBOL	GL34A					
Polarity color bands (2 nd band)		Gray	Red	Orange	Yellow	Green	
Max. repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	V
Max. RMS voltage	V_{RMS}	35	70	140	280	420	V
Max. DC blocking voltage	V_{DC}	50	100	200	400	600	V
Max. average forward rectified current at T _L = 75 °C	I _{F(AV)}	0.5					Α
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	10				Α	
Max. full load reverse current, full cycle average at $T_A = 55$ °C	I _{R(AV)}	30				μΑ	
Operating junction and storage temperature range	T _J , T _{STG}	-65 to +175					°C



GL34A, GL34B, GL34D, GL34G, GL34J

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)								
PARAMETER	TEST (CONDITIONS	SYMBOL	GL34A GL34B GL34D GL34G G		GL34J	UNIT	
Max. instantaneous forward voltage	0.5 A		V _F	1.2			1.3	V
Max. DC reverse current at rated		T _A = 25 °C		5.0				
DC blocking voltage		T _A = 125 °C	IR	50			μA	
Typical reverse recovery time	$I_F = 0.5$ $I_{rr} = 0.2$	A, I _R = 1.0 A, 5 A	t _{rr}	1.5			μs	
Typical junction capacitance	4.0 V, 1	MHz	CJ	4.0			pF	

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)								
PARAMETER	SYMBOL	GL34A	GL34B	GL34D	GL34G	GL34J	UNIT	
Maximum thermal resistance	$R_{\theta JA}^{(1)}$	150					°C/W	
iviaximum memarresistance	R _{0JT} (2)	70					C/ VV	

Notes

⁽²⁾ Thermal resistance from junction to terminal, 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal

ORDERING INFORMATION (Example)								
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE				
GL34G-E3/98	0.036	98	2500	7" diameter plastic tape and reel				
GL34G-E3/83	0.036	83	9000	13" diameter plastic tape and reel				

 $^{^{(1)}}$ Thermal resistance from junction to ambient, 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal

www.vishay.com Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Max. Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Characteristics





Fig. 5 - Typical Junction Capacitance

GL34A, GL34B, GL34D, GL34G, GL34J

Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

GL34 (DO-213AA)



^{1&}lt;sup>st</sup> band denotes type and polarity 2nd band denotes voltage type



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.